

TYPES

- Type **E**: corner clamp.
- Type **EB**: corner clamp with securing pin.
- Type **F**: surface clamp.
- Type **FA**: surface clamp with stop plate.
- Type **FB**: surface clamp with securing pin.

Die-cast zinc alloy **ZD**

Epoxy resin coating:

- Black, RAL 9005, textured finish **SW**
- Silver, RAL 9006, textured finish **SR**

Grub screws

Stainless Steel AISI 304

Rubber inserts

Acrylonitrile butadiene rubber (NBR)

Stop plate (type FA)

AISI 316L stainless steel

Securing pins (type EB and FB)

- Stainless Steel AISI 304



Plastic coated polyamide (PA)

FEATURES AND APPLICATIONS


Clamps GN 939 are used to fasten panels of glass, plastic or other materials. Both corner and surface clamps are available, depending on the installation situation. !da duplicazione!

The panels are clamped between the rubber inserts. In addition, positive locking by means of a securing pin or stop plate can be selected as a type.


If the clamps are used with profile systems with 8 or 10 mm slots, the T-nuts GN 938.1 (see page) are available as mounting accessories. These enable simple alignment, secure the clamps against rotation and counteract possible stresses.





GN 939-E



GN 939-F



Conversion Table			
1 mm = 0.039 inch			
l1		s	
mm	inch	mm	inch
60	2.36	5	0.20
		6	0.24
		8	0.31
		10	0.39
		12	0.47



GN 939-E-SW

Code	Description	d1 Clamping screw	b1	b2	l1	l3	h1	s	sw/rTorx	⚖
GN.42433	GN 939-ZD-60-5-E-SW	M6	8.5	11.4	60	8.3	15.5	5	T30	260
GN.42448	GN 939-ZD-60-6-E-SW	M6	8.5	11.4	60	8.3	15.5	6	T30	261
GN.42464	GN 939-ZD-60-8-E-SW	M6	8.5	11.4	60	8.3	15.5	8	T30	273
GN.42476	GN 939-ZD-60-10-E-SW	M6	8.5	11.4	60	8.3	15.5	10	T30	285
GN.42488	GN 939-ZD-60-12-E-SW	M6	8.5	11.4	60	8.3	15.5	12	T30	297

GN 939-E-SR

Code	Description	d1 Clamping screw	b1	b2	l1	l3	h1	s	sw/rTorx	⚖
GN.42432	GN 939-ZD-60-5-E-SR	M6	8.5	11.4	60	8.3	15.5	5	T30	260
GN.42447	GN 939-ZD-60-6-E-SR	M6	8.5	11.4	60	8.3	15.5	6	T30	261
GN.42463	GN 939-ZD-60-8-E-SR	M6	8.5	11.4	60	8.3	15.5	8	T30	273
GN.42475	GN 939-ZD-60-10-E-SR	M6	8.5	11.4	60	8.3	15.5	10	T30	285
GN.42487	GN 939-ZD-60-12-E-SR	M6	8.5	11.4	60	8.3	15.5	12	T30	297


GN 939-EB-SW

Code	Description	d1 Clamping screw	d2	b1	b2	l1	l3	h1	m1	s	sw/rTorx	⚖
GN.42431	GN 939-ZD-60-5-EB-SW	M6	8.4	8.5	11.4	60	8.3	15.5	34	5	T30	260
GN.42446	GN 939-ZD-60-6-EB-SW	M6	8.4	8.5	11.4	60	8.3	15.5	34	6	T30	266
GN.42462	GN 939-ZD-60-8-EB-SW	M6	8.4	8.5	11.4	60	8.3	15.5	34	8	T30	278
GN.42474	GN 939-ZD-60-10-EB-SW	M6	8.4	8.5	11.4	60	8.3	15.5	34	10	T30	291
GN.42486	GN 939-ZD-60-12-EB-SW	M6	8.4	8.5	11.4	60	8.3	15.5	34	12	T30	303

GN 939-EB-SR

Code	Description	d1 Clamping screw	d2	b1	b2	l1	l3	h1	m1	s	sw/rTorx	⚖
GN.42430	GN 939-ZD-60-5-EB-SR	M6	8.4	8.5	11.4	60	8.3	15.5	34	5	T30	260
GN.42445	GN 939-ZD-60-6-EB-SR	M6	8.4	8.5	11.4	60	8.3	15.5	34	6	T30	266
GN.42461	GN 939-ZD-60-8-EB-SR	M6	8.4	8.5	11.4	60	8.3	15.5	34	8	T30	278
GN.42473	GN 939-ZD-60-10-EB-SR	M6	8.4	8.5	11.4	60	8.3	15.5	34	10	T30	291
GN.42485	GN 939-ZD-60-12-EB-SR	M6	8.4	8.5	11.4	60	8.3	15.5	34	12	T30	303

Conversion Table 1 mm = 0.039 inch			
l1		s	
mm	inch	mm	inch
60	2.36	5	0.20
		6	0.24
		8	0.31
		10	0.39
		12	0.47



METRIC

GN 939-F-SW

Code	Description	d1 Clamping screw	b1	b2	l1	l2	l3	h1	s	sw/rTorx	△
GN.42439	GN 939-ZD-60-5-F-SW	M6	8.5	11.4	60	60	8.3	15.5	5	T30	244
GN.42454	GN 939-ZD-60-6-F-SW	M6	8.5	11.4	60	60	8.3	15.5	6	T30	248
GN.42470	GN 939-ZD-60-8-F-SW	M6	8.5	11.4	60	60	8.3	15.5	8	T30	256
GN.42482	GN 939-ZD-60-10-F-SW	M6	8.5	11.4	60	60	8.3	15.5	10	T30	265
GN.42494	GN 939-ZD-60-12-F-SW	M6	8.5	11.4	60	60	8.3	15.5	12	T30	273

GN 939-F-SR

Code	Description	d1 Clamping screw	b1	b2	l1	l2	l3	h1	s	sw/rTorx	△
GN.42438	GN 939-ZD-60-5-F-SR	M6	8.5	11.4	60	60	8.3	15.5	5	T30	244
GN.42453	GN 939-ZD-60-6-F-SR	M6	8.5	11.4	60	60	8.3	15.5	6	T30	248
GN.42469	GN 939-ZD-60-8-F-SR	M6	8.5	11.4	60	60	8.3	15.5	8	T30	256
GN.42481	GN 939-ZD-60-10-F-SR	M6	8.5	11.4	60	60	8.3	15.5	10	T30	265
GN.42493	GN 939-ZD-60-12-F-SR	M6	8.5	11.4	60	60	8.3	15.5	12	T30	273

GN 939-FA-SW



Code	Description	d1 Clamping screw	b1	b2	l1	l2	l3	l4	h2	s	sw/rTorx	△
GN.42435	GN 939-ZD-60-5-FA-SW	M6	8.5	11.4	60	60	8.3	8.2	16.7	5	T30	252
GN.42450	GN 939-ZD-60-6-FA-SW	M6	8.5	11.4	60	60	8.3	8.2	16.7	6	T30	256
GN.42466	GN 939-ZD-60-8-FA-SW	M6	8.5	11.4	60	60	8.3	8.2	16.7	8	T30	265
GN.42478	GN 939-ZD-60-10-FA-SW	M6	8.5	11.4	60	60	8.3	8.2	16.7	10	T30	275
GN.42490	GN 939-ZD-60-12-FA-SW	M6	8.5	11.4	60	60	8.3	8.2	16.7	12	T30	285

GN 939-FA-SR

Code	Description	d1 Clamping screw	b1	b2	l1	l2	l3	l4	h2	s	sw/rTorx	△
GN.42434	GN 939-ZD-60-5-FA-SR	M6	8.5	11.4	60	60	8.3	8.2	16.7	5	T30	252
GN.42449	GN 939-ZD-60-6-FA-SR	M6	8.5	11.4	60	60	8.3	8.2	16.7	6	T30	256
GN.42465	GN 939-ZD-60-8-FA-SR	M6	8.5	11.4	60	60	8.3	8.2	16.7	8	T30	265
GN.42477	GN 939-ZD-60-10-FA-SR	M6	8.5	11.4	60	60	8.3	8.2	16.7	10	T30	275
GN.42489	GN 939-ZD-60-12-FA-SR	M6	8.5	11.4	60	60	8.3	8.2	16.7	12	T30	285



GN 939-FB-SW
GN 939-FB-SR



Conversion Table			
1 mm = 0.039 inch			
l1		s	
mm	inch	mm	inch
60	2.36	5	0.20
		6	0.24
		8	0.31
		10	0.39
		12	0.47

GN 939-FB-SW

METRIC

Code	Description	d1 Clamping screw	d2	b1	b2	l1	l2	l3	h1	m2	s	sw/rTorx	△
GN.42437	GN 939-ZD-60-5-FB-SW	M6	8.4	8.5	11.4	60	60	8.3	15.5	34.5	5	T30	248
GN.42452	GN 939-ZD-60-6-FB-SW	M6	8.4	8.5	11.4	60	60	8.3	15.5	34.5	6	T30	252
GN.42468	GN 939-ZD-60-8-FB-SW	M6	8.4	8.5	11.4	60	60	8.3	15.5	34.5	8	T30	261
GN.42480	GN 939-ZD-60-10-FB-SW	M6	8.4	8.5	11.4	60	60	8.3	15.5	34.5	10	T30	270
GN.42492	GN 939-ZD-60-12-FB-SW	M6	8.4	8.5	11.4	60	60	8.3	15.5	34.5	12	T30	265

GN 939-FB-SR

Code	Description	d1 Clamping screw	d2	b1	b2	l1	l2	l3	h1	m2	s	sw/rTorx	△
GN.42436	GN 939-ZD-60-5-FB-SR	M6	8.4	8.5	11.4	60	60	8.3	15.5	34.5	5	T30	248
GN.42451	GN 939-ZD-60-6-FB-SR	M6	8.4	8.5	11.4	60	60	8.3	15.5	34.5	6	T30	252
GN.42467	GN 939-ZD-60-8-FB-SR	M6	8.4	8.5	11.4	60	60	8.3	15.5	34.5	8	T30	261
GN.42479	GN 939-ZD-60-10-FB-SR	M6	8.4	8.5	11.4	60	60	8.3	15.5	34.5	10	T30	270
GN.42491	GN 939-ZD-60-12-FB-SR	M6	8.4	8.5	11.4	60	60	8.3	15.5	34.5	12	T30	265