

LEVER BODY

Black-oxide steel.

HANDLE

Phenolic based (PF) Duroplast, black colour, glossy finish, PLX. (see page 639).

HUB CAP

Anodised aluminium, natural colour.

STANDARD EXECUTIONS

Black-oxide steel clamping element, treated steel return spring.

- **GN 125-D**: straight arm, threaded hole or threaded screw of length as shown in the table.

- **GN 125-E**: 15° inclined arm, threaded hole or threaded screw of length as shown in the table.

FEATURES AND APPLICATIONS

Particularly suitable when the lever turning angle is limited owing to lack of space.

SPECIAL EXECUTIONS ON REQUEST

AISI 303 stainless steel adjustable handles.


INSTRUCTIONS

For clamping, lift the lever to disengage the clamping device teeth and bring it back to start position. By releasing the lever, the return spring automatically engages the teeth.



GN 125-D


GN 125-E



GN 125 (d2)

INCH

Code	Description	d1	d2	d3	d4	d5	h1	h2	h3	h4	h5	l	tmin	△
GN.918321	GN 125-32-5/16-18-D	1.26	5/16-18	0.53	0.31	0.79	0.81	0.06	0.49	-	0.16	3.94	0.43	0.31
GN.918121	GN 125-32-5/16-18-E	1.26	5/16-18	0.53	0.31	0.79	0.81	0.06	0.49	1.42	0.16	3.94	0.43	0.31
GN.918341	GN 125-36-3/8-16-D	1.42	3/8-16	0.63	0.39	0.98	0.96	0.08	0.59	-	0.18	4.72	0.55	0.49
GN.918131	GN 125-36-3/8-16-E	1.42	3/8-16	0.63	0.39	0.98	0.96	0.08	0.59	1.77	0.18	4.72	0.55	0.49
GN.918361	GN 125-40-1/2-13-D	1.57	1/2-13	0.75	0.47	1.18	1.04	0.08	0.63	-	0.18	5.12	0.67	0.68
GN.918141	GN 125-40-1/2-13-E	1.57	1/2-13	0.75	0.47	1.18	1.04	0.08	0.63	1.97	0.18	5.12	0.67	0.68
GN.918371	GN 125-45-5/8-11-D	1.77	5/8-11	0.91	0.47	1.26	1.24	0.08	0.79	-	0.2	5.71	0.91	0.94
GN.918151	GN 125-45-5/8-11-E	1.77	5/8-11	0.91	0.47	1.26	1.24	0.08	0.79	2.36	0.2	5.71	0.91	0.94



GN 125 (d2 - l1)

INCH

Code	Description	d1	d2	d3	d4	d5	h1	h2	h3	h4	h5	l	l1	⚖
GN.918402	GN 125-32-5/16-18-079-D	1.26	5/16-18	0.53	0.31	0.79	0.81	0.06	0.49	-	0.16	3.94	0.79	0.33
GN.918202	GN 125-32-5/16-18-079-E	1.26	5/16-18	0.53	0.31	0.79	0.81	0.06	0.49	1.42	0.16	3.94	0.79	0.33
GN.918404	GN 125-32-5/16-18-126-D	1.26	5/16-18	0.53	0.31	0.79	0.81	0.06	0.49	-	0.16	3.94	1.26	0.34
GN.918204	GN 125-32-5/16-18-126-E	1.26	5/16-18	0.53	0.31	0.79	0.81	0.06	0.49	1.42	0.16	3.94	1.26	0.34
GN.918412	GN 125-36-3/8-16-098-D	1.42	3/8-16	0.63	0.39	0.98	0.96	0.08	0.59	-	0.18	4.72	0.98	0.53
GN.918212	GN 125-36-3/8-16-098-E	1.42	3/8-16	0.63	0.39	0.98	0.96	0.08	0.59	1.77	0.18	4.72	0.98	0.53
GN.918414	GN 125-36-3/8-16-157-D	1.42	3/8-16	0.63	0.39	0.98	0.96	0.08	0.59	-	0.18	4.72	1.57	0.54
GN.918214	GN 125-36-3/8-16-157-E	1.42	3/8-16	0.63	0.39	0.98	0.96	0.08	0.59	1.77	0.18	4.72	1.57	0.54
GN.918422	GN 125-40-1/2-13-126-D	1.57	1/2-13	0.75	0.47	1.18	1.04	0.08	0.63	-	0.18	5.12	1.26	0.75
GN.918222	GN 125-40-1/2-13-126-E	1.57	1/2-13	0.75	0.47	1.18	1.04	0.08	0.63	1.97	0.18	5.12	1.26	0.75
GN.918423	GN 125-40-1/2-13-157-D	1.57	1/2-13	0.75	0.47	1.18	1.04	0.08	0.63	-	0.18	5.12	1.57	0.77
GN.918223	GN 125-40-1/2-13-157-E	1.57	1/2-13	0.75	0.47	1.18	1.04	0.08	0.63	1.97	0.18	5.12	1.57	0.77
GN.918434	GN 125-45-5/8-11-248-D	1.77	5/8-11	0.91	0.47	1.26	1.24	0.08	0.79	-	0.2	5.71	2.48	1.17
GN.918234	GN 125-45-5/8-11-248-E	1.77	5/8-11	0.91	0.47	1.26	1.24	0.08	0.79	2.36	0.2	5.71	2.48	1.17