



BASE FLANGE

Die-cast zinc alloy with epoxy resin coating, black colour.
Two holes for clamping by means of countersunk head screws.

PLUNGER

AISI 303 stainless steel.

SPRING

AISI 301 stainless steel.

KNOB

Polyamide based (PA) technopolymer, black colour, matte finish.

STANDARD EXECUTIONS

- **GN 822.8-B**: without rest position.
- **GN 822.8-C**: with rest position: pull the knob and turn it by 30°.

FEATURES AND APPLICATIONS

GN 822.8 mini indexing plungers have compact dimensions and are particularly suitable for assembly on thin sheets.

