

LEVER BODY

Die-cast zinc alloy, epoxy resin coating, black colour, matte finish.

STANDARD EXECUTIONS

Black-oxide steel clamping element and retaining screw. Steel return spring.

- Threaded hole.
- Threaded screw, length as shown in the table.

FEATURES AND APPLICATIONS

The horizontal position of the GN 302 adjustable handle lever offers a more compact design. Particularly suitable for applications where lack of space reduces the field of action.



SPECIAL EXECUTIONS ON REQUEST

- Lever body in different colours.
- Chrome-plated lever.
- Clamping element with different threadings.

INSTRUCTIONS OF USE

For clamping, lift the lever to disengage the clamping device teeth and bring it back to start position. By releasing the lever, the return spring automatically engages the teeth.

If the lever cannot make a 360° rotation, the clamping element can be easily screwed by means of the hexagon socket front head screw (after having disengaged the lever).



GN 302 (d1)

INCH

Code	Description	l1	d1	d3	d4	h1	h2	h3	h4	tmin	⚖
GN.914611	GN 302-45-1/4-20-SW	1.77	1/4-20	0.39	0.51	0.96	0.16	0.87	0.14	0.35	0.07
GN.914631	GN 302-63-5/16-18-SW	2.48	5/16-18	0.53	0.69	1.22	0.26	1.12	0.16	0.43	0.16
GN.914641	GN 302-78-3/8-16-SW	3.07	3/8-16	0.63	0.83	1.42	0.31	1.34	0.16	0.55	0.26

GN 302 (d1 - l2)

INCH

Code	Description	l1	d1	d3	d4	h1	h2	h3	h4	l2	⚖
GN.914711	GN 302-45-1/4-20-079-SW	1.77	1/4-20	0.39	0.51	0.96	0.16	0.87	0.14	0.79	0.08
GN.914716	GN 302-45-1/4-20-098-SW	1.77	1/4-20	0.39	0.51	0.96	0.16	0.87	0.14	0.98	0.08
GN.914721	GN 302-45-1/4-20-126-SW	1.77	1/4-20	0.39	0.51	0.96	0.16	0.87	0.14	1.26	0.08
GN.914756	GN 302-63-5/16-18-126-SW	2.48	5/16-18	0.53	0.69	1.22	0.26	1.12	0.16	1.26	0.19
GN.914761	GN 302-63-5/16-18-157-SW	2.48	5/16-18	0.53	0.69	1.22	0.26	1.12	0.16	1.57	0.2
GN.914766	GN 302-63-5/16-18-197-SW	2.48	5/16-18	0.53	0.69	1.22	0.26	1.12	0.16	1.97	0.2
GN.914791	GN 302-78-3/8-16-126-SW	3.07	3/8-16	0.63	0.83	1.42	0.31	1.34	0.16	1.26	0.31
GN.914796	GN 302-78-3/8-16-157-SW	3.07	3/8-16	0.63	0.83	1.42	0.31	1.34	0.16	1.57	0.32
GN.914801	GN 302-78-3/8-16-197-SW	3.07	3/8-16	0.63	0.83	1.42	0.31	1.34	0.16	1.97	0.33