

LEVER BODY

Die cast zinc alloy, epoxy resin coating.

COLOUR

RAL 9005 (SW) black, RAL 3000 (RS) red or RAL 2004 (OS) orange, matte finish.

BASE FLANGE

Die-cast zinc alloy, epoxy resing coating, black colour, matte finish, with two holes for clamping by means of countersunk head screws.

CLAMPING ELEMENT

Zinc-plated steel.

NUT


Zinc-plated steel.

STANDARD EXECUTIONS

- **GN 702-A:** base flanges with two holes for clamping by means of countersunk head screws.
- **GN 702-B:** machine element with threaded hole.
- **GN 702-C:** machine element with threaded ring.


FEATURES AND APPLICATIONS

GN 702 locks are suitable for clamping, by means of the lever rotation, drawers or doors in applications subject to strong vibrations. Locking position of the lever every 90 °.




GN 702-A

Code	Description	d	r	b	l ₁	l ₂	l _{3 min}	l ₄	Δ
GN.30754	GN 702-17-40-A-SW	17	40	10	5.5	16.5	21.5	11	75
GN.30753	GN 702-17-40-A-RS	17	40	10	5.5	16.5	21.5	11	78
GN.70151	GN 702-17-40-A-OS	17	40	10	5.5	16.5	21.5	11	77
GN.30764	GN 702-17-55-A-SW	17	55	10	5.5	16.5	21.5	11	84
GN.30763	GN 702-17-55-A-RS	17	55	10	5.5	16.5	21.5	11	83
GN.70161	GN 702-17-55-A-OS	17	55	10	5.5	16.5	21.5	11	83



GN 702-B

Code	Description	d	r	b	l_1	l_2	$l_{3 \min}$	l_4	Δ
GN.30758	GN 702-17-40-B-SW	17	40	10	5.5	16.5	21.5	11	59
GN.30757	GN 702-17-40-B-RS	17	40	10	5.5	16.5	21.5	11	59
GN.70152	GN 702-17-40-B-OS	17	40	10	5.5	16.5	21.5	11	58
GN.30768	GN 702-17-55-B-SW	17	55	10	5.5	16.5	21.5	11	64
GN.30767	GN 702-17-55-B-RS	17	55	10	5.5	16.5	21.5	11	70
GN.70162	GN 702-17-55-B-OS	17	55	10	5.5	16.5	21.5	11	65



GN 702-C

Code	Description	d	r	b	l_1	l_2	$l_{3 \min}$	l_4	Δ
GN.30760	GN 702-17-40-C-SW	17	40	10	5.5	16.5	21.5	11	69
GN.30759	GN 702-17-40-C-RS	17	40	10	5.5	16.5	21.5	11	70
GN.70153	GN 702-17-40-C-OS	17	40	10	5.5	16.5	21.5	11	70
GN.30770	GN 702-17-55-C-SW	17	55	10	5.5	16.5	21.5	11	76
GN.30769	GN 702-17-55-C-RS	17	55	10	5.5	16.5	21.5	11	76
GN.70163	GN 702-17-55-C-OS	17	55	10	5.5	16.5	21.5	11	76