

CLAMPING ELEMENTS

Black-oxide steel.

CLAMPING SCREW

Zinc-plated steel.

SPRING

Stainless steel.

ASSEMBLY TOOL (TO BE ORDERED SEPARATELY)



Black-oxide steel.

FEATURES AND APPLICATIONS

GN 928 clamping elements allow the fastening of round cross section shafts, from 6 to 125 mm of diameter, in a precise and quick way. d1 threaded hole can be used for connecting to other elements, for clamping by means of GN 928.1, for connecting to a grub screw in order to keep the element in axial position during assembly.



Conversion Table	
1 mm = 0.039 inch	
d1	
mm	inch
8	0.31
10	0.39
12	0.47
16	0.63
20	0.79
25	0.98
30	1.18



Code	Description	d1h11	d4H7	d2	d3	d5	l1	l2	l3	e+0.2	sw		Assembly tool
GN.68451	GN 928-8	8	8	M4	6 + 10	M2.5	22	8	4	d3/2 + 2.8	3	5	GN 928.1-3
GN.68452	GN 928-10	10	10	M5	10 + 15	M3	30	10	5	d3/2 + 3.3	4	15	GN 928.1-4
GN.68453	GN 928-12	12	12	M6	15 + 20	M4	36	12	6	d3/2 + 3.5	5	20	GN 928.1-5
GN.68454	GN 928-16	16	16	M8	20 + 30	M5	48	16	8	d3/2 + 4	6	52	GN 928.1-6
GN.68455	GN 928-20	20	20	M10	30 + 40	M6	60	20	10	d3/2 + 4.8	8	105	GN 928.1-8
GN.68456	GN 928-25	25	25	M12	40 + 60	M8	72	25	12	d3/2 + 5.6	10	190	GN 928.1-10
GN.68457	GN 928-30	30	30	M16	60 + 125	M10	85	30	16	d3/2 + 7.9	14	345	GN 928.1-14