



BASE FLANGE

AISI 304 stainless steel with two holes for fixation by means of two screws.

PLUNGER

AISI 303 stainless steel.

SPRING

AISI 301 stainless steel.







STANDARD EXECUTIONS

Polyamide based (PA) technopolymer knob, black colour, matte finish:

- **GN 822.9-B**: without rest position.
 - **GN 822.9-C**: with six detent positions: pull the knob and turn it by 30°.
- AISI CF-8 stainless steel knob, sandblasted matte finish.
- **GN 822.9-BN**: without rest position.
 - **GN 822.9-CN**: with six detent positions: pull the knob and turn it by 30°.

FEATURES AND APPLICATIONS

GN 822.9 indexing plungers have compact dimensions and are used on thin sheets.



Conversion Table	
1 mm = 0.039 inch	
d1	
mm	inch
4	0.16
5	0.20
6	0.24
8	0.31
10	0.39

GN 822.9-B

Code	Description	d1	d2-0.05-0.1	d3	d4	b1	b2	k	l1	l2	l3	l4	l5	Stroke	[N]*	[N]#	
		Plunger h9 Hole +0.08 +0.03															
GN.36633	GN 822.9-4-5-B	4	8	21	4.3	35	15	25	5	20.5	2	2	5	4	12	23	
GN.36637	GN 822.9-4-10-B	4	8	21	4.3	35	15	25	10	20.5	2	2	5	4	12	25	
GN.36643	GN 822.9-5-6-B	5	10	25	4.3	40	18	30	6	25.5	2.5	2	6	6	16	40	
GN.36647	GN 822.9-5-12-B	5	10	25	4.3	40	18	30	12	25.5	2.5	2	6	6	16	43	
GN.36653	GN 822.9-6-6-B	6	10	25	4.3	40	18	30	6	25.5	2.5	2	6	6	16	42	
GN.36657	GN 822.9-6-12-B	6	10	25	4.3	40	18	30	12	25.5	2.5	2	6	6	16	45	
GN.36663	GN 822.9-8-10-B	8	14	33	5.3	50	23	38	10	35	2.5	3	10	11	35	100	
GN.36669	GN 822.9-8-20-B	8	14	33	5.3	50	23	38	20	35	2.5	3	10	11	35	106	
GN.36677	GN 822.9-10-10-B	10	14	33	5.3	50	23	38	10	35	2.5	3	10	11	35	112	
GN.36683	GN 822.9-10-20-B	10	14	33	5.3	50	23	38	20	35	2.5	3	10	11	35	119	

* Spring preload

Spring maximum load