



STANDARD EXECUTIONS


Hub with threaded pass-through hole.

Arm fixed to the hub by welding.

- **GN 99.5:** zinc-plated steel.

- **GN 99.6:** AISI 304 stainless steel, sandblasted matte finish.

- **GN 99.6-A4:** AISI 316L stainless steel, sandblasted matte finish.



Conversion Table	
1 mm = 0.039 inch	
	l2
mm	inch
60	2.36
76	2.99
95	3.74
119	4.68
152	5.98

GN 99.5

METRIC

Code	Description	l1	l2	d1	h1	h2	d2	d3	⚖
GN.20501	GN 99.5-63-M8	63	60	M8	12.5	30.5	16	10	39
GN.20511	GN 99.5-80-M10	80	76	M10	15	37	20	12	74
GN.20521	GN 99.5-100-M12	100	95	M12	19	46	25	14	146
GN.20531	GN 99.5-125-M16	125	119	M16	25	58.5	32	18	309
GN.20541	GN 99.5-160-M20	160	152	M20	31	73	40	20	522

GN 99.6

INOX
STAINLESS
STEEL

METRIC

Code	Description	l1	l2	d1	h1	h2	d2	d3	⚖
GN.20601	GN 99.6-63-M8	63	60	M8	12.5	30.5	16	10	39
GN.20611	GN 99.6-80-M10	80	76	M10	15	37	20	12	75
GN.20621	GN 99.6-100-M12	100	95	M12	19	46	25	14	147
GN.20631	GN 99.6-125-M16	125	119	M16	25	58.5	32	18	309
GN.20641	GN 99.6-160-M20	160	152	M20	31	73	40	20	526

GN 99.6-A4

INOX
STAINLESS
STEEL

METRIC

Code	Description	l1	l2	d1	h1	h2	d2	d3	⚖
GN.20602	GN 99.6-63-M8-A4	63	60	M8	12.5	30.5	16	10	45
GN.20612	GN 99.6-80-M10-A4	80	76	M10	15	37	20	12	75
GN.20622	GN 99.6-100-M12-A4	100	95	M12	19	46	25	14	149