



1

LEVER BODY

Die-cast zinc alloy, epoxy resin coating

- RAL 9005 black colour matte finish **B**
- RAL 2004 orange colour matte finish **O**
- RAL 3000 red colour matte finish **R**
- RAL 9006 silver colour matte finish **S**



2



3

AXIS

Nickel-plated AISI 303 stainless steel.



4

CLAMPING ELEMENT

Zinc-plated steel with threaded hole or threaded screw.



5

STANDARD EXECUTIONS

Threaded hole (d1):

- **GN 927-A (d1)**: positioning with zinc-plated, threaded adjustment wing nut, with zinc-plated support bushing with glass fibre reinforced acetal-based technopolymer (POM) contact insert.
- **GN 927-B (d1)**: positioning without adjustment wing nut, with support bushing in glass-fibre reinforced polyamide based (PA) technopolymer.



6

Threaded screw (d2 - l2):

- **GN 927-A (d2 - l2)**: positioning with zinc-plated, threaded adjustment wing nut, with zinc-plated support bushing with glass fibre reinforced acetal-based technopolymer (POM) contact insert.
- **GN 927-B (d2 - l2)**: positioning without adjustment wing nut, with support bushing in glass-fibre reinforced polyamide based (PA) technopolymer.



7



8



9



10



11



12



13



14



15



16



17



18



19




**FEATURES AND APPLICATIONS**


GN 927 clamping levers are particularly suitable for quick clamping.

The GN 927-A version with adjustment wing nut provides quick and efficient tightening. In fact, the adjustment wing nut at the base enables adjustment of the tightening force used and simultaneous locking of the lever in the position required.

This type of lever allows you to reach clamping forces up to 8 kN.

Way of clamping





GN 927-A (d1)



INCH

Code	Description	d ₁	l ₁	l _{3 min} *	l _{3 max} *	l ₄	l ₅ *	d ₃	d ₄	h**	t	b	⚖
GN.93560151	GN 927-44-8-32-A-B	8 - 32	1.73	0.52	0.60	0.08	0.09	0.47	0.59	0.02	0.31	0.47	0.06
GN.93562151	GN 927-44-10-32-A-B	10 - 32	1.73	0.52	0.60	0.08	0.09	0.47	0.59	0.02	0.31	0.47	0.06
GN.93193351	GN 927-63-10-32-A-B	10 - 32	2.48	0.64	0.74	0.10	0.12	0.63	0.75	0.03	0.39	0.63	0.12
GN.93193151	GN 927-63-1/4-20-A-B	1/4 - 20	2.48	0.64	0.74	0.10	0.12	0.63	0.75	0.03	0.39	0.63	0.12
GN.93194851	GN 927-82-1/4-20-A-B	1/4 - 20	3.23	0.77	0.89	0.12	0.15	0.79	0.98	0.04	0.47	0.79	0.25
GN.93195151	GN 927-82-5/16-18-A-B	5/16 - 18	3.23	0.77	0.89	0.12	0.15	0.79	0.98	0.04	0.47	0.79	0.46
GN.93189851	GN 927-101-5/16-18-A-B	5/16 - 18	3.98	1.00	1.16	0.16	0.19	1.02	1.18	0.06	0.59	0.98	0.46
GN.93190151	GN 927-101-3/8-16-A-B	3/8 - 16	3.98	1.00	1.16	0.16	0.19	1.02	1.18	0.06	0.59	0.98	0.47
GN.93195096	GN 927-44-8-32-A-O	8 - 32	1.73	0.52	0.60	0.08	0.09	0.47	0.59	0.02	0.31	0.47	0.06
GN.93195097	GN 927-44-10-32-A-O	10 - 32	1.73	0.52	0.60	0.08	0.09	0.47	0.59	0.02	0.31	0.47	0.06
GN.93195098	GN 927-63-10-32-A-O	10 - 32	2.48	0.64	0.74	0.10	0.12	0.63	0.75	0.03	0.39	0.63	0.12
GN.93195099	GN 927-63-1/4-20-A-O	1/4 - 20	2.48	0.64	0.74	0.10	0.12	0.63	0.75	0.03	0.39	0.63	0.12
GN.93195100	GN 927-82-1/4-20-A-O	1/4 - 20	3.23	0.77	0.89	0.12	0.15	0.79	0.98	0.04	0.47	0.79	0.25
GN.93195101	GN 927-82-5/16-18-A-O	5/16 - 18	3.23	0.77	0.89	0.12	0.15	0.79	0.98	0.04	0.47	0.79	0.46
GN.93195102	GN 927-101-5/16-18-A-O	5/16 - 18	3.98	1.00	1.16	0.16	0.19	1.02	1.18	0.06	0.59	0.98	0.46
GN.93190101	GN 927-101-3/8-16-A-O	3/8 - 16	3.98	1.00	1.16	0.16	0.19	1.02	1.18	0.06	0.59	0.98	0.47
GN.93197701	GN 927-44-8-32-A-R	8 - 32	1.73	0.52	0.60	0.08	0.09	0.47	0.59	0.02	0.31	0.47	0.06
GN.93197702	GN 927-44-10-32-A-R	10 - 32	1.73	0.52	0.60	0.08	0.09	0.47	0.59	0.02	0.31	0.47	0.06
GN.93197703	GN 927-63-10-32-A-R	10 - 32	2.48	0.64	0.74	0.10	0.12	0.63	0.75	0.03	0.39	0.63	0.12
GN.93197704	GN 927-63-1/4-20-A-R	1/4 - 20	2.48	0.64	0.74	0.10	0.12	0.63	0.75	0.03	0.39	0.63	0.12
GN.93197705	GN 927-82-1/4-20-A-R	1/4 - 20	3.23	0.77	0.89	0.12	0.15	0.79	0.98	0.04	0.47	0.79	0.25
GN.93197706	GN 927-82-5/16-18-A-R	5/16 - 18	3.23	0.77	0.89	0.12	0.15	0.79	0.98	0.04	0.47	0.79	0.46
GN.93197707	GN 927-101-5/16-18-A-R	5/16 - 18	3.98	1.00	1.16	0.16	0.19	1.02	1.18	0.06	0.59	0.98	0.46
GN.93197708	GN 927-101-3/8-16-A-R	3/8 - 16	3.98	1.00	1.16	0.16	0.19	1.02	1.18	0.06	0.59	0.98	0.47
GN.93190501	GN 927-44-8-32-A-S	8 - 32	1.73	0.52	0.60	0.08	0.09	0.47	0.59	0.02	0.31	0.47	0.06
GN.93190502	GN 927-44-10-32-A-S	10 - 32	1.73	0.52	0.60	0.08	0.09	0.47	0.59	0.02	0.31	0.47	0.06
GN.93190503	GN 927-63-10-32-A-S	10 - 32	2.48	0.64	0.74	0.10	0.12	0.63	0.75	0.03	0.39	0.63	0.12
GN.93190504	GN 927-63-1/4-20-A-S	1/4 - 20	2.48	0.64	0.74	0.10	0.12	0.63	0.75	0.03	0.39	0.63	0.12
GN.93190505	GN 927-82-1/4-20-A-S	1/4 - 20	3.23	0.77	0.89	0.12	0.15	0.79	0.98	0.04	0.47	0.79	0.25
GN.93190506	GN 927-82-5/16-18-A-S	5/16 - 18	3.23	0.77	0.89	0.12	0.15	0.79	0.98	0.04	0.47	0.79	0.46
GN.93190507	GN 927-101-5/16-18-A-S	5/16 - 18	3.98	1.00	1.16	0.16	0.19	1.02	1.18	0.06	0.59	0.98	0.46
GN.93190508	GN 927-101-3/8-16-A-S	3/8 - 16	3.98	1.00	1.16	0.16	0.19	1.02	1.18	0.06	0.59	0.98	0.47

* In clamping position

** Stroke at 90° rotation of the lever* In clamping position

** Stroke at 90° rotation of the lever




INCH

GN 927-B (d1)

Code	Description	d ₁	l ₁	l ₆ *	l ₅ *	d ₃	d ₅	h**	t	b	
GN.93560251	GN 927-44-8-32-B-B	8 - 32	1.73	0.52	0.09	0.47	0.55	0.02	0.31	0.47	0.05
GN.93562251	GN 927-44-10-32-B-B	10 - 32	1.73	0.52	0.09	0.47	0.55	0.02	0.31	0.47	0.05
GN.93193451	GN 927-63-10-32-B-B	10 - 32	2.48	0.64	0.12	0.63	0.73	0.03	0.39	0.63	0.12
GN.93193251	GN 927-63-1/4-20-B-B	1/4 - 20	2.48	0.64	0.12	0.63	0.73	0.03	0.39	0.63	0.12
GN.93194951	GN 927-82-1/4-20-B-B	1/4 - 20	3.23	0.77	0.15	0.79	0.89	0.04	0.47	0.79	0.12
GN.93195251	GN 927-82-5/16-18-B-B	5/16 - 18	3.23	0.77	0.15	0.79	0.89	0.04	0.47	0.79	0.12
GN.93189951	GN 927-101-5/16-18-B-B	5/16 - 18	3.98	1.00	0.19	1.02	1.06	0.06	0.59	0.98	0.12
GN.93190251	GN 927-101-3/8-16-B-B	3/8 - 16	3.98	1.00	0.19	1.02	1.06	0.06	0.59	0.98	0.12
GN.93195103	GN 927-44-8-32-B-O	8 - 32	1.73	0.52	0.09	0.47	0.55	0.02	0.31	0.47	0.05
GN.93195104	GN 927-44-10-32-B-O	10 - 32	1.73	0.52	0.09	0.47	0.55	0.02	0.31	0.47	0.05
GN.93195105	GN 927-63-10-32-B-O	10 - 32	2.48	0.64	0.12	0.63	0.73	0.03	0.39	0.63	0.12
GN.93195106	GN 927-63-1/4-20-B-O	1/4 - 20	2.48	0.64	0.12	0.63	0.73	0.03	0.39	0.63	0.12
GN.93195107	GN 927-82-1/4-20-B-O	1/4 - 20	3.23	0.77	0.15	0.79	0.89	0.04	0.47	0.79	0.12
GN.93195108	GN 927-82-5/16-18-B-O	5/16 - 18	3.23	0.77	0.15	0.79	0.89	0.04	0.47	0.79	0.12
GN.93195109	GN 927-101-5/16-18-B-O	5/16 - 18	3.98	1.00	0.19	1.02	1.06	0.06	0.59	0.98	0.12
GN.93195110	GN 927-101-3/8-16-B-O	3/8 - 16	3.98	1.00	0.19	1.02	1.06	0.06	0.59	0.98	0.12
GN.93197709	GN 927-44-8-32-B-R	8 - 32	1.73	0.52	0.09	0.47	0.55	0.02	0.31	0.47	0.05
GN.93197710	GN 927-44-10-32-B-R	10 - 32	1.73	0.52	0.09	0.47	0.55	0.02	0.31	0.47	0.05
GN.93197711	GN 927-63-10-32-B-R	10 - 32	2.48	0.64	0.12	0.63	0.73	0.03	0.39	0.63	0.12
GN.93197712	GN 927-63-1/4-20-B-R	1/4 - 20	2.48	0.64	0.12	0.63	0.73	0.03	0.39	0.63	0.12
GN.93197713	GN 927-82-1/4-20-B-R	1/4 - 20	3.23	0.77	0.15	0.79	0.89	0.04	0.47	0.79	0.12
GN.93197714	GN 927-82-5/16-18-B-R	5/16 - 18	3.23	0.77	0.15	0.79	0.89	0.04	0.47	0.79	0.12
GN.93197715	GN 927-101-5/16-18-B-R	5/16 - 18	3.98	1.00	0.19	1.02	1.06	0.06	0.59	0.98	0.12
GN.93197716	GN 927-101-3/8-16-B-R	3/8 - 16	3.98	1.00	0.19	1.02	1.06	0.06	0.59	0.98	0.12
GN.93190509	GN 927-44-8-32-B-S	8 - 32	1.73	0.52	0.09	0.47	0.55	0.02	0.31	0.47	0.05
GN.93190510	GN 927-44-10-32-B-S	10 - 32	1.73	0.52	0.09	0.47	0.55	0.02	0.31	0.47	0.05
GN.93190511	GN 927-63-10-32-B-S	10 - 32	2.48	0.64	0.12	0.63	0.73	0.03	0.39	0.63	0.12
GN.93190512	GN 927-63-1/4-20-B-S	1/4 - 20	2.48	0.64	0.12	0.63	0.73	0.03	0.39	0.63	0.12
GN.93190513	GN 927-82-1/4-20-B-S	1/4 - 20	3.23	0.77	0.15	0.79	0.89	0.04	0.47	0.79	0.12
GN.93190514	GN 927-82-5/16-18-B-S	5/16 - 18	3.23	0.77	0.15	0.79	0.89	0.04	0.47	0.79	0.12
GN.93190515	GN 927-101-5/16-18-B-S	5/16 - 18	3.98	1.00	0.19	1.02	1.06	0.06	0.59	0.98	0.12
GN.93190516	GN 927-101-3/8-16-B-S	3/8 - 16	3.98	1.00	0.19	1.02	1.06	0.06	0.59	0.98	0.12

* In clamping position

** Stroke at 90° rotation of the lever





GN 927-A (d2 - I2)

INCH

Code	Description	d ₂	l ₁	l ₂ *	l _{3 min} *	l _{3 max} *	l ₄	l ₅ *	d ₃	d ₄	h**	b	Δ
GN.93560651	GN 927-44-8-32x12-A-B	8 - 32	1.73	0.47	0.52	0.60	0.08	0.09	0.47	0.59	0.02	0.47	0.06
GN.93560851	GN 927-44-8-32x16-A-B	8 - 32	1.73	0.63	0.52	0.60	0.08	0.09	0.47	0.59	0.02	0.47	0.06
GN.93561051	GN 927-44-8-32x20-A-B	8 - 32	1.73	0.79	0.52	0.60	0.08	0.09	0.47	0.59	0.02	0.47	0.06
GN.93561251	GN 927-44-8-32x25-A-B	8 - 32	1.73	0.98	0.52	0.60	0.08	0.09	0.47	0.59	0.02	0.47	0.06
GN.93561451	GN 927-44-8-32x30-A-B	8 - 32	1.73	1.18	0.52	0.60	0.08	0.09	0.47	0.59	0.02	0.47	0.07
GN.93562651	GN 927-44-10-32x12-A-B	10 - 32	1.73	0.47	0.52	0.60	0.08	0.09	0.47	0.59	0.02	0.47	0.06
GN.93562851	GN 927-44-10-32x16-A-B	10 - 32	1.73	0.63	0.52	0.60	0.08	0.09	0.47	0.59	0.02	0.47	0.06
GN.93563051	GN 927-44-10-32x20-A-B	10 - 32	1.73	0.79	0.52	0.60	0.08	0.09	0.47	0.59	0.02	0.47	0.07
GN.93563251	GN 927-44-10-32x25-A-B	10 - 32	1.73	0.98	0.52	0.60	0.08	0.09	0.47	0.59	0.02	0.47	0.07
GN.93563252	GN 927-44-10-32x30-A-B	10 - 32	1.73	1.18	0.52	0.60	0.08	0.09	0.47	0.59	0.02	0.47	0.07
GN.93563651	GN 927-44-10-32x35-A-B	10 - 32	1.73	1.38	0.52	0.60	0.08	0.09	0.47	0.59	0.02	0.47	0.07
GN.93563851	GN 927-44-10-32x40-A-B	10 - 32	1.73	1.57	0.52	0.60	0.08	0.09	0.47	0.59	0.02	0.47	0.07
GN.93565151	GN 927-63-10-32x16-A-B	10 - 32	2.48	0.63	0.64	0.74	0.10	0.12	0.63	0.75	0.03	0.63	0.13
GN.93193551	GN 927-63-10-32x20-A-B	10 - 32	2.48	0.79	0.64	0.74	0.10	0.12	0.63	0.75	0.03	0.63	0.13
GN.93193651	GN 927-63-10-32x25-A-B	10 - 32	2.48	0.98	0.64	0.74	0.10	0.12	0.63	0.75	0.03	0.63	0.14
GN.93193751	GN 927-63-10-32x30-A-B	10 - 32	2.48	1.18	0.64	0.74	0.10	0.12	0.63	0.75	0.03	0.63	0.13
GN.93193851	GN 927-63-10-32x35-A-B	10 - 32	2.48	1.38	0.64	0.74	0.10	0.12	0.63	0.75	0.03	0.63	0.14
GN.93193951	GN 927-63-10-32x40-A-B	10 - 32	2.48	1.57	0.64	0.74	0.10	0.12	0.63	0.75	0.03	0.63	0.14
GN.93194051	GN 927-63-1/4-20x25-A-B	1/4 - 20	2.48	1.97	0.64	0.74	0.10	0.12	0.63	0.75	0.03	0.63	0.14
GN.93565551	GN 927-63-1/4-20x16-A-B	1/4 - 20	2.48	0.63	0.64	0.74	0.10	0.12	0.63	0.75	0.03	0.63	0.13
GN.93194151	GN 927-63-1/4-20x20-A-B	1/4 - 20	2.48	0.79	0.64	0.74	0.10	0.12	0.63	0.75	0.03	0.63	0.13
GN.93194351	GN 927-63-1/4-20x25-A-B	1/4 - 20	2.48	0.98	0.64	0.74	0.10	0.12	0.63	0.75	0.03	0.63	0.14
GN.93194451	GN 927-63-1/4-20x30-A-B	1/4 - 20	2.48	1.18	0.64	0.74	0.10	0.12	0.63	0.75	0.03	0.63	0.14
GN.93194551	GN 927-63-1/4-20x35-A-B	1/4 - 20	2.48	1.38	0.64	0.74	0.10	0.12	0.63	0.75	0.03	0.63	0.14
GN.93194251	GN 927-63-1/4-20x40-A-B	1/4 - 20	2.48	1.57	0.64	0.74	0.10	0.12	0.63	0.75	0.03	0.63	0.15
GN.93194651	GN 927-63-1/4-20x50-A-B	1/4 - 20	2.48	1.97	0.64	0.74	0.10	0.12	0.63	0.75	0.03	0.63	0.15
GN.93566151	GN 927-82-1/4-20x20-A-B	1/4 - 20	3.23	0.79	0.77	0.89	0.12	0.15	0.79	0.98	0.04	0.79	0.26
GN.93195351	GN 927-82-1/4-20x25-A-B	1/4 - 20	3.23	0.98	0.77	0.89	0.12	0.15	0.79	0.98	0.04	0.79	0.26
GN.93195451	GN 927-82-1/4-20x30-A-B	1/4 - 20	3.23	1.18	0.77	0.89	0.12	0.15	0.79	0.98	0.04	0.79	0.26
GN.93195551	GN 927-82-1/4-20x35-A-B	1/4 - 20	3.23	1.38	0.77	0.89	0.12	0.15	0.79	0.98	0.04	0.79	0.26
GN.93195651	GN 927-82-1/4-20x40-A-B	1/4 - 20	3.23	1.57	0.77	0.89	0.12	0.15	0.79	0.98	0.04	0.79	0.26
GN.93195751	GN 927-82-1/4-20x50-A-B	1/4 - 20	3.23	1.97	0.77	0.89	0.12	0.15	0.79	0.98	0.04	0.79	0.28
GN.93195851	GN 927-82-1/4-20x60-A-B	1/4 - 20	3.23	2.36	0.77	0.89	0.12	0.15	0.79	0.98	0.04	0.79	0.26
GN.93566551	GN 927-82-5/16-18x20-A-B	5/16 - 18	3.23	0.79	0.77	0.89	0.12	0.15	0.79	0.98	0.04	0.79	0.24
GN.93196151	GN 927-82-5/16-18x25-A-B	5/16 - 18	3.23	0.98	0.77	0.89	0.12	0.15	0.79	0.98	0.04	0.79	0.27
GN.93196351	GN 927-82-5/16-18x30-A-B	5/16 - 18	3.23	1.18	0.77	0.89	0.12	0.15	0.79	0.98	0.04	0.79	0.26
GN.93196451	GN 927-82-5/16-18x35-A-B	5/16 - 18	3.23	1.38	0.77	0.89	0.12	0.15	0.79	0.98	0.04	0.79	0.28
GN.93196452	GN 927-82-5/16-18x40-A-B	5/16 - 18	3.23	1.57	0.77	0.89	0.12	0.15	0.79	0.98	0.04	0.79	0.28
GN.93196251	GN 927-82-5/16-18x50-A-B	5/16 - 18	3.23	1.97	0.77	0.89	0.12	0.15	0.79	0.98	0.04	0.79	0.29
GN.93196651	GN 927-82-5/16-18x60-A-B	5/16 - 18	3.23	2.36	0.77	0.89	0.12	0.15	0.79	0.98	0.04	0.79	0.30
GN.93190351	GN 927-101-5/16-18x20-A-B	5/16 - 18	3.98	0.79	1.00	1.16	0.16	0.19	1.02	1.18	0.06	0.98	0.49
GN.93567151	GN 927-101-5/16-18x25-A-B	5/16 - 18	3.98	0.98	1.00	1.16	0.16	0.19	1.02	1.18	0.06	0.98	0.50
GN.93567152	GN 927-101-5/16-18x30-A-B	5/16 - 18	3.98	1.18	1.00	1.16	0.16	0.19	1.02	1.18	0.06	0.98	0.50
GN.93567551	GN 927-101-5/16-18x35-A-B	5/16 - 18	3.98	1.38	1.00	1.16	0.16	0.19	1.02	1.18	0.06	0.98	0.50
GN.93190751	GN 927-101-5/16-18x40-A-B	5/16 - 18	3.98	1.57	1.00	1.16	0.16	0.19	1.02	1.18	0.06	0.98	0.51
GN.93190951	GN 927-101-5/16-18x50-A-B	5/16 - 18	3.98	1.97	1.00	1.16	0.16	0.19	1.02	1.18	0.06	0.98	0.51
GN.93192151	GN 927-101-5/16-18x60-A-B	5/16 - 18	3.98	2.36	1.00	1.16	0.16	0.19	1.02	1.18	0.06	0.98	0.52
GN.93191151	GN 927-101-3/8-16x20-A-B	3/8 - 16	3.98	0.79	1.00	1.16	0.16	0.19	1.02	1.18	0.06	0.98	0.51
GN.93567951	GN 927-101-3/8-16x25-A-B	3/8 - 16	3.98	0.98	1.00	1.16	0.16	0.19	1.02	1.18	0.06	0.98	0.51
GN.93191351	GN 927-101-3/8-16x30-A-B	3/8 - 16	3.98	1.18	1.00	1.16	0.16	0.19	1.02	1.18	0.06	0.98	0.51
GN.93568351	GN 927-101-3/8-16x35-A-B	3/8 - 16	3.98	1.38	1.00	1.16	0.16	0.19	1.02	1.18	0.06	0.98	0.52
GN.93191551	GN 927-101-3/8-16x40-A-B	3/8 - 16	3.98	1.57	1.00	1.16	0.16	0.19	1.02	1.18	0.06	0.98	0.52
GN.93191751	GN 927-101-3/8-16x50-A-B	3/8 - 16	3.98	1.97	1.00	1.16	0.16	0.19	1.02	1.18	0.06	0.98	0.54
GN.93191951	GN 927-101-3/8-16x60-A-B	3/8 - 16	3.98	2.36	1.00	1.16	0.16	0.19	1.02	1.18	0.06	0.98	0.53

* In clamping position

** Stroke at 90° rotation of the lever




GN 927-A (d2 - l2)

INCH

Code	Description	d ₂	l ₁	l ₂ *	l _{3 min} *	l _{3 max} *	l ₄	l ₅ *	d ₃	d ₄	h**	b	△
GN.93193894	GN 927-44-8-32x12-A-O	8 - 32	1.73	0.47	0.52	0.60	0.08	0.09	0.47	0.59	0.02	0.47	0.05
GN.93193895	GN 927-44-8-32x16-A-O	8 - 32	1.73	0.63	0.52	0.60	0.08	0.09	0.47	0.59	0.02	0.47	0.06
GN.93193896	GN 927-44-8-32x20-A-O	8 - 32	1.73	0.79	0.52	0.60	0.08	0.09	0.47	0.59	0.02	0.47	0.06
GN.93193897	GN 927-44-8-32x25-A-O	8 - 32	1.73	0.98	0.52	0.60	0.08	0.09	0.47	0.59	0.02	0.47	0.06
GN.93193898	GN 927-44-8-32x30-A-O	8 - 32	1.73	1.18	0.52	0.60	0.08	0.09	0.47	0.59	0.02	0.47	0.06
GN.93193899	GN 927-44-10-32x12-A-O	10 - 32	1.73	0.47	0.52	0.60	0.08	0.09	0.47	0.59	0.02	0.47	0.06
GN.93193900	GN 927-44-10-32x16-A-O	10 - 32	1.73	0.63	0.52	0.60	0.08	0.09	0.47	0.59	0.02	0.47	0.06
GN.93193901	GN 927-44-10-32x20-A-O	10 - 32	1.73	0.79	0.52	0.60	0.08	0.09	0.47	0.59	0.02	0.47	0.06
GN.93193902	GN 927-44-10-32x25-A-O	10 - 32	1.73	0.98	0.52	0.60	0.08	0.09	0.47	0.59	0.02	0.47	0.06
GN.93193903	GN 927-44-10-32x30-A-O	10 - 32	1.73	1.18	0.52	0.60	0.08	0.09	0.47	0.59	0.02	0.47	0.06
GN.93193904	GN 927-44-10-32x35-A-O	10 - 32	1.73	1.38	0.52	0.60	0.08	0.09	0.47	0.59	0.02	0.47	0.06
GN.93193905	GN 927-44-10-32x40-A-O	10 - 32	1.73	1.57	0.52	0.60	0.08	0.09	0.47	0.59	0.02	0.47	0.06
GN.93193906	GN 927-63-10-32x16-A-O	10 - 32	2.48	0.63	0.64	0.74	0.10	0.12	0.63	0.75	0.03	0.63	0.13
GN.93193907	GN 927-63-10-32x20-A-O	10 - 32	2.48	0.79	0.64	0.74	0.10	0.12	0.63	0.75	0.03	0.63	0.13
GN.93193908	GN 927-63-10-32x25-A-O	10 - 32	2.48	0.98	0.64	0.74	0.10	0.12	0.63	0.75	0.03	0.63	0.14
GN.93193909	GN 927-63-10-32x30-A-O	10 - 32	2.48	1.18	0.64	0.74	0.10	0.12	0.63	0.75	0.03	0.63	0.14
GN.93193910	GN 927-63-10-32x35-A-O	10 - 32	2.48	1.38	0.64	0.74	0.10	0.12	0.63	0.75	0.03	0.63	0.14
GN.93193911	GN 927-63-10-32x40-A-O	10 - 32	2.48	1.57	0.64	0.74	0.10	0.12	0.63	0.75	0.03	0.63	0.14
GN.93193912	GN 927-63-10-32x50-A-O	10 - 32	2.48	1.97	0.64	0.74	0.10	0.12	0.63	0.75	0.03	0.63	0.14
GN.93193913	GN 927-63-1/4-20x16-A-O	1/4 - 20	2.48	0.63	0.64	0.74	0.10	0.12	0.63	0.75	0.03	0.63	0.13
GN.93193914	GN 927-63-1/4-20x20-A-O	1/4 - 20	2.48	0.79	0.64	0.74	0.10	0.12	0.63	0.75	0.03	0.63	0.13
GN.93193915	GN 927-63-1/4-20x25-A-O	1/4 - 20	2.48	0.98	0.64	0.74	0.10	0.12	0.63	0.75	0.03	0.63	0.14
GN.93193916	GN 927-63-1/4-20x30-A-O	1/4 - 20	2.48	1.18	0.64	0.74	0.10	0.12	0.63	0.75	0.03	0.63	0.14
GN.93193917	GN 927-63-1/4-20x35-A-O	1/4 - 20	2.48	1.38	0.64	0.74	0.10	0.12	0.63	0.75	0.03	0.63	0.14
GN.93193918	GN 927-63-1/4-20x40-A-O	1/4 - 20	2.48	1.57	0.64	0.74	0.10	0.12	0.63	0.75	0.03	0.63	0.15
GN.93193919	GN 927-63-1/4-20x50-A-O	1/4 - 20	2.48	1.97	0.64	0.74	0.10	0.12	0.63	0.75	0.03	0.63	0.15
GN.93193920	GN 927-82-1/4-20x20-A-O	1/4 - 20	3.23	0.79	0.77	0.89	0.12	0.15	0.79	0.98	0.04	0.79	0.26
GN.93193921	GN 927-82-1/4-20x25-A-O	1/4 - 20	3.23	0.98	0.77	0.89	0.12	0.15	0.79	0.98	0.04	0.79	0.26
GN.93193922	GN 927-82-1/4-20x30-A-O	1/4 - 20	3.23	1.18	0.77	0.89	0.12	0.15	0.79	0.98	0.04	0.79	0.26
GN.93193923	GN 927-82-1/4-20x35-A-O	1/4 - 20	3.23	1.38	0.77	0.89	0.12	0.15	0.79	0.98	0.04	0.79	0.26
GN.93193924	GN 927-82-1/4-20x40-A-O	1/4 - 20	3.23	1.57	0.77	0.89	0.12	0.15	0.79	0.98	0.04	0.79	0.26
GN.93193925	GN 927-82-1/4-20x50-A-O	1/4 - 20	3.23	1.97	0.77	0.89	0.12	0.15	0.79	0.98	0.04	0.79	0.26
GN.93193926	GN 927-82-1/4-20x60-A-O	1/4 - 20	3.23	2.36	0.77	0.89	0.12	0.15	0.79	0.98	0.04	0.79	0.26
GN.93193927	GN 927-82-5/16-18x20-A-O	5/16 - 18	3.23	0.79	0.77	0.89	0.12	0.15	0.79	0.98	0.04	0.79	0.27
GN.93193928	GN 927-82-5/16-18x25-A-O	5/16 - 18	3.23	0.98	0.77	0.89	0.12	0.15	0.79	0.98	0.04	0.79	0.27
GN.93193929	GN 927-82-5/16-18x30-A-O	5/16 - 18	3.23	1.18	0.77	0.89	0.12	0.15	0.79	0.98	0.04	0.79	0.27
GN.93193930	GN 927-82-5/16-18x35-A-O	5/16 - 18	3.23	1.38	0.77	0.89	0.12	0.15	0.79	0.98	0.04	0.79	0.28
GN.93196551	GN 927-82-5/16-18x40-A-O	5/16 - 18	3.23	1.57	0.77	0.89	0.12	0.15	0.79	0.98	0.04	0.79	0.28
GN.93196552	GN 927-82-5/16-18x50-A-O	5/16 - 18	3.23	1.97	0.77	0.89	0.12	0.15	0.79	0.98	0.04	0.79	0.28
GN.93196553	GN 927-82-5/16-18x60-A-O	5/16 - 18	3.23	2.36	0.77	0.89	0.12	0.15	0.79	0.98	0.04	0.79	0.30
GN.93196554	GN 927-101-5/16-18x20-A-O	5/16 - 18	3.98	0.79	1.00	1.16	0.16	0.19	1.02	1.18	0.06	0.98	0.49
GN.93196555	GN 927-101-5/16-18x25-A-O	5/16 - 18	3.98	0.98	1.00	1.16	0.16	0.19	1.02	1.18	0.06	0.98	0.50
GN.93196556	GN 927-101-5/16-18x30-A-O	5/16 - 18	3.98	1.18	1.00	1.16	0.16	0.19	1.02	1.18	0.06	0.98	0.50
GN.93196557	GN 927-101-5/16-18x35-A-O	5/16 - 18	3.98	1.38	1.00	1.16	0.16	0.19	1.02	1.18	0.06	0.98	0.50
GN.93196558	GN 927-101-5/16-18x40-A-O	5/16 - 18	3.98	1.57	1.00	1.16	0.16	0.19	1.02	1.18	0.06	0.98	0.51
GN.93196559	GN 927-101-5/16-18x50-A-O	5/16 - 18	3.98	1.97	1.00	1.16	0.16	0.19	1.02	1.18	0.06	0.98	0.51
GN.93196560	GN 927-101-5/16-18x60-A-O	5/16 - 18	3.98	2.36	1.00	1.16	0.16	0.19	1.02	1.18	0.06	0.98	0.52
GN.93191254	GN 927-101-3/8-16x20-A-O	3/8 - 16	3.98	0.79	1.00	1.16	0.16	0.19	1.02	1.18	0.06	0.98	0.51
GN.93191252	GN 927-101-3/8-16x25-A-O	3/8 - 16	3.98	0.98	1.00	1.16	0.16	0.19	1.02	1.18	0.06	0.98	0.51
GN.93191253	GN 927-101-3/8-16x30-A-O	3/8 - 16	3.98	1.18	1.00	1.16	0.16	0.19	1.02	1.18	0.06	0.98	0.51
GN.93191254	GN 927-101-3/8-16x35-A-O	3/8 - 16	3.98	1.38	1.00	1.16	0.16	0.19	1.02	1.18	0.06	0.98	0.52
GN.93191255	GN 927-101-3/8-16x40-A-O	3/8 - 16	3.98	1.57	1.00	1.16	0.16	0.19	1.02	1.18	0.06	0.98	0.52
GN.93191256	GN 927-101-3/8-16x50-A-O	3/8 - 16	3.98	1.97	1.00	1.16	0.16	0.19	1.02	1.18	0.06	0.98	0.54
GN.93191257	GN 927-101-3/8-16x60-A-O	3/8 - 16	3.98	2.36	1.00	1.16	0.16	0.19	1.02	1.18	0.06	0.98	0.55

* In clamping position

** Stroke at 90° rotation of the lever





GN 927-A (d2 - l2)

INCH

Code	Description	d ₂	l ₁	l ₂ *	l _{3 min} *	l _{3 max} *	l ₄	l ₅ *	d ₃	d ₄	h**	b	Δ
GN.93563432	GN 927-44-8-32x12-A-R	8 - 32	1.73	0.47	0.52	0.60	0.08	0.09	0.47	0.59	0.02	0.47	0.06
GN.93563433	GN 927-44-8-32x16-A-R	8 - 32	1.73	0.63	0.52	0.60	0.08	0.09	0.47	0.59	0.02	0.47	0.06
GN.93563434	GN 927-44-8-32x20-A-R	8 - 32	1.73	0.79	0.52	0.60	0.08	0.09	0.47	0.59	0.02	0.47	0.06
GN.93563435	GN 927-44-8-32x25-A-R	8 - 32	1.73	0.98	0.52	0.60	0.08	0.09	0.47	0.59	0.02	0.47	0.06
GN.93563436	GN 927-44-8-32x30-A-R	8 - 32	1.73	1.18	0.52	0.60	0.08	0.09	0.47	0.59	0.02	0.47	0.07
GN.93563437	GN 927-44-10-32x12-A-R	10 - 32	1.73	0.47	0.52	0.60	0.08	0.09	0.47	0.59	0.02	0.47	0.06
GN.93563438	GN 927-44-10-32x16-A-R	10 - 32	1.73	0.63	0.52	0.60	0.08	0.09	0.47	0.59	0.02	0.47	0.06
GN.93563439	GN 927-44-10-32x20-A-R	10 - 32	1.73	0.79	0.52	0.60	0.08	0.09	0.47	0.59	0.02	0.47	0.07
GN.93563440	GN 927-44-10-32x25-A-R	10 - 32	1.73	0.98	0.52	0.60	0.08	0.09	0.47	0.59	0.02	0.47	0.07
GN.93563441	GN 927-44-10-32x30-A-R	10 - 32	1.73	1.18	0.52	0.60	0.08	0.09	0.47	0.59	0.02	0.47	0.07
GN.93563442	GN 927-44-10-32x35-A-R	10 - 32	1.73	1.38	0.52	0.60	0.08	0.09	0.47	0.59	0.02	0.47	0.07
GN.93563443	GN 927-44-10-32x40-A-R	10 - 32	1.73	1.57	0.52	0.60	0.08	0.09	0.47	0.59	0.02	0.47	0.07
GN.93563444	GN 927-63-10-32x16-A-R	10 - 32	2.48	0.63	0.64	0.74	0.10	0.12	0.63	0.75	0.03	0.63	0.13
GN.93563444	GN 927-63-10-32x20-A-R	10 - 32	2.48	0.79	0.64	0.74	0.10	0.12	0.63	0.75	0.03	0.63	0.13
GN.93563445	GN 927-63-10-32x25-A-R	10 - 32	2.48	0.98	0.64	0.74	0.10	0.12	0.63	0.75	0.03	0.63	0.14
GN.93563446	GN 927-63-10-32x30-A-R	10 - 32	2.48	1.18	0.64	0.74	0.10	0.12	0.63	0.75	0.03	0.63	0.14
GN.93563447	GN 927-63-10-32x35-A-R	10 - 32	2.48	1.38	0.64	0.74	0.10	0.12	0.63	0.75	0.03	0.63	0.14
GN.93563448	GN 927-63-10-32x40-A-R	10 - 32	2.48	1.57	0.64	0.74	0.10	0.12	0.63	0.75	0.03	0.63	0.14
GN.93563449	GN 927-63-1/4-20x16-A-R	1/4 - 20	2.48	0.63	0.64	0.74	0.10	0.12	0.63	0.75	0.03	0.63	0.13
GN.93563450	GN 927-63-1/4-20x20-A-R	1/4 - 20	2.48	0.79	0.64	0.74	0.10	0.12	0.63	0.75	0.03	0.63	0.13
GN.93563451	GN 927-63-1/4-20x25-A-R	1/4 - 20	2.48	0.98	0.64	0.74	0.10	0.12	0.63	0.75	0.03	0.63	0.14
GN.93563452	GN 927-63-1/4-20x30-A-R	1/4 - 20	2.48	1.18	0.64	0.74	0.10	0.12	0.63	0.75	0.03	0.63	0.14
GN.93563453	GN 927-63-1/4-20x35-A-R	1/4 - 20	2.48	1.38	0.64	0.74	0.10	0.12	0.63	0.75	0.03	0.63	0.14
GN.93563454	GN 927-63-1/4-20x40-A-R	1/4 - 20	2.48	1.57	0.64	0.74	0.10	0.12	0.63	0.75	0.03	0.63	0.15
GN.93563455	GN 927-63-1/4-20x50-A-R	1/4 - 20	2.48	1.97	0.64	0.74	0.10	0.12	0.63	0.75	0.03	0.63	0.15
GN.93563457	GN 927-82-1/4-20x20-A-R	1/4 - 20	3.23	0.79	0.77	0.89	0.12	0.15	0.79	0.98	0.04	0.79	0.26
GN.93563458	GN 927-82-1/4-20x25-A-R	1/4 - 20	3.23	0.98	0.77	0.89	0.12	0.15	0.79	0.98	0.04	0.79	0.26
GN.93563459	GN 927-82-1/4-20x30-A-R	1/4 - 20	3.23	1.18	0.77	0.89	0.12	0.15	0.79	0.98	0.04	0.79	0.26
GN.93563460	GN 927-82-1/4-20x35-A-R	1/4 - 20	3.23	1.38	0.77	0.89	0.12	0.15	0.79	0.98	0.04	0.79	0.26
GN.93563461	GN 927-82-1/4-20x40-A-R	1/4 - 20	3.23	1.57	0.77	0.89	0.12	0.15	0.79	0.98	0.04	0.79	0.26
GN.93563462	GN 927-82-1/4-20x50-A-R	1/4 - 20	3.23	1.97	0.77	0.89	0.12	0.15	0.79	0.98	0.04	0.79	0.26
GN.93563463	GN 927-82-1/4-20x60-A-R	1/4 - 20	3.23	2.36	0.77	0.89	0.12	0.15	0.79	0.98	0.04	0.79	0.26
GN.93563464	GN 927-82-5/16-18x20-A-R	5/16 - 18	3.23	0.79	0.77	0.89	0.12	0.15	0.79	0.98	0.04	0.79	0.27
GN.93563465	GN 927-82-5/16-18x25-A-R	5/16 - 18	3.23	0.98	0.77	0.89	0.12	0.15	0.79	0.98	0.04	0.79	0.27
GN.93563466	GN 927-82-5/16-18x30-A-R	5/16 - 18	3.23	1.18	0.77	0.89	0.12	0.15	0.79	0.98	0.04	0.79	0.26
GN.93563467	GN 927-82-5/16-18x35-A-R	5/16 - 18	3.23	1.38	0.77	0.89	0.12	0.15	0.79	0.98	0.04	0.79	0.28
GN.93563468	GN 927-82-5/16-18x40-A-R	5/16 - 18	3.23	1.57	0.77	0.89	0.12	0.15	0.79	0.98	0.04	0.79	0.28
GN.93563469	GN 927-82-5/16-18x50-A-R	5/16 - 18	3.23	1.97	0.77	0.89	0.12	0.15	0.79	0.98	0.04	0.79	0.28
GN.93563470	GN 927-82-5/16-18x60-A-R	5/16 - 18	3.23	2.36	0.77	0.89	0.12	0.15	0.79	0.98	0.04	0.79	0.30
GN.93190299	GN 927-101-5/16-18x20-A-R	5/16 - 18	3.98	0.79	1.00	1.16	0.16	0.19	1.02	1.18	0.06	0.98	0.49
GN.93190300	GN 927-101-5/16-18x25-A-R	5/16 - 18	3.98	0.98	1.00	1.16	0.16	0.19	1.02	1.18	0.06	0.98	0.50
GN.93190301	GN 927-101-5/16-18x30-A-R	5/16 - 18	3.98	1.18	1.00	1.16	0.16	0.19	1.02	1.18	0.06	0.98	0.50
GN.93190302	GN 927-101-5/16-18x35-A-R	5/16 - 18	3.98	1.38	1.00	1.16	0.16	0.19	1.02	1.18	0.06	0.98	0.50
GN.93190303	GN 927-101-5/16-18x40-A-R	5/16 - 18	3.98	1.57	1.00	1.16	0.16	0.19	1.02	1.18	0.06	0.98	0.51
GN.93190304	GN 927-101-5/16-18x50-A-R	5/16 - 18	3.98	1.97	1.00	1.16	0.16	0.19	1.02	1.18	0.06	0.98	0.51
GN.93192091	GN 927-101-5/16-18x60-A-R	5/16 - 18	3.98	2.36	1.00	1.16	0.16	0.19	1.02	1.18	0.06	0.98	0.52
GN.93192092	GN 927-101-3/8-16x20-A-R	3/8 - 16	3.98	0.79	1.00	1.16	0.16	0.19	1.02	1.18	0.06	0.98	0.51
GN.93192093	GN 927-101-3/8-16x25-A-R	3/8 - 16	3.98	0.98	1.00	1.16	0.16	0.19	1.02	1.18	0.06	0.98	0.51
GN.93192094	GN 927-101-3/8-16x30-A-R	3/8 - 16	3.98	1.18	1.00	1.16	0.16	0.19	1.02	1.18	0.06	0.98	0.52
GN.93192095	GN 927-101-3/8-16x35-A-R	3/8 - 16	3.98	1.38	1.00	1.16	0.16	0.19	1.02	1.18	0.06	0.98	0.52
GN.93192096	GN 927-101-3/8-16x40-A-R	3/8 - 16	3.98	1.57	1.00	1.16	0.16	0.19	1.02	1.18	0.06	0.98	0.52
GN.93192097	GN 927-101-3/8-16x50-A-R	3/8 - 16	3.98	1.97	1.00	1.16	0.16	0.19	1.02	1.18	0.06	0.98	0.54
GN.93192023	GN 927-101-3/8-16x60-A-R	3/8 - 16	3.98	2.36	1.00	1.16	0.16	0.19	1.02	1.18	0.06	0.98	0.55

* In clamping position

** Stroke at 90° rotation of the lever




INCH

GN 927-A (d2 - I2)

Code	Description	d ₂	l ₁	l ₂ *	l _{3 min} *	l _{3 max} *	l ₄	l ₅ *	d ₃	d ₄	h**	b	△
GN.93190551	GN 927-44-8-32x12-A-S	8 - 32	1.73	0.47	0.52	0.60	0.08	0.09	0.47	0.59	0.02	0.47	0.06
GN.93190552	GN 927-44-8-32x16-A-S	8 - 32	1.73	0.63	0.52	0.60	0.08	0.09	0.47	0.59	0.02	0.47	0.06
GN.93190553	GN 927-44-8-32x20-A-S	8 - 32	1.73	0.79	0.52	0.60	0.08	0.09	0.47	0.59	0.02	0.47	0.06
GN.93190554	GN 927-44-8-32x25-A-S	8 - 32	1.73	0.98	0.52	0.60	0.08	0.09	0.47	0.59	0.02	0.47	0.06
GN.93190555	GN 927-44-8-32x30-A-S	8 - 32	1.73	1.18	0.52	0.60	0.08	0.09	0.47	0.59	0.02	0.47	0.07
GN.93190556	GN 927-44-10-32x12-A-S	10 - 32	1.73	0.47	0.52	0.60	0.08	0.09	0.47	0.59	0.02	0.47	0.06
GN.93190557	GN 927-44-10-32x16-A-S	10 - 32	1.73	0.63	0.52	0.60	0.08	0.09	0.47	0.59	0.02	0.47	0.06
GN.93190558	GN 927-44-10-32x20-A-S	10 - 32	1.73	0.79	0.52	0.60	0.08	0.09	0.47	0.59	0.02	0.47	0.07
GN.93190559	GN 927-44-10-32x25-A-S	10 - 32	1.73	0.98	0.52	0.60	0.08	0.09	0.47	0.59	0.02	0.47	0.07
GN.93190560	GN 927-44-10-32x30-A-S	10 - 32	1.73	1.18	0.52	0.60	0.08	0.09	0.47	0.59	0.02	0.47	0.07
GN.93190561	GN 927-44-10-32x35-A-S	10 - 32	1.73	1.38	0.52	0.60	0.08	0.09	0.47	0.59	0.02	0.47	0.07
GN.93190562	GN 927-44-10-32x40-A-S	10 - 32	1.73	1.57	0.52	0.60	0.08	0.09	0.47	0.59	0.02	0.47	0.07
GN.93190563	GN 927-63-10-32x16-A-S	10 - 32	2.48	0.63	0.64	0.74	0.10	0.12	0.63	0.75	0.03	0.63	0.13
GN.93190564	GN 927-63-10-32x20-A-S	10 - 32	2.48	0.79	0.64	0.74	0.10	0.12	0.63	0.75	0.03	0.63	0.13
GN.93190565	GN 927-63-10-32x25-A-S	10 - 32	2.48	0.98	0.64	0.74	0.10	0.12	0.63	0.75	0.03	0.63	0.14
GN.93190566	GN 927-63-10-32x30-A-S	10 - 32	2.48	1.18	0.64	0.74	0.10	0.12	0.63	0.75	0.03	0.63	0.14
GN.93190567	GN 927-63-10-32x35-A-S	10 - 32	2.48	1.38	0.64	0.74	0.10	0.12	0.63	0.75	0.03	0.63	0.14
GN.93190568	GN 927-63-10-32x40-A-S	10 - 32	2.48	1.57	0.64	0.74	0.10	0.12	0.63	0.75	0.03	0.63	0.14
GN.93190569	GN 927-63-10-32x50-A-S	10 - 32	2.48	1.97	0.64	0.74	0.10	0.12	0.63	0.75	0.03	0.63	0.14
GN.93190570	GN 927-63-1/4-20x16-A-S	1/4 - 20	2.48	0.63	0.64	0.74	0.10	0.12	0.63	0.75	0.03	0.63	0.13
GN.93190571	GN 927-63-1/4-20x20-A-S	1/4 - 20	2.48	0.79	0.64	0.74	0.10	0.12	0.63	0.75	0.03	0.63	0.13
GN.93190572	GN 927-63-1/4-20x25-A-S	1/4 - 20	2.48	0.98	0.64	0.74	0.10	0.12	0.63	0.75	0.03	0.63	0.14
GN.93190573	GN 927-63-1/4-20x30-A-S	1/4 - 20	2.48	1.18	0.64	0.74	0.10	0.12	0.63	0.75	0.03	0.63	0.14
GN.93190574	GN 927-63-1/4-20x35-A-S	1/4 - 20	2.48	1.38	0.64	0.74	0.10	0.12	0.63	0.75	0.03	0.63	0.14
GN.93190575	GN 927-63-1/4-20x40-A-S	1/4 - 20	2.48	1.57	0.64	0.74	0.10	0.12	0.63	0.75	0.03	0.63	0.15
GN.93190576	GN 927-63-1/4-20x50-A-S	1/4 - 20	2.48	1.97	0.64	0.74	0.10	0.12	0.63	0.75	0.03	0.63	0.15
GN.93190577	GN 927-82-1/4-20x20-A-S	1/4 - 20	3.23	0.79	0.77	0.89	0.12	0.15	0.79	0.98	0.04	0.79	0.26
GN.93190578	GN 927-82-1/4-20x25-A-S	1/4 - 20	3.23	0.98	0.77	0.89	0.12	0.15	0.79	0.98	0.04	0.79	0.26
GN.93190579	GN 927-82-1/4-20x30-A-S	1/4 - 20	3.23	1.18	0.77	0.89	0.12	0.15	0.79	0.98	0.04	0.79	0.26
GN.93190580	GN 927-82-1/4-20x35-A-S	1/4 - 20	3.23	1.38	0.77	0.89	0.12	0.15	0.79	0.98	0.04	0.79	0.26
GN.93190581	GN 927-82-1/4-20x40-A-S	1/4 - 20	3.23	1.57	0.77	0.89	0.12	0.15	0.79	0.98	0.04	0.79	0.26
GN.93190582	GN 927-82-1/4-20x50-A-S	1/4 - 20	3.23	1.97	0.77	0.89	0.12	0.15	0.79	0.98	0.04	0.79	0.26
GN.93190583	GN 927-82-1/4-20x60-A-S	1/4 - 20	3.23	2.36	0.77	0.89	0.12	0.15	0.79	0.98	0.04	0.79	0.26
GN.93190584	GN 927-82-5/16-18x20-A-S	5/16 - 18	3.23	0.79	0.77	0.89	0.12	0.15	0.79	0.98	0.04	0.79	0.27
GN.93190585	GN 927-82-5/16-18x25-A-S	5/16 - 18	3.23	0.98	0.77	0.89	0.12	0.15	0.79	0.98	0.04	0.79	0.27
GN.93190586	GN 927-82-5/16-18x30-A-S	5/16 - 18	3.23	1.18	0.77	0.89	0.12	0.15	0.79	0.98	0.04	0.79	0.26
GN.93190587	GN 927-82-5/16-18x35-A-S	5/16 - 18	3.23	1.38	0.77	0.89	0.12	0.15	0.79	0.98	0.04	0.79	0.28
GN.93190588	GN 927-82-5/16-18x40-A-S	5/16 - 18	3.23	1.57	0.77	0.89	0.12	0.15	0.79	0.98	0.04	0.79	0.28
GN.93190589	GN 927-82-5/16-18x50-A-S	5/16 - 18	3.23	1.97	0.77	0.89	0.12	0.15	0.79	0.98	0.04	0.79	0.28
GN.93190590	GN 927-82-5/16-18x60-A-S	5/16 - 18	3.23	2.36	0.77	0.89	0.12	0.15	0.79	0.98	0.04	0.79	0.30
GN.93190591	GN 927-101-5/16-18x20-A-S	5/16 - 18	3.98	0.79	1.00	1.16	0.16	0.19	1.02	1.18	0.06	0.98	0.49
GN.93190592	GN 927-101-5/16-18x25-A-S	5/16 - 18	3.98	0.98	1.00	1.16	0.16	0.19	1.02	1.18	0.06	0.98	0.50
GN.93190593	GN 927-101-5/16-18x30-A-S	5/16 - 18	3.98	1.18	1.00	1.16	0.16	0.19	1.02	1.18	0.06	0.98	0.50
GN.93190594	GN 927-101-5/16-18x35-A-S	5/16 - 18	3.98	1.38	1.00	1.16	0.16	0.19	1.02	1.18	0.06	0.98	0.50
GN.93190595	GN 927-101-5/16-18x40-A-S	5/16 - 18	3.98	1.57	1.00	1.16	0.16	0.19	1.02	1.18	0.06	0.98	0.51
GN.93190596	GN 927-101-5/16-18x50-A-S	5/16 - 18	3.98	1.97	1.00	1.16	0.16	0.19	1.02	1.18	0.06	0.98	0.51
GN.93190597	GN 927-101-5/16-18x60-A-S	5/16 - 18	3.98	2.36	1.00	1.16	0.16	0.19	1.02	1.18	0.06	0.98	0.52
GN.93190598	GN 927-101-3/8-16x20-A-S	3/8 - 16	3.98	0.79	1.00	1.16	0.16	0.19	1.02	1.18	0.06	0.98	0.51
GN.93190599	GN 927-101-3/8-16x25-A-S	3/8 - 16	3.98	0.98	1.00	1.16	0.16	0.19	1.02	1.18	0.06	0.98	0.51
GN.93190600	GN 927-101-3/8-16x30-A-S	3/8 - 16	3.98	1.18	1.00	1.16	0.16	0.19	1.02	1.18	0.06	0.98	0.52
GN.93190601	GN 927-101-3/8-16x35-A-S	3/8 - 16	3.98	1.38	1.00	1.16	0.16	0.19	1.02	1.18	0.06	0.98	0.52
GN.93190602	GN 927-101-3/8-16x40-A-S	3/8 - 16	3.98	1.57	1.00	1.16	0.16	0.19	1.02	1.18	0.06	0.98	0.52
GN.93190603	GN 927-101-3/8-16x50-A-S	3/8 - 16	3.98	1.97	1.00	1.16	0.16	0.19	1.02	1.18	0.06	0.98	0.54
GN.93190604	GN 927-101-3/8-16x60-A-S	3/8 - 16	3.98	2.36	1.00	1.16	0.16	0.19	1.02	1.18	0.06	0.98	0.55

* In clamping position

** Stroke at 90° rotation of the lever



GN 927-B (d2 - I2)

INCH

Code	Description	d ₂	l ₁	l ₂ *	l ₅ *	l ₆ *	d ₃	d ₅	h**	b	Δ
GN.93560751	GN 927-44-8-32x12-B-B	8 - 32	1.73	0.47	0.52	0.09	0.47	0.55	0.02	0.47	0.05
GN.93560951	GN 927-44-8-32x16-B-B	8 - 32	1.73	0.63	0.52	0.09	0.47	0.55	0.02	0.47	0.06
GN.93561151	GN 927-44-8-32x20-B-B	8 - 32	1.73	0.79	0.52	0.09	0.47	0.55	0.02	0.47	0.06
GN.93561351	GN 927-44-8-32x25-B-B	8 - 32	1.73	0.98	0.52	0.09	0.47	0.55	0.02	0.47	0.06
GN.93561551	GN 927-44-8-32x30-B-B	8 - 32	1.73	1.18	0.52	0.09	0.47	0.55	0.02	0.47	0.06
GN.93562751	GN 927-44-10-32x12-B-B	10 - 32	1.73	0.47	0.52	0.09	0.47	0.55	0.02	0.47	0.06
GN.93562951	GN 927-44-10-32x16-B-B	10 - 32	1.73	0.63	0.52	0.09	0.47	0.55	0.02	0.47	0.06
GN.93563151	GN 927-44-10-32x20-B-B	10 - 32	1.73	0.79	0.52	0.09	0.47	0.55	0.02	0.47	0.06
GN.93563351	GN 927-44-10-32x25-B-B	10 - 32	1.73	0.98	0.52	0.09	0.47	0.55	0.02	0.47	0.06
GN.93563551	GN 927-44-10-32x30-B-B	10 - 32	1.73	1.18	0.52	0.09	0.47	0.55	0.02	0.47	0.06
GN.93563751	GN 927-44-10-32x35-B-B	10 - 32	1.73	1.38	0.52	0.09	0.47	0.55	0.02	0.47	0.06
GN.93563951	GN 927-44-10-32x40-B-B	10 - 32	1.73	1.57	0.52	0.09	0.47	0.55	0.02	0.47	0.06
GN.93565351	GN 927-63-10-32x16-B-B	10 - 32	2.48	0.63	0.64	0.12	0.63	0.73	0.03	0.63	0.12
GN.93196751	GN 927-63-10-32x20-B-B	10 - 32	2.48	0.79	0.64	0.12	0.63	0.73	0.03	0.63	0.12
GN.93196851	GN 927-63-10-32x25-B-B	10 - 32	2.48	0.98	0.64	0.12	0.63	0.73	0.03	0.63	0.12
GN.93196951	GN 927-63-10-32x30-B-B	10 - 32	2.48	1.18	0.64	0.12	0.63	0.73	0.03	0.63	0.12
GN.93197051	GN 927-63-10-32x35-B-B	10 - 32	2.48	1.38	0.64	0.12	0.63	0.73	0.03	0.63	0.12
GN.93197751	GN 927-63-10-32x40-B-B	10 - 32	2.48	1.57	0.64	0.12	0.63	0.73	0.03	0.63	0.12
GN.93197851	GN 927-63-1/4-20x16-B-B	1/4 - 20	2.48	0.63	0.64	0.12	0.63	0.73	0.03	0.63	0.12
GN.93565751	GN 927-63-1/4-20x20-B-B	1/4 - 20	2.48	0.79	0.64	0.12	0.63	0.73	0.03	0.63	0.12
GN.93197151	GN 927-63-1/4-20x25-B-B	1/4 - 20	2.48	0.98	0.64	0.12	0.63	0.73	0.03	0.63	0.12
GN.93197351	GN 927-63-1/4-20x30-B-B	1/4 - 20	2.48	1.18	0.64	0.12	0.63	0.73	0.03	0.63	0.13
GN.93197451	GN 927-63-1/4-20x35-B-B	1/4 - 20	2.48	1.38	0.64	0.12	0.63	0.73	0.03	0.63	0.13
GN.93197551	GN 927-63-1/4-20x40-B-B	1/4 - 20	2.48	1.57	0.64	0.12	0.63	0.73	0.03	0.63	0.13
GN.93197651	GN 927-63-1/4-20x50-B-B	1/4 - 20	2.48	1.97	0.64	0.12	0.63	0.73	0.03	0.63	0.13
GN.93566351	GN 927-82-1/4-20x20-B-B	1/4 - 20	3.23	0.79	0.77	0.15	0.79	0.89	0.04	0.79	0.27
GN.93198751	GN 927-82-1/4-20x25-B-B	1/4 - 20	3.23	0.98	0.77	0.15	0.79	0.89	0.04	0.79	0.27
GN.93198851	GN 927-82-1/4-20x30-B-B	1/4 - 20	3.23	1.18	0.77	0.15	0.79	0.89	0.04	0.79	0.27
GN.93198951	GN 927-82-1/4-20x35-B-B	1/4 - 20	3.23	1.38	0.77	0.15	0.79	0.89	0.04	0.79	0.27
GN.93199051	GN 927-82-1/4-20x40-B-B	1/4 - 20	3.23	1.57	0.77	0.15	0.79	0.89	0.04	0.79	0.27
GN.93199151	GN 927-82-1/4-20x50-B-B	1/4 - 20	3.23	1.97	0.77	0.15	0.79	0.89	0.04	0.79	0.27
GN.93199251	GN 927-82-1/4-20x60-B-B	1/4 - 20	3.23	2.36	0.77	0.15	0.79	0.89	0.04	0.79	0.27
GN.93566751	GN 927-82-5/16-18x20-B-B	5/16 - 18	3.23	0.79	0.77	0.15	0.79	0.89	0.04	0.79	0.27
GN.93198151	GN 927-82-5/16-18x25-B-B	5/16 - 18	3.23	0.98	0.77	0.15	0.79	0.89	0.04	0.79	0.22
GN.93198251	GN 927-82-5/16-18x30-B-B	5/16 - 18	3.23	1.18	0.77	0.15	0.79	0.89	0.04	0.79	0.24
GN.93198351	GN 927-82-5/16-18x35-B-B	5/16 - 18	3.23	1.38	0.77	0.15	0.79	0.89	0.04	0.79	0.24
GN.93198451	GN 927-82-5/16-18x40-B-B	5/16 - 18	3.23	1.57	0.77	0.15	0.79	0.89	0.04	0.79	0.24
GN.93198551	GN 927-82-5/16-18x50-B-B	5/16 - 18	3.23	1.97	0.77	0.15	0.79	0.89	0.04	0.79	0.26
GN.93198651	GN 927-82-5/16-18x60-B-B	5/16 - 18	3.23	2.36	0.77	0.15	0.79	0.89	0.04	0.79	0.26
GN.93190451	GN 927-101-5/16-18x20-B-B	5/16 - 18	3.98	0.79	1.00	0.19	1.02	1.06	0.06	0.98	0.44
GN.93567351	GN 927-101-5/16-18x25-B-B	5/16 - 18	3.98	0.98	1.00	0.19	1.02	1.06	0.06	0.98	0.45
GN.93567352	GN 927-101-5/16-18x30-B-B	5/16 - 18	3.98	1.18	1.00	0.19	1.02	1.06	0.06	0.98	0.45
GN.93567751	GN 927-101-5/16-18x35-B-B	5/16 - 18	3.98	1.38	1.00	0.19	1.02	1.06	0.06	0.98	0.45
GN.93190851	GN 927-101-5/16-18x40-B-B	5/16 - 18	3.98	1.57	1.00	0.19	1.02	1.06	0.06	0.98	0.46
GN.93191051	GN 927-101-5/16-18x50-B-B	5/16 - 18	3.98	1.97	1.00	0.19	1.02	1.06	0.06	0.98	0.46
GN.93192251	GN 927-101-5/16-18x60-B-B	5/16 - 18	3.98	2.36	1.00	0.19	1.02	1.06	0.06	0.98	0.47
GN.93191251	GN 927-101-3/8-16x20-B-B	3/8 - 16	3.98	0.79	1.00	0.19	1.02	1.06	0.06	0.98	0.45
GN.93568151	GN 927-101-3/8-16x25-B-B	3/8 - 16	3.98	0.98	1.00	0.19	1.02	1.06	0.06	0.98	0.46
GN.93191451	GN 927-101-3/8-16x30-B-B	3/8 - 16	3.98	1.18	1.00	0.19	1.02	1.06	0.06	0.98	0.46
GN.93568551	GN 927-101-3/8-16x35-B-B	3/8 - 16	3.98	1.38	1.00	0.19	1.02	1.06	0.06	0.98	0.47
GN.93191651	GN 927-101-3/8-16x40-B-B	3/8 - 16	3.98	1.57	1.00	0.19	1.02	1.06	0.06	0.98	0.47
GN.93191851	GN 927-101-3/8-16x50-B-B	3/8 - 16	3.98	1.97	1.00	0.19	1.02	1.06	0.06	0.98	0.46
GN.93191852	GN 927-101-3/8-16x60-B-B	3/8 - 16	3.98	2.36	1.00	0.19	1.02	1.06	0.06	0.98	0.49

* In clamping position
 ** Stroke at 90° rotation of the lever

1

2

3

4

5

6

7

8

9

10

11

12

13

14

15



16

17

18

19

Clamping handles




INCH

GN 927-B (d2 - I2)

Code	Description	d ₂	l ₁	l ₂ *	l ₆ *	l ₅ *	d ₃	d ₅	h**	b	
GN.93191258	GN 927-44-8-32x12-B-O	8 - 32	1.73	0.47	0.52	0.09	0.47	0.55	0.02	0.47	0.05
GN.93191259	GN 927-44-8-32x16-B-O	8 - 32	1.73	0.63	0.52	0.09	0.47	0.55	0.02	0.47	0.05
GN.93191260	GN 927-44-8-32x20-B-O	8 - 32	1.73	0.79	0.52	0.09	0.47	0.55	0.02	0.47	0.05
GN.93191261	GN 927-44-8-32x25-B-O	8 - 32	1.73	0.98	0.52	0.09	0.47	0.55	0.02	0.47	0.05
GN.93191262	GN 927-44-8-32x30-B-O	8 - 32	1.73	1.18	0.52	0.09	0.47	0.55	0.02	0.47	0.05
GN.93191263	GN 927-44-10-32x12-B-O	10 - 32	1.73	0.47	0.52	0.09	0.47	0.55	0.02	0.47	0.05
GN.93191264	GN 927-44-10-32x16-B-O	10 - 32	1.73	0.63	0.52	0.09	0.47	0.55	0.02	0.47	0.05
GN.93191265	GN 927-44-10-32x20-B-O	10 - 32	1.73	0.79	0.52	0.09	0.47	0.55	0.02	0.47	0.05
GN.93191266	GN 927-44-10-32x25-B-O	10 - 32	1.73	0.98	0.52	0.09	0.47	0.55	0.02	0.47	0.06
GN.93191267	GN 927-44-10-32x30-B-O	10 - 32	1.73	1.18	0.52	0.09	0.47	0.55	0.02	0.47	0.06
GN.93191268	GN 927-44-10-32x35-B-O	10 - 32	1.73	1.38	0.52	0.09	0.47	0.55	0.02	0.47	0.06
GN.93191269	GN 927-44-10-32x40-B-O	10 - 32	1.73	1.57	0.52	0.09	0.47	0.55	0.02	0.47	0.06
GN.93191270	GN 927-63-10-32x16-B-O	10 - 32	2.48	0.63	0.64	0.12	0.63	0.73	0.03	0.63	0.12
GN.93191271	GN 927-63-10-32x20-B-O	10 - 32	2.48	0.79	0.64	0.12	0.63	0.73	0.03	0.63	0.12
GN.93191272	GN 927-63-10-32x25-B-O	10 - 32	2.48	0.98	0.64	0.12	0.63	0.73	0.03	0.63	0.12
GN.93191273	GN 927-63-10-32x30-B-O	10 - 32	2.48	1.18	0.64	0.12	0.63	0.73	0.03	0.63	0.12
GN.93191274	GN 927-63-10-32x35-B-O	10 - 32	2.48	1.38	0.64	0.12	0.63	0.73	0.03	0.63	0.12
GN.93191275	GN 927-63-10-32x40-B-O	10 - 32	2.48	1.57	0.64	0.12	0.63	0.73	0.03	0.63	0.12
GN.93191276	GN 927-63-10-32x50-B-O	10 - 32	2.48	1.97	0.64	0.12	0.63	0.73	0.03	0.63	0.12
GN.93191277	GN 927-63-1/4-20x16-B-O	1/4 - 20	2.48	0.63	0.64	0.12	0.63	0.73	0.03	0.63	0.12
GN.93191278	GN 927-63-1/4-20x20-B-O	1/4 - 20	2.48	0.79	0.64	0.12	0.63	0.73	0.03	0.63	0.12
GN.93191279	GN 927-63-1/4-20x25-B-O	1/4 - 20	2.48	0.98	0.64	0.12	0.63	0.73	0.03	0.63	0.12
GN.93197301	GN 927-63-1/4-20x30-B-O	1/4 - 20	2.48	1.18	0.64	0.12	0.63	0.73	0.03	0.63	0.13
GN.93197302	GN 927-63-1/4-20x35-B-O	1/4 - 20	2.48	1.38	0.64	0.12	0.63	0.73	0.03	0.63	0.13
GN.93197303	GN 927-63-1/4-20x40-B-O	1/4 - 20	2.48	1.57	0.64	0.12	0.63	0.73	0.03	0.63	0.13
GN.93197601	GN 927-63-1/4-20x50-B-O	1/4 - 20	2.48	1.97	0.64	0.12	0.63	0.73	0.03	0.63	0.13
GN.93197602	GN 927-82-1/4-20x20-B-O	1/4 - 20	3.23	0.79	0.77	0.15	0.79	0.89	0.04	0.79	0.27
GN.93197603	GN 927-82-1/4-20x25-B-O	1/4 - 20	3.23	0.98	0.77	0.15	0.79	0.89	0.04	0.79	0.27
GN.93197604	GN 927-82-1/4-20x30-B-O	1/4 - 20	3.23	1.18	0.77	0.15	0.79	0.89	0.04	0.79	0.27
GN.93197605	GN 927-82-1/4-20x35-B-O	1/4 - 20	3.23	1.38	0.77	0.15	0.79	0.89	0.04	0.79	0.27
GN.93197606	GN 927-82-1/4-20x40-B-O	1/4 - 20	3.23	1.57	0.77	0.15	0.79	0.89	0.04	0.79	0.27
GN.93197607	GN 927-82-1/4-20x50-B-O	1/4 - 20	3.23	1.97	0.77	0.15	0.79	0.89	0.04	0.79	0.27
GN.93197608	GN 927-82-1/4-20x60-B-O	1/4 - 20	3.23	2.36	0.77	0.15	0.79	0.89	0.04	0.79	0.27
GN.93197609	GN 927-82-5/16-18x20-B-O	5/16 - 18	3.23	0.79	0.77	0.15	0.79	0.89	0.04	0.79	0.27
GN.93197610	GN 927-82-5/16-18x25-B-O	5/16 - 18	3.23	0.98	0.77	0.15	0.79	0.89	0.04	0.79	0.24
GN.93197611	GN 927-82-5/16-18x30-B-O	5/16 - 18	3.23	1.18	0.77	0.15	0.79	0.89	0.04	0.79	0.24
GN.93197612	GN 927-82-5/16-18x35-B-O	5/16 - 18	3.23	1.38	0.77	0.15	0.79	0.89	0.04	0.79	0.24
GN.93197613	GN 927-82-5/16-18x40-B-O	5/16 - 18	3.23	1.57	0.77	0.15	0.79	0.89	0.04	0.79	0.24
GN.93197614	GN 927-82-5/16-18x50-B-O	5/16 - 18	3.23	1.97	0.77	0.15	0.79	0.89	0.04	0.79	0.25
GN.93197615	GN 927-82-5/16-18x60-B-O	5/16 - 18	3.23	2.36	0.77	0.15	0.79	0.89	0.04	0.79	0.26
GN.93197616	GN 927-101-5/16-18x20-B-O	5/16 - 18	3.98	0.79	1.00	0.19	1.02	1.06	0.06	0.98	0.44
GN.93197617	GN 927-101-5/16-18x25-B-O	5/16 - 18	3.98	0.98	1.00	0.19	1.02	1.06	0.06	0.98	0.45
GN.93197618	GN 927-101-5/16-18x30-B-O	5/16 - 18	3.98	1.18	1.00	0.19	1.02	1.06	0.06	0.98	0.45
GN.93197619	GN 927-101-5/16-18x35-B-O	5/16 - 18	3.98	1.38	1.00	0.19	1.02	1.06	0.06	0.98	0.45
GN.93197620	GN 927-101-5/16-18x40-B-O	5/16 - 18	3.98	1.57	1.00	0.19	1.02	1.06	0.06	0.98	0.46
GN.93197621	GN 927-101-5/16-18x50-B-O	5/16 - 18	3.98	1.97	1.00	0.19	1.02	1.06	0.06	0.98	0.46
GN.93197622	GN 927-101-5/16-18x60-B-O	5/16 - 18	3.98	2.36	1.00	0.19	1.02	1.06	0.06	0.98	0.47
GN.93197623	GN 927-101-3/8-16x20-B-O	3/8 - 16	3.98	0.79	1.00	0.19	1.02	1.06	0.06	0.98	0.45
GN.93197624	GN 927-101-3/8-16x25-B-O	3/8 - 16	3.98	0.98	1.00	0.19	1.02	1.06	0.06	0.98	0.46
GN.93197625	GN 927-101-3/8-16x30-B-O	3/8 - 16	3.98	1.18	1.00	0.19	1.02	1.06	0.06	0.98	0.46
GN.93197626	GN 927-101-3/8-16x35-B-O	3/8 - 16	3.98	1.38	1.00	0.19	1.02	1.06	0.06	0.98	0.47
GN.93197627	GN 927-101-3/8-16x40-B-O	3/8 - 16	3.98	1.57	1.00	0.19	1.02	1.06	0.06	0.98	0.47
GN.93197628	GN 927-101-3/8-16x50-B-O	3/8 - 16	3.98	1.97	1.00	0.19	1.02	1.06	0.06	0.98	0.48
GN.93197629	GN 927-101-3/8-16x60-B-O	3/8 - 16	3.98	2.36	1.00	0.19	1.02	1.06	0.06	0.98	0.49

* In clamping position

** Stroke at 90° rotation of the lever





GN 927-B (d2 - l2)

INCH

Code	Description	d ₂	l ₁	l ₂ *	l ₆ *	l ₅ *	d ₃	d ₅	h**	b	Δ
GN.93192024	GN 927-44-8-32x12-B-R	8 - 32	1.73	0.47	0.52	0.09	0.47	0.55	0.02	0.47	0.05
GN.93192025	GN 927-44-8-32x16-B-R	8 - 32	1.73	0.63	0.52	0.09	0.47	0.55	0.02	0.47	0.06
GN.93192026	GN 927-44-8-32x20-B-R	8 - 32	1.73	0.79	0.52	0.09	0.47	0.55	0.02	0.47	0.06
GN.93192027	GN 927-44-8-32x25-B-R	8 - 32	1.73	0.98	0.52	0.09	0.47	0.55	0.02	0.47	0.06
GN.93192028	GN 927-44-8-32x30-B-R	8 - 32	1.73	1.18	0.52	0.09	0.47	0.55	0.02	0.47	0.06
GN.93192029	GN 927-44-10-32x12-B-R	10 - 32	1.73	0.47	0.52	0.09	0.47	0.55	0.02	0.47	0.06
GN.93192030	GN 927-44-10-32x16-B-R	10 - 32	1.73	0.63	0.52	0.09	0.47	0.55	0.02	0.47	0.06
GN.93192031	GN 927-44-10-32x20-B-R	10 - 32	1.73	0.79	0.52	0.09	0.47	0.55	0.02	0.47	0.06
GN.93192032	GN 927-44-10-32x25-B-R	10 - 32	1.73	0.98	0.52	0.09	0.47	0.55	0.02	0.47	0.06
GN.93192033	GN 927-44-10-32x30-B-R	10 - 32	1.73	1.18	0.52	0.09	0.47	0.55	0.02	0.47	0.06
GN.93192034	GN 927-44-10-32x35-B-R	10 - 32	1.73	1.38	0.52	0.09	0.47	0.55	0.02	0.47	0.06
GN.93192035	GN 927-44-10-32x40-B-R	10 - 32	1.73	1.57	0.52	0.09	0.47	0.55	0.02	0.47	0.06
GN.93192036	GN 927-63-10-32x16-B-R	10 - 32	2.48	0.63	0.64	0.12	0.63	0.73	0.03	0.63	0.12
GN.93192037	GN 927-63-10-32x20-B-R	10 - 32	2.48	0.79	0.64	0.12	0.63	0.73	0.03	0.63	0.12
GN.93192038	GN 927-63-10-32x25-B-R	10 - 32	2.48	0.98	0.64	0.12	0.63	0.73	0.03	0.63	0.12
GN.93192039	GN 927-63-10-32x30-B-R	10 - 32	2.48	1.18	0.64	0.12	0.63	0.73	0.03	0.63	0.12
GN.93192040	GN 927-63-10-32x35-B-R	10 - 32	2.48	1.38	0.64	0.12	0.63	0.73	0.03	0.63	0.12
GN.93192041	GN 927-63-10-32x40-B-R	10 - 32	2.48	1.57	0.64	0.12	0.63	0.73	0.03	0.63	0.12
GN.93192042	GN 927-63-1/4-20x16-B-R	1/4 - 20	2.48	0.63	0.64	0.12	0.63	0.73	0.03	0.63	0.12
GN.93192043	GN 927-63-1/4-20x20-B-R	1/4 - 20	2.48	0.79	0.64	0.12	0.63	0.73	0.03	0.63	0.12
GN.93192044	GN 927-63-1/4-20x25-B-R	1/4 - 20	2.48	0.98	0.64	0.12	0.63	0.73	0.03	0.63	0.12
GN.93192045	GN 927-63-1/4-20x30-B-R	1/4 - 20	2.48	1.18	0.64	0.12	0.63	0.73	0.03	0.63	0.13
GN.93192046	GN 927-63-1/4-20x35-B-R	1/4 - 20	2.48	1.38	0.64	0.12	0.63	0.73	0.03	0.63	0.13
GN.93192047	GN 927-63-1/4-20x40-B-R	1/4 - 20	2.48	1.57	0.64	0.12	0.63	0.73	0.03	0.63	0.13
GN.93192048	GN 927-63-1/4-20x50-B-R	1/4 - 20	2.48	1.97	0.64	0.12	0.63	0.73	0.03	0.63	0.13
GN.93192049	GN 927-82-1/4-20x20-B-R	1/4 - 20	3.23	0.79	0.77	0.15	0.79	0.89	0.04	0.79	0.27
GN.93192050	GN 927-82-1/4-20x25-B-R	1/4 - 20	3.23	0.98	0.77	0.15	0.79	0.89	0.04	0.79	0.27
GN.93192051	GN 927-82-1/4-20x30-B-R	1/4 - 20	3.23	1.18	0.77	0.15	0.79	0.89	0.04	0.79	0.27
GN.93192052	GN 927-82-1/4-20x35-B-R	1/4 - 20	3.23	1.38	0.77	0.15	0.79	0.89	0.04	0.79	0.27
GN.93192053	GN 927-82-1/4-20x40-B-R	1/4 - 20	3.23	1.57	0.77	0.15	0.79	0.89	0.04	0.79	0.27
GN.93192054	GN 927-82-1/4-20x50-B-R	1/4 - 20	3.23	1.97	0.77	0.15	0.79	0.89	0.04	0.79	0.27
GN.93192055	GN 927-82-1/4-20x60-B-R	1/4 - 20	3.23	2.36	0.77	0.15	0.79	0.89	0.04	0.79	0.27
GN.93192056	GN 927-82-5/16-18x20-B-R	5/16 - 18	3.23	0.79	0.77	0.15	0.79	0.89	0.04	0.79	0.27
GN.93192057	GN 927-82-5/16-18x25-B-R	5/16 - 18	3.23	0.98	0.77	0.15	0.79	0.89	0.04	0.79	0.27
GN.93192058	GN 927-82-5/16-18x30-B-R	5/16 - 18	3.23	1.18	0.77	0.15	0.79	0.89	0.04	0.79	0.27
GN.93192059	GN 927-82-5/16-18x35-B-R	5/16 - 18	3.23	1.38	0.77	0.15	0.79	0.89	0.04	0.79	0.27
GN.93192060	GN 927-82-5/16-18x40-B-R	5/16 - 18	3.23	1.57	0.77	0.15	0.79	0.89	0.04	0.79	0.27
GN.93192061	GN 927-82-5/16-18x50-B-R	5/16 - 18	3.23	1.97	0.77	0.15	0.79	0.89	0.04	0.79	0.27
GN.93192062	GN 927-82-5/16-18x60-B-R	5/16 - 18	3.23	2.36	0.77	0.15	0.79	0.89	0.04	0.79	0.27
GN.93192063	GN 927-101-5/16-18x20-B-R	5/16 - 18	3.98	0.79	1.00	0.19	1.02	1.06	0.06	0.98	0.44
GN.93192064	GN 927-101-5/16-18x25-B-R	5/16 - 18	3.98	0.98	1.00	0.19	1.02	1.06	0.06	0.98	0.45
GN.93192065	GN 927-101-5/16-18x30-B-R	5/16 - 18	3.98	1.18	1.00	0.19	1.02	1.06	0.06	0.98	0.45
GN.93192066	GN 927-101-5/16-18x35-B-R	5/16 - 18	3.98	1.38	1.00	0.19	1.02	1.06	0.06	0.98	0.45
GN.93192067	GN 927-101-5/16-18x40-B-R	5/16 - 18	3.98	1.57	1.00	0.19	1.02	1.06	0.06	0.98	0.46
GN.93192068	GN 927-101-5/16-18x50-B-R	5/16 - 18	3.98	1.97	1.00	0.19	1.02	1.06	0.06	0.98	0.46
GN.93192069	GN 927-101-5/16-18x60-B-R	5/16 - 18	3.98	2.36	1.00	0.19	1.02	1.06	0.06	0.98	0.47
GN.93190470	GN 927-101-3/8-16x20-B-R	3/8 - 16	3.98	0.79	1.00	0.19	1.02	1.06	0.06	0.98	0.45
GN.93190471	GN 927-101-3/8-16x25-B-R	3/8 - 16	3.98	0.98	1.00	0.19	1.02	1.06	0.06	0.98	0.46
GN.93190472	GN 927-101-3/8-16x30-B-R	3/8 - 16	3.98	1.18	1.00	0.19	1.02	1.06	0.06	0.98	0.46
GN.93190473	GN 927-101-3/8-16x35-B-R	3/8 - 16	3.98	1.38	1.00	0.19	1.02	1.06	0.06	0.98	0.47
GN.93190474	GN 927-101-3/8-16x40-B-R	3/8 - 16	3.98	1.57	1.00	0.19	1.02	1.06	0.06	0.98	0.47
GN.93190475	GN 927-101-3/8-16x50-B-R	3/8 - 16	3.98	1.97	1.00	0.19	1.02	1.06	0.06	0.98	0.48
GN.93190476	GN 927-101-3/8-16x60-B-R	3/8 - 16	3.98	2.36	1.00	0.19	1.02	1.06	0.06	0.98	0.49

* In clamping position

** Stroke at 90° rotation of the lever



INCH

GN 927-B (d2 - l2)

Code	Description	d ₂	l ₁	l ₂ *	l ₆ *	l ₅ *	d ₃	d ₅	h**	b	
GN.93190605	GN 927-44-8-32x12-B-S	8 - 32	1.73	0.47	0.52	0.09	0.47	0.55	0.02	0.47	0.05
GN.93190606	GN 927-44-8-32x16-B-S	8 - 32	1.73	0.63	0.52	0.09	0.47	0.55	0.02	0.47	0.05
GN.93190607	GN 927-44-8-32x20-B-S	8 - 32	1.73	0.79	0.52	0.09	0.47	0.55	0.02	0.47	0.05
GN.93190608	GN 927-44-8-32x25-B-S	8 - 32	1.73	0.98	0.52	0.09	0.47	0.55	0.02	0.47	0.05
GN.93190609	GN 927-44-8-32x30-B-S	8 - 32	1.73	1.18	0.52	0.09	0.47	0.55	0.02	0.47	0.06
GN.93190610	GN 927-44-10-32x12-B-S	10 - 32	1.73	0.47	0.52	0.09	0.47	0.55	0.02	0.47	0.05
GN.93190611	GN 927-44-10-32x16-B-S	10 - 32	1.73	0.63	0.52	0.09	0.47	0.55	0.02	0.47	0.05
GN.93190612	GN 927-44-10-32x20-B-S	10 - 32	1.73	0.79	0.52	0.09	0.47	0.55	0.02	0.47	0.06
GN.93190613	GN 927-44-10-32x25-B-S	10 - 32	1.73	0.98	0.52	0.09	0.47	0.55	0.02	0.47	0.06
GN.93190614	GN 927-44-10-32x30-B-S	10 - 32	1.73	1.18	0.52	0.09	0.47	0.55	0.02	0.47	0.06
GN.93190615	GN 927-44-10-32x35-B-S	10 - 32	1.73	1.38	0.52	0.09	0.47	0.55	0.02	0.47	0.06
GN.93190616	GN 927-44-10-32x40-B-S	10 - 32	1.73	1.57	0.52	0.09	0.47	0.55	0.02	0.47	0.06
GN.93190617	GN 927-63-10-32x16-B-S	10 - 32	2.48	0.63	0.64	0.12	0.63	0.73	0.03	0.63	0.12
GN.93190618	GN 927-63-10-32x20-B-S	10 - 32	2.48	0.79	0.64	0.12	0.63	0.73	0.03	0.63	0.12
GN.93190619	GN 927-63-10-32x25-B-S	10 - 32	2.48	0.98	0.64	0.12	0.63	0.73	0.03	0.63	0.12
GN.93190620	GN 927-63-10-32x30-B-S	10 - 32	2.48	1.18	0.64	0.12	0.63	0.73	0.03	0.63	0.12
GN.93190621	GN 927-63-10-32x35-B-S	10 - 32	2.48	1.38	0.64	0.12	0.63	0.73	0.03	0.63	0.12
GN.93190622	GN 927-63-10-32x40-B-S	10 - 32	2.48	1.57	0.64	0.12	0.63	0.73	0.03	0.63	0.12
GN.93190623	GN 927-63-10-32x50-B-S	10 - 32	2.48	1.97	0.64	0.12	0.63	0.73	0.03	0.63	0.12
GN.93190624	GN 927-63-1/4-20x16-B-S	1/4 - 20	2.48	0.63	0.64	0.12	0.63	0.73	0.03	0.63	0.12
GN.93190625	GN 927-63-1/4-20x20-B-S	1/4 - 20	2.48	0.79	0.64	0.12	0.63	0.73	0.03	0.63	0.12
GN.93190626	GN 927-63-1/4-20x25-B-S	1/4 - 20	2.48	0.98	0.64	0.12	0.63	0.73	0.03	0.63	0.12
GN.93190627	GN 927-63-1/4-20x30-B-S	1/4 - 20	2.48	1.18	0.64	0.12	0.63	0.73	0.03	0.63	0.13
GN.93190628	GN 927-63-1/4-20x35-B-S	1/4 - 20	2.48	1.38	0.64	0.12	0.63	0.73	0.03	0.63	0.13
GN.93190629	GN 927-63-1/4-20x40-B-S	1/4 - 20	2.48	1.57	0.64	0.12	0.63	0.73	0.03	0.63	0.13
GN.93190630	GN 927-63-1/4-20x50-B-S	1/4 - 20	2.48	1.97	0.64	0.12	0.63	0.73	0.03	0.63	0.13
GN.93190631	GN 927-82-1/4-20x20-B-S	1/4 - 20	3.23	0.79	0.77	0.15	0.79	0.89	0.04	0.79	0.27
GN.93190632	GN 927-82-1/4-20x25-B-S	1/4 - 20	3.23	0.98	0.77	0.15	0.79	0.89	0.04	0.79	0.27
GN.93190633	GN 927-82-1/4-20x30-B-S	1/4 - 20	3.23	1.18	0.77	0.15	0.79	0.89	0.04	0.79	0.27
GN.93190634	GN 927-82-1/4-20x35-B-S	1/4 - 20	3.23	1.38	0.77	0.15	0.79	0.89	0.04	0.79	0.27
GN.93190635	GN 927-82-1/4-20x40-B-S	1/4 - 20	3.23	1.57	0.77	0.15	0.79	0.89	0.04	0.79	0.27
GN.93190636	GN 927-82-1/4-20x50-B-S	1/4 - 20	3.23	1.97	0.77	0.15	0.79	0.89	0.04	0.79	0.27
GN.93190637	GN 927-82-1/4-20x60-B-S	1/4 - 20	3.23	2.36	0.77	0.15	0.79	0.89	0.04	0.79	0.27
GN.93190638	GN 927-82-5/16-18x20-B-S	5/16 - 18	3.23	0.79	0.77	0.15	0.79	0.89	0.04	0.79	0.27
GN.93190639	GN 927-82-5/16-18x25-B-S	5/16 - 18	3.23	0.98	0.77	0.15	0.79	0.89	0.04	0.79	0.24
GN.93190640	GN 927-82-5/16-18x30-B-S	5/16 - 18	3.23	1.18	0.77	0.15	0.79	0.89	0.04	0.79	0.24
GN.93190641	GN 927-82-5/16-18x35-B-S	5/16 - 18	3.23	1.38	0.77	0.15	0.79	0.89	0.04	0.79	0.24
GN.93190642	GN 927-82-5/16-18x40-B-S	5/16 - 18	3.23	1.57	0.77	0.15	0.79	0.89	0.04	0.79	0.24
GN.93190643	GN 927-82-5/16-18x50-B-S	5/16 - 18	3.23	1.97	0.77	0.15	0.79	0.89	0.04	0.79	0.25
GN.93190644	GN 927-82-5/16-18x60-B-S	5/16 - 18	3.23	2.36	0.77	0.15	0.79	0.89	0.04	0.79	0.26
GN.93190645	GN 927-101-5/16-18x20-B-S	5/16 - 18	3.98	0.79	1.00	0.19	1.02	1.06	0.06	0.98	0.44
GN.93190646	GN 927-101-5/16-18x25-B-S	5/16 - 18	3.98	0.98	1.00	0.19	1.02	1.06	0.06	0.98	0.45
GN.93190647	GN 927-101-5/16-18x30-B-S	5/16 - 18	3.98	1.18	1.00	0.19	1.02	1.06	0.06	0.98	0.45
GN.93190648	GN 927-101-5/16-18x35-B-S	5/16 - 18	3.98	1.38	1.00	0.19	1.02	1.06	0.06	0.98	0.45
GN.93190649	GN 927-101-5/16-18x40-B-S	5/16 - 18	3.98	1.57	1.00	0.19	1.02	1.06	0.06	0.98	0.46
GN.93190650	GN 927-101-5/16-18x50-B-S	5/16 - 18	3.98	1.97	1.00	0.19	1.02	1.06	0.06	0.98	0.46
GN.93190651	GN 927-101-5/16-18x60-B-S	5/16 - 18	3.98	2.36	1.00	0.19	1.02	1.06	0.06	0.98	0.47
GN.93190652	GN 927-101-3/8-16x20-B-S	3/8 - 16	3.98	0.79	1.00	0.19	1.02	1.06	0.06	0.98	0.45
GN.93190653	GN 927-101-3/8-16x25-B-S	3/8 - 16	3.98	0.98	1.00	0.19	1.02	1.06	0.06	0.98	0.46
GN.93190654	GN 927-101-3/8-16x30-B-S	3/8 - 16	3.98	1.18	1.00	0.19	1.02	1.06	0.06	0.98	0.46
GN.93190655	GN 927-101-3/8-16x35-B-S	3/8 - 16	3.98	1.38	1.00	0.19	1.02	1.06	0.06	0.98	0.47
GN.93190656	GN 927-101-3/8-16x40-B-S	3/8 - 16	3.98	1.57	1.00	0.19	1.02	1.06	0.06	0.98	0.47
GN.93190657	GN 927-101-3/8-16x50-B-S	3/8 - 16	3.98	1.97	1.00	0.19	1.02	1.06	0.06	0.98	0.48
GN.93190658	GN 927-101-3/8-16x60-B-S	3/8 - 16	3.98	2.36	1.00	0.19	1.02	1.06	0.06	0.98	0.49

* In clamping position

** Stroke at 90° rotation of the lever