

- 1
- 2
- 3
- 4
- 5
- 6
- 7
- 8
- 9
- 10
- 11
- 12
- 13
- 14
- 15
- 16
- 17
- 18

**MATERIAL**

Glass-fibre reinforced polyamide based (PA) technopolymer, black colour, matte finish.

**STANDARD EXECUTIONS**


- **1.780+x**: zinc-plated steel pin, hexagon socket at threaded end.
- **1.780+x-SST**: AISI 303 stainless steel pin, hexagonal socket at threaded end.



ELESA Original design

**Conversion Table**  
1 mm = 0.039 inch

mm	inch
40	1.57
50	1.97
56	2.20
65	2.56
80	3.15
90	3.54
100	3.94



**1.780+x**

**METRIC**

Code	Description	D	L	d6g	d1	l	s	△
124921	1.780/40+x-M6	18	40	M6	15	13	3	25
124931	1.780/50+x-M6	21	50	M6	17	13	3	37
124941	1.780/56+x-M6	22	56	M6	18	13	3	39
124951	1.780/65+x-M8	24.5	65	M8	20.5	15	4	66
124952	1.780/65+x-M10	24.5	65	M10	20.5	17	5	67
124961	1.780/80+x-M8	26.5	80	M8	21	15	4	76
124962	1.780/80+x-M10	26.5	80	M10	21	17	5	79
124971	1.780/90+x-M10	28.5	90	M10	22.5	20	5	90
124972	1.780/90+x-M12	28.5	90	M12	22.5	20	5	104
124981	1.780/100+x-M12	31	100	M12	25	20	5	115

**1.780+x-SST**

**INOX**  
STAINLESS  
STEEL

**METRIC**

Code	Description	D	L	d6g	d1	l	s	△
124926	1.780/40+x-M6-SST	18	40	M6	15	13	3	25
124936	1.780/50+x-M6-SST	21	50	M6	17	13	3	37
124946	1.780/56+x-M6-SST	22	56	M6	18	13	3	39
124956	1.780/65+x-M8-SST	24.5	65	M8	20.5	15	4	66
124966	1.780/80+x-M8-SST	26.5	80	M8	21	15	4	76
124967	1.780/80+x-M10-SST	26.5	80	M10	21	17	5	79
124976	1.780/90+x-M10-SST	28.5	90	M10	22.5	20	5	90
124977	1.780/90+x-M12-SST	28.5	90	M12	22.5	20	5	104
124986	1.780/100+x-M12-SST	31	100	M12	25	20	5	115

Fixed & Revolving handles