

LEVER BODY

Die-cast zinc alloy with epoxy resin coating, or stainless steel, sandblasted matte finish.

STANDARD EXECUTIONS

Threaded hole or threaded screw.

- **GN 300:** zinc alloy lever, black-oxide steel clamping element and retaining screw with hexagon socket. Stainless steel return spring.
- **GN 300.1:** zinc alloy lever, AISI 303 stainless steel clamping element and retaining screw with hexagon socket. AISI 301 stainless steel return spring.
- **GN 300.5:** stainless steel lever, AISI 303 stainless steel clamping element and retaining screw with hexagon socket. AISI 301 stainless steel return spring.

FEATURES AND APPLICATIONS

Particularly suitable when the lever turning angle is limited owing to lack of space.

INSTRUCTIONS OF USE

For clamping, lift the lever to disengage the clamping device teeth and bring it back to start position. By releasing the lever, the return spring automatically engages the teeth.


If the lever cannot make a 360° rotation, the clamping element can be easily screwed by means of the hexagon socket front head screw (after having disengaged the lever).

SPECIAL EXECUTIONS ON REQUEST FOR GN 300 AND GN 300.1

- Lever body in different colours.
- Chrome-plated lever.
- Clamping element with different threadings and lengths.

SPECIAL EXECUTIONS ON REQUEST FOR GN 300.5



- Clamping element with different threadings and lengths.
- Adjustable handle with hexagonal head retaining screw (GN 300.5-AS).
- Adjustable handles with lever in cast CF-8 stainless steel with electropolished finish (GN 300.6).



GN 300 (d1)

INCH

Code	Description	l1	d1	d3	d4	h1	h2	h3	h4	tmin	△
GN.906101	GN 300-45-10-32-SW	1.77	10-32	0.39	0.51	0.96	0.16	1.38	0.14	0.35	0.07
GN.906111	GN 300-45-1/4-20-SW	1.77	1/4-20	0.39	0.51	0.96	0.16	1.38	0.14	0.35	0.07
GN.906116	GN 300-45-5/16-18-SW	1.77	5/16-18	0.39	0.51	0.96	0.16	1.38	0.14	0.35	0.06
GN.906121	GN 300-63-1/4-20-SW	2.48	1/4-20	0.53	0.69	1.22	0.26	1.77	0.16	0.43	0.17
GN.906131	GN 300-63-5/16-18-SW	2.48	5/16-18	0.53	0.69	1.22	0.26	1.77	0.16	0.43	0.16
GN.906141	GN 300-78-5/16-18-SW	3.07	5/16-18	0.63	0.83	1.42	0.31	2.17	0.16	0.55	0.27
GN.906151	GN 300-78-3/8-16-SW	3.07	3/8-16	0.63	0.83	1.42	0.31	2.17	0.16	0.67	0.43
GN.906161	GN 300-92-3/8-16-SW	3.62	3/8-16	0.75	0.94	1.69	0.43	2.56	0.16	0.67	0.43
GN.906171	GN 300-92-1/2-13-SW	3.62	1/2-13	0.75	0.94	1.69	0.43	2.56	0.16	0.67	0.38
GN.906181	GN 300-108-1/2-13-SW	4.25	1/2-13	0.91	1.18	1.99	0.47	2.99	0.2	0.87	0.67
GN.906191	GN 300-108-5/8-11-SW	4.25	5/8-11	0.91	1.18	1.99	0.47	2.99	0.2	0.87	0.67



GN 300.1 (d1)

INOX STAINLESS STEEL INCH


Code	Description	l1	d1	d3	d4	h1	h2	h3	h4	tmin	⚖
GN.905101	GN 300.1-45-10-32-SW	1.77	10-32	0.39	0.51	0.96	0.16	1.38	0.14	0.35	0.08
GN.905111	GN 300.1-45-1/4-20-SW	1.77	1/4-20	0.39	0.51	0.96	0.16	1.38	0.14	0.35	0.07
GN.905121	GN 300.1-63-1/4-20-SW	2.48	1/4-20	0.53	0.69	1.22	0.26	1.77	0.16	0.43	0.17
GN.905131	GN 300.1-63-5/16-18-SW	2.48	5/16-18	0.53	0.69	1.22	0.26	1.77	0.16	0.43	0.16
GN.905141	GN 300.1-78-5/16-18-SW	3.07	5/16-18	0.63	0.83	1.42	0.31	2.17	0.16	0.55	0.27
GN.905151	GN 300.1-78-3/8-16-SW	3.07	3/8-16	0.63	0.83	1.42	0.31	2.17	0.16	0.55	0.26
GN.905161	GN 300.1-92-3/8-16-SW	3.62	3/8-16	0.75	0.94	1.69	0.43	2.56	0.16	0.67	0.41
GN.905171	GN 300.1-92-1/2-13-SW	3.62	1/2-13	0.75	0.94	1.69	0.43	2.56	0.16	0.67	0.39

GN 300.5 (d1)

INOX STAINLESS STEEL INCH

Code	Description	l1	d1	d3	d4	h1	h2	h3	h4	tmin	⚖
GN.915701	GN 300.5-45-1/4-20-IS	1.77	1/4-20	0.39	0.51	0.96	0.16	1.22	0.14	0.35	0.09
GN.915711	GN 300.5-63-5/16-18-IS	2.48	5/16-18	0.53	0.69	1.22	0.26	1.77	0.16	0.43	0.19
GN.915721	GN 300.5-78-3/8-16-IS	3.07	3/8-16	0.63	0.83	1.42	0.31	2.17	0.16	0.55	0.31

GN 300 - GN 300.1 - GN 300.5
(d1-l2)



GN 300 (d1 - l2)

INCH

Code	Description	l1	d1	d3	d4	h1	h2	h3	h4	l2	Δ
GN.906201	GN 300-45-10-32-047-SW	1.77	10-32	0.39	0.51	0.96	0.16	1.38	0.14	0.47	0.08
GN.906206	GN 300-45-10-32-063-SW	1.77	10-32	0.39	0.51	0.96	0.16	1.38	0.14	0.63	0.08
GN.906211	GN 300-45-10-32-079-SW	1.77	10-32	0.39	0.51	0.96	0.16	1.38	0.14	0.79	0.08
GN.906216	GN 300-45-10-32-098-SW	1.77	10-32	0.39	0.51	0.96	0.16	1.38	0.14	0.98	0.08
GN.906221	GN 300-45-10-32-126-SW	1.77	10-32	0.39	0.51	0.96	0.16	1.38	0.14	1.26	0.08
GN.906226	GN 300-45-10-32-157-SW	1.77	10-32	0.39	0.51	0.96	0.16	1.38	0.14	1.57	0.09
GN.906241	GN 300-45-1/4-20-039-SW	1.77	1/4-20	0.39	0.51	0.96	0.16	1.38	0.14	0.39	0.07
GN.906246	GN 300-45-1/4-20-047-SW	1.77	1/4-20	0.39	0.51	0.96	0.16	1.38	0.14	0.47	0.08
GN.906251	GN 300-45-1/4-20-063-SW	1.77	1/4-20	0.39	0.51	0.96	0.16	1.38	0.14	0.63	0.08
GN.906256	GN 300-45-1/4-20-079-SW	1.77	1/4-20	0.39	0.51	0.96	0.16	1.38	0.14	0.79	0.08
GN.906261	GN 300-45-1/4-20-098-SW	1.77	1/4-20	0.39	0.51	0.96	0.16	1.38	0.14	0.98	0.08
GN.906266	GN 300-45-1/4-20-126-SW	1.77	1/4-20	0.39	0.51	0.96	0.16	1.38	0.14	1.26	0.09
GN.906271	GN 300-45-1/4-20-157-SW	1.77	1/4-20	0.39	0.51	0.96	0.16	1.38	0.14	1.57	0.09
GN.906273	GN 300-45-1/4-20-177-SW	1.77	1/4-20	0.39	0.51	0.96	0.16	1.38	0.14	1.77	0.11
GN.906323	GN 300-63-1/4-20-079-SW	2.48	1/4-20	0.53	0.69	1.22	0.26	1.77	0.16	0.79	0.18
GN.906325	GN 300-63-1/4-20-098-SW	2.48	1/4-20	0.53	0.69	1.22	0.26	1.77	0.16	0.98	0.18
GN.906279	GN 300-63-5/16-18-047-SW	2.48	5/16-18	0.53	0.69	1.22	0.26	1.77	0.16	0.47	0.18
GN.906281	GN 300-63-5/16-18-063-SW	2.48	5/16-18	0.53	0.69	1.22	0.26	1.77	0.16	0.63	0.18
GN.906286	GN 300-63-5/16-18-079-SW	2.48	5/16-18	0.53	0.69	1.22	0.26	1.77	0.16	0.79	0.19
GN.906291	GN 300-63-5/16-18-098-SW	2.48	5/16-18	0.53	0.69	1.22	0.26	1.77	0.16	0.98	0.19
GN.906296	GN 300-63-5/16-18-126-SW	2.48	5/16-18	0.53	0.69	1.22	0.26	1.77	0.16	1.26	0.19
GN.906301	GN 300-63-5/16-18-157-SW	2.48	5/16-18	0.53	0.69	1.22	0.26	1.77	0.16	1.57	0.2
GN.906276	GN 300-63-5/16-18-177-SW	2.48	5/16-18	0.53	0.69	1.22	0.26	1.77	0.16	1.77	0.2
GN.906311	GN 300-63-5/16-18-197-SW	2.48	5/16-18	0.53	0.69	1.22	0.26	1.77	0.16	1.97	0.2
GN.906316	GN 300-63-5/16-18-248-SW	2.48	5/16-18	0.53	0.69	1.22	0.26	1.77	0.16	2.48	0.22
GN.906336	GN 300-63-3/8-16-079-SW	2.48	3/8-16	0.53	0.69	1.22	0.26	1.77	0.16	0.79	0.19
GN.906341	GN 300-63-3/8-16-098-SW	2.48	3/8-16	0.53	0.69	1.22	0.26	1.77	0.16	0.98	0.2
GN.906346	GN 300-63-3/8-16-126-SW	2.48	3/8-16	0.53	0.69	1.22	0.26	1.77	0.16	1.26	0.21
GN.906351	GN 300-63-3/8-16-157-SW	2.48	3/8-16	0.53	0.69	1.22	0.26	1.77	0.16	1.57	0.21
GN.906356	GN 300-63-3/8-16-177-SW	2.48	3/8-16	0.53	0.69	1.22	0.26	1.77	0.16	1.77	0.21
GN.906361	GN 300-63-3/8-16-197-SW	2.48	3/8-16	0.53	0.69	1.22	0.26	1.77	0.16	1.97	0.22
GN.906366	GN 300-63-3/8-16-248-SW	2.48	3/8-16	0.53	0.69	1.22	0.26	1.77	0.16	2.48	0.24
GN.906381	GN 300-78-3/8-16-063-SW	3.07	3/8-16	0.63	0.83	1.42	0.31	2.17	0.16	0.63	0.3
GN.906386	GN 300-78-3/8-16-079-SW	3.07	3/8-16	0.63	0.83	1.42	0.31	2.17	0.16	0.79	0.31
GN.906391	GN 300-78-3/8-16-098-SW	3.07	3/8-16	0.63	0.83	1.42	0.31	2.17	0.16	0.98	0.31
GN.906401	GN 300-78-3/8-16-126-SW	3.07	3/8-16	0.63	0.83	1.42	0.31	2.17	0.16	1.26	0.31
GN.906406	GN 300-78-3/8-16-157-SW	3.07	3/8-16	0.63	0.83	1.42	0.31	2.17	0.16	1.57	0.32
GN.906411	GN 300-78-3/8-16-177-SW	3.07	3/8-16	0.63	0.83	1.42	0.31	2.17	0.16	1.77	0.33
GN.906416	GN 300-78-3/8-16-197-SW	3.07	3/8-16	0.63	0.83	1.42	0.31	2.17	0.16	1.97	0.33
GN.906421	GN 300-78-3/8-16-248-SW	3.07	3/8-16	0.63	0.83	1.42	0.31	2.17	0.16	2.48	0.35
GN.906449	GN 300-78-1/2-13-126-SW	3.07	1/2-13	0.63	0.83	1.42	0.31	2.17	0.16	1.26	0.33
GN.906479	GN 300-92-3/8-16-098-SW	3.62	3/8-16	0.75	0.94	1.69	0.43	2.56	0.16	0.98	0.45
GN.906481	GN 300-92-3/8-16-126-SW	3.62	3/8-16	0.75	0.94	1.69	0.43	2.56	0.16	1.26	0.46
GN.906483	GN 300-92-3/8-16-138-SW	3.62	3/8-16	0.75	0.94	1.69	0.43	2.56	0.16	1.38	0.46
GN.906491	GN 300-92-3/8-16-157-SW	3.62	3/8-16	0.75	0.94	1.69	0.43	2.56	0.16	1.57	0.47
GN.906493	GN 300-92-3/8-16-177-SW	3.62	3/8-16	0.75	0.94	1.69	0.43	2.56	0.16	1.77	0.47
GN.906496	GN 300-92-3/8-16-197-SW	3.62	3/8-16	0.75	0.94	1.69	0.43	2.56	0.16	1.97	0.48
GN.906499	GN 300-92-3/8-16-248-SW	3.62	3/8-16	0.75	0.94	1.69	0.43	2.56	0.16	2.48	0.49



INCH

Code	Description	l1	d1	d3	d4	h1	h2	h3	h4	l2	△
GN.906516	GN 300-92-1/2-13-098-SW	3.62	1/2-13	0.75	0.94	1.69	0.43	2.56	0.16	0.98	0.47
GN.906521	GN 300-92-1/2-13-126-SW	3.62	1/2-13	0.75	0.94	1.69	0.43	2.56	0.16	1.26	0.48
GN.906523	GN 300-92-1/2-13-138-SW	3.62	1/2-13	0.75	0.94	1.69	0.43	2.56	0.16	1.38	0.48
GN.906526	GN 300-92-1/2-13-157-SW	3.62	1/2-13	0.75	0.94	1.69	0.43	2.56	0.16	1.57	0.49
GN.906531	GN 300-92-1/2-13-177-SW	3.62	1/2-13	0.75	0.94	1.69	0.43	2.56	0.16	1.77	0.49
GN.906536	GN 300-92-1/2-13-197-SW	3.62	1/2-13	0.75	0.94	1.69	0.43	2.56	0.16	1.97	0.5
GN.906541	GN 300-92-1/2-13-248-SW	3.62	1/2-13	0.75	0.94	1.69	0.43	2.56	0.16	2.48	0.53
GN.906551	GN 300-108-1/2-13-217-SW	4.25	1/2-13	0.91	1.18	1.99	0.47	2.99	0.2	2.17	0.83
GN.906556	GN 300-108-1/2-13-248-SW	4.25	1/2-13	0.91	1.18	1.99	0.47	2.99	0.2	2.48	0.84
GN.906571	GN 300-108-5/8-11-157-SW	4.25	5/8-11	0.91	1.18	1.99	0.47	2.99	0.2	1.57	0.83
GN.906576	GN 300-108-5/8-11-217-SW	4.25	5/8-11	0.91	1.18	1.99	0.47	2.99	0.2	2.17	0.87
GN.906581	GN 300-108-5/8-11-248-SW	4.25	5/8-11	0.91	1.18	1.99	0.47	2.99	0.2	2.48	0.9

GN 300.1 (d1 - l2)

INOX STAINLESS STEEL

INCH

Code	Description	l1	d1	d3	d4	h1	h2	h3	h4	l2	△
GN.905211	GN 300.1-45-1/4-20-063-SW	1.77	1/4-20	0.39	0.51	0.96	0.16	1.38	0.14	0.63	0.08
GN.905221	GN 300.1-45-1/4-20-079-SW	1.77	1/4-20	0.39	0.51	0.96	0.16	1.38	0.14	0.79	0.08
GN.905231	GN 300.1-45-1/4-20-098-SW	1.77	1/4-20	0.39	0.51	0.96	0.16	1.38	0.14	0.98	0.08
GN.905241	GN 300.1-45-1/4-20-126-SW	1.77	1/4-20	0.39	0.51	0.96	0.16	1.38	0.14	1.26	0.09
GN.905251	GN 300.1-45-1/4-20-157-SW	1.77	1/4-20	0.39	0.51	0.96	0.16	1.38	0.14	1.57	0.09
GN.905261	GN 300.1-45-1/4-20-177-SW	1.77	1/4-20	0.39	0.51	0.96	0.16	1.38	0.14	1.77	0.1
GN.905291	GN 300.1-63-5/16-18-079-SW	2.48	5/16-18	0.53	0.69	1.22	0.26	1.77	0.16	0.79	0.19
GN.905301	GN 300.1-63-5/16-18-126-SW	2.48	5/16-18	0.53	0.69	1.22	0.26	1.77	0.16	1.26	0.19
GN.905311	GN 300.1-63-5/16-18-157-SW	2.48	5/16-18	0.53	0.69	1.22	0.26	1.77	0.16	1.57	0.2
GN.905321	GN 300.1-63-5/16-18-197-SW	2.48	5/16-18	0.53	0.69	1.22	0.26	1.77	0.16	1.97	0.2
GN.905331	GN 300.1-63-5/16-18-248-SW	2.48	5/16-18	0.53	0.69	1.22	0.26	1.77	0.16	2.48	0.22
GN.905341	GN 300.1-63-3/8-16-079-SW	2.48	3/8-16	0.53	0.69	1.22	0.26	1.77	0.16	0.79	0.19
GN.905346	GN 300.1-63-3/8-16-157-SW	2.48	3/8-16	0.53	0.69	1.22	0.26	1.77	0.16	1.57	0.2
GN.905361	GN 300.1-78-3/8-16-098-SW	3.07	3/8-16	0.63	0.83	1.42	0.31	2.17	0.16	0.98	0.31
GN.905371	GN 300.1-78-3/8-16-126-SW	3.07	3/8-16	0.63	0.83	1.42	0.31	2.17	0.16	1.26	0.31
GN.905381	GN 300.1-78-3/8-16-157-SW	3.07	3/8-16	0.63	0.83	1.42	0.31	2.17	0.16	1.57	0.32
GN.905391	GN 300.1-78-3/8-16-197-SW	3.07	3/8-16	0.63	0.83	1.42	0.31	2.17	0.16	1.97	0.33
GN.905401	GN 300.1-78-3/8-16-248-SW	3.07	3/8-16	0.63	0.83	1.42	0.31	2.17	0.16	2.48	0.35
GN.905411	GN 300.1-78-1/2-13-126-SW	3.07	1/2-13	0.63	0.83	1.42	0.31	2.17	0.16	1.26	0.31
GN.905421	GN 300.1-92-1/2-13-126-SW	3.62	1/2-13	0.75	0.94	1.69	0.43	2.56	0.16	1.26	0.48
GN.905431	GN 300.1-92-1/2-13-197-SW	3.62	1/2-13	0.75	0.94	1.69	0.43	2.56	0.16	1.97	0.5
GN.905441	GN 300.1-92-1/2-13-248-SW	3.62	1/2-13	0.75	0.94	1.69	0.43	2.56	0.16	2.48	0.53

GN 300.5 (d1 - l2)

INOX STAINLESS STEEL

INCH

Code	Description	l1	d1	d3	d4	h1	h2	h3	h4	l2	△
GN.915732	GN 300.5-45-1/4-20-079-IS	1.77	1/4-20	0.39	0.51	0.96	0.16	1.38	0.14	0.79	0.09
GN.915733	GN 300.5-45-1/4-20-098-IS	1.77	1/4-20	0.39	0.51	0.96	0.16	1.38	0.14	0.98	0.1
GN.915734	GN 300.5-45-1/4-20-126-IS	1.18	1/4-20	0.39	0.51	0.96	0.16	1.38	0.14	1.26	0.1
GN.915744	GN 300.5-63-5/16-18-126-IS	2.48	5/16-18	0.53	0.69	1.22	0.26	1.77	0.16	1.26	0.22
GN.915745	GN 300.5-63-5/16-18-157-IS	2.48	5/16-18	0.53	0.69	1.22	0.26	1.77	0.16	1.57	0.23
GN.915746	GN 300.5-63-5/16-18-197-IS	2.48	5/16-18	0.53	0.69	1.22	0.26	1.77	0.16	1.97	0.24
GN.915754	GN 300.5-78-3/8-16-126-IS	3.07	3/8-16	0.63	0.83	1.42	0.31	2.17	0.16	1.26	0.37
GN.915755	GN 300.5-78-3/8-16-157-IS	3.07	3/8-16	0.63	0.83	1.42	0.31	2.17	0.16	1.57	0.37
GN.915756	GN 300.5-78-3/8-16-197-IS	3.07	3/8-16	0.63	0.83	1.42	0.31	2.17	0.16	1.97	0.39