

MATERIAL

Cast aluminium, fine sandblasted matte surface, turned and mirror-polished rim.

STANDARD EXECUTIONS

Standard reamed hole.



- **GN 321-A:** without handle.
- **GN 321-R:** with revolving handle in polyamide based (PA) technopolymer, black colour, matte finish.

SPECIAL EXECUTIONS ON REQUEST

- Handwheels with safety bushing GN 000.5 (see page 160).
- GN 323 handwheels with black epoxy resin coating, matte finish.
- Handwheels with keyway in compliance with ANSI B17.1-1967 tolerance. (see page A-16).

TECHNICAL DATA

Axial and radial runout lower than IT 12.



GN 321-A

Code	Description	d1	d2	d3	b	l1	l2	⚖
GN.925501	GN 321-80-B3/8-A	3.15	0.375	1.02	0.51	0.63	1.02	0.3
GN.925521	GN 321-100-B3/8-A	3.94	0.375	1.1	0.55	0.67	1.18	0.47
GN.925541	GN 321-125-B1/2-A	4.92	0.500	1.22	0.59	0.71	1.3	0.7
GN.925571	GN 321-140-B5/8-A	5.51	0.625	1.42	0.65	0.75	1.42	0.95
GN.925591	GN 321-160-B5/8-A	6.3	0.625	1.42	0.71	0.79	1.54	1.26
GN.925601	GN 321-200-B5/8-A	7.87	0.625	1.77	0.81	0.94	1.77	1.95
GN.925621	GN 321-250-B3/4-A	9.84	0.750	1.89	0.91	1.1	2.01	3.35

INCH

GN 321-R

Code	Description	d1	d2	d3	b	l1	l2	l3	r	d7	⚖
GN.925505	GN 321-80-B3/8-R	3.15	0.375	1.02	0.51	0.63	1.02	1.73	1.32	0.63	0.35
GN.925525	GN 321-100-B3/8-R	3.94	0.375	1.1	0.55	0.67	1.18	2.3	1.67	0.71	0.56
GN.925545	GN 321-125-B1/2-R	4.92	0.500	1.22	0.59	0.71	1.3	2.42	2.13	0.87	0.87
GN.925575	GN 321-140-B5/8-R	5.51	0.625	1.42	0.65	0.75	1.42	3.01	2.4	0.94	1.12
GN.925595	GN 321-160-B5/8-R	6.3	0.625	1.42	0.71	0.79	1.54	3.01	2.8	0.94	1.49
GN.925605	GN 321-200-B5/8-R	7.87	0.625	1.77	0.81	0.94	1.77	3.41	3.5	0.98	2.18
GN.925625	GN 321-250-B3/4-R	9.84	0.750	1.89	0.91	1.1	2.01	3.41	4.45	0.98	3.58

INCH

