



MATERIAL

Cast aluminium, fine sandblasted matte surface, turned and mirror-polished rim.

STANDARD EXECUTIONS

Standard reamed hole.

- **GN 322-A:** without handle.
- **GN 322-R:** with revolving handle in polyamide based (PA) technopolymer, black colour, matte finish.
- **GN 322.3:** with fold-away handle in polyamide based (PA) technopolymer, black colour, matte finish.

SPECIAL EXECUTIONS ON REQUEST


- Handwheels with safety GN 000.5 (see page 131).
- GN 324 handwheels with black epoxy resin coating, matte finish.
- GN 322.7 handwheels with automatic fold-away safety handle.
- Keyway in compliance with ANSI B17.1-1967 tolerance (see page A-16).

TECHNICAL DATA

Axial and radial runout lower than IT 12.





GN 322-A



INCH

GN 322-A

Code	Description	d1	d2	d3	b	l1	l2	⚖
GN.926101	GN 322-125-B1/2-A	4.92	0.500	1.22	0.59	0.71	1.3	0.76
GN.926113	GN 322-140-B5/8-A	5.51	0.625	1.42	0.65	0.75	1.42	0.96
GN.926121	GN 322-160-B5/8-A	6.3	0.625	1.42	0.71	0.79	1.54	1.17
GN.926131	GN 322-200-B5/8-A	7.87	0.625	1.65	0.81	0.94	1.77	1.96
GN.926141	GN 322-250-B3/4-A	9.84	0.750	1.89	0.91	1.1	2.01	3.26



GN 322-R

INCH

Code	Description	d1	d2	d3	b	l1	l2	l3	r	d7	⚖
GN.926105	GN 322-125-B1/2-R	4.92	0.500	1.22	0.59	0.71	1.3	2.42	2.13	0.87	0.84
GN.926117	GN 322-140-B5/8-R	5.51	0.625	1.42	0.65	0.75	1.42	3.01	2.4	0.94	1.03
GN.926125	GN 322-160-B5/8-R	6.3	0.625	1.42	0.71	0.79	1.54	3.01	2.8	0.94	1.4
GN.926135	GN 322-200-B5/8-R	7.87	0.625	1.65	0.81	0.94	1.77	3.41	3.5	0.98	2.19
GN.926145	GN 322-250-B3/4-R	9.84	0.750	1.89	0.91	1.1	2.01	3.41	4.45	0.98	3.52

GN 322.3

INCH

Code	Description	d1	d2	d3	b	l1	l2	l3	c	r	d7	⚖
GN.926205	GN 322.3-125-B1/2-R	4.92	0.500	1.22	0.96	0.71	1.73	2.36	0.26	1.97	0.87	1.03
GN.926225	GN 322.3-160-B5/8-R	6.3	0.625	1.42	0.98	0.79	1.85	2.95	0.26	2.66	0.94	1.54
GN.926235	GN 322.3-200-B5/8-R	7.87	0.625	1.65	0.98	0.94	2.07	3.35	0.3	3.31	0.98	2.15
GN.926245	GN 322.3-250-B3/4-R	9.84	0.750	1.89	1.04	1.1	2.4	3.35	0.47	4.37	0.98	3.06

