



BASE

Glass-fibre reinforced polyamide based (PA) technopolymer, black colour, matte finish.

ARTICULATED STEM

Threaded zinc-plated steel with regulation hexagon.

STANDARD EXECUTIONS

- **LS.A:** without no-slip disk.
- **LS.A-AS:** with NBR rubber no-slip disk, hardness 70 Shore A, supplied assembled to the base.

FEATURES

The particular assembling system of the no-slip disk to the base assures a perfect anchoring, preventing separation even in case of impact during transport or of adhesion (sticking) to the floor (see No-slip disks on page 1283).

ORDER INFORMATION

The levelling elements are supplied unassembled to make carriage and storage easier. The components (base and stem) are supplied in separate packing: less volume taken and better protection from scratches and dirt.

To order bases and stems separately, see:


- table of possible combinations Bases/Stems (see page 1291)
- the codes of the Bases (see page 1288)
- the codes of the Stems (see page 1290 INCH Stems).

ACCESSORIES ON REQUEST

Zinc-plated steel nut (see Nuts NT. on page 1283).



ELESA Original design




INCH

LS.A

LS.A-AS

Code	Description	Code	Description	D	d2A	L	L1#	I	l1	h	s	Articulation Ø	Max. limit static load* [lbF]	ΔΔ	ΔΔ#
90341221	LS.A-25-14-3/8-16x2	90346221	LS.A-25-14-AS-3/8-16x2	0.98	3/8-16	2.94	3.06	2.000	0.94	0.47	9/16	0.55	1120	0.11	0.11
90341231	LS.A-25-14-3/8-16x4	90346231	LS.A-25-14-AS-3/8-16x4	0.98	3/8-16	4.94	5.06	4.000	0.94	0.47	9/16	0.55	1120	0.22	0.22
90341235	LS.A-25-14-3/8-16x6	90346235	LS.A-25-14-AS-3/8-16x6	0.98	3/8-16	6.94	7.06	6.000	0.94	0.47	9/16	0.55	1120	0.3	0.31
90341321	LS.A-25-14-1/2-13x2	90346321	LS.A-25-14-AS-1/2-13x2	0.98	1/2-13	2.94	3.06	2.000	0.94	0.47	9/16	0.55	1120	0.12	0.13
90341331	LS.A-25-14-1/2-13x4	90346331	LS.A-25-14-AS-1/2-13x4	0.98	1/2-13	4.94	5.06	4.000	0.94	0.47	9/16	0.55	1120	0.21	0.22
90341335	LS.A-25-14-1/2-13x6	90346335	LS.A-25-14-AS-1/2-13x6	0.98	1/2-13	6.94	7.06	6.000	0.94	0.47	9/16	0.55	1120	0.32	0.33
90341523	LS.A-25-14-5/8-11x4	90346523	LS.A-25-14-AS-5/8-11x4	0.98	5/8-11	4.94	5.06	4.000	0.94	0.47	9/16	0.55	1120	0.23	0.24
90341541	LS.A-25-14-5/8-11x6	90346541	LS.A-25-14-AS-5/8-11x6	0.98	5/8-11	6.94	7.06	6.000	0.94	0.47	9/16	0.55	1120	0.34	0.35
90341565	LS.A-25-14-5/8-11x8	90346565	LS.A-25-14-AS-5/8-11x8	0.98	5/8-11	8.94	9.06	8.000	0.94	0.47	9/16	0.55	1120	0.43	0.44

* The max static load is the value above which the load applied to the element may cause some plastic material breakage, in particular conditions of use. Obviously, a factor that takes into consideration the importance and the safety level of the specific application must be applied to this value.



LS.A		LS.A-AS		INCH											
Code	Description	Code	Description	D	d2A	L	L1#	l	l1	h	s	Articulation Ø	Max. limit static load* [lbf]	⚖	⚖#
90342221	LS.A-32-14-3/8-16x2	90347221	LS.A-32-14-AS-3/8-16x2	1.26	3/8-16	2.98	3.1	2.000	0.98	0.59	9/16	0.55	1568	0.1	0.11
90342231	LS.A-32-14-3/8-16x4	90347231	LS.A-32-14-AS-3/8-16x4	1.26	3/8-16	4.98	5.1	4.000	0.98	0.59	9/16	0.55	1568	0.19	0.2
90342235	LS.A-32-14-3/8-16x6	90347235	LS.A-32-14-AS-3/8-16x6	1.26	3/8-16	6.98	7.1	6.000	0.98	0.59	9/16	0.55	1568	0.3	0.31
90342321	LS.A-32-14-1/2-13x2	90347321	LS.A-32-14-AS-1/2-13x2	1.26	1/2-13	2.98	3.1	2.000	0.98	0.59	9/16	0.55	1568	0.12	0.13
90342331	LS.A-32-14-1/2-13x4	90347331	LS.A-32-14-AS-1/2-13x4	1.26	1/2-13	4.98	5.1	4.000	0.98	0.59	9/16	0.55	1568	0.21	0.22
90342335	LS.A-32-14-1/2-13x6	90347335	LS.A-32-14-AS-1/2-13x6	1.26	1/2-13	6.98	7.1	6.000	0.98	0.59	9/16	0.55	1568	0.3	0.31
90342523	LS.A-32-14-5/8-11x4	90347523	LS.A-32-14-AS-5/8-11x4	1.26	5/8-11	4.98	5.1	4.000	0.98	0.59	5/8	0.55	1568	0.22	0.23
90342541	LS.A-32-14-5/8-11x6	90347541	LS.A-32-14-AS-5/8-11x6	1.26	5/8-11	6.98	7.1	6.000	0.98	0.59	5/8	0.55	1568	0.32	0.33
90342565	LS.A-32-14-5/8-11x8	90347565	LS.A-32-14-AS-5/8-11x8	1.26	5/8-11	8.98	9.1	8.000	0.98	0.59	5/8	0.55	1568	0.42	0.43
90343221	LS.A-40-14-3/8-16x2	90348221	LS.A-40-14-AS-3/8-16x2	1.57	3/8-16	2.98	3.1	2.000	0.98	0.67	9/16	0.55	2240	0.11	0.12
90343231	LS.A-40-14-3/8-16x4	90348231	LS.A-40-14-AS-3/8-16x4	1.57	3/8-16	4.98	5.1	4.000	0.98	0.67	9/16	0.55	2240	0.2	0.21
90343235	LS.A-40-14-3/8-16x6	90348235	LS.A-40-14-AS-3/8-16x6	1.57	3/8-16	6.98	7.1	6.000	0.98	0.67	9/16	0.55	2240	0.29	0.3
90343321	LS.A-40-14-1/2-13x2	90348321	LS.A-40-14-AS-1/2-13x2	1.57	1/2-13	2.98	3.1	2.000	0.98	0.67	9/16	0.55	2240	0.13	0.14
90343331	LS.A-40-14-1/2-13x4	90348331	LS.A-40-14-AS-1/2-13x4	1.57	1/2-13	4.98	5.1	4.000	0.98	0.67	9/16	0.55	2240	0.21	0.23
90343335	LS.A-40-14-1/2-13x6	90348335	LS.A-40-14-AS-1/2-13x6	1.57	1/2-13	6.98	7.1	6.000	0.98	0.67	9/16	0.55	2240	0.3	0.31
90343523	LS.A-40-14-5/8-11x4	90348523	LS.A-40-14-AS-5/8-11x4	1.57	5/8-11	4.98	5.1	4.000	0.98	0.67	5/8	0.55	2240	0.24	0.25
90343541	LS.A-40-14-5/8-11x6	90348541	LS.A-40-14-AS-5/8-11x6	1.57	5/8-11	6.98	7.1	6.000	0.98	0.67	5/8	0.55	2240	0.33	0.34
90343565	LS.A-40-14-5/8-11x8	90348565	LS.A-40-14-AS-5/8-11x8	1.57	5/8-11	8.98	9.1	8.000	0.98	0.67	5/8	0.55	2240	0.44	0.45
90344221	LS.A-50-14-3/8-16x2	90349221	LS.A-50-14-AS-3/8-16x2	1.97	3/8-16	3.06	3.18	2.000	1.06	0.75	9/16	0.55	2240	0.13	0.13
90344231	LS.A-50-14-3/8-16x4	90349231	LS.A-50-14-AS-3/8-16x4	1.97	3/8-16	5.07	5.19	4.000	1.06	0.75	9/16	0.55	2240	0.24	0.24
90344235	LS.A-50-14-3/8-16x6	90349235	LS.A-50-14-AS-3/8-16x6	1.97	3/8-16	7.06	7.18	6.000	1.06	0.75	9/16	0.55	2240	0.33	0.33
90344321	LS.A-50-14-1/2-13x2	90349321	LS.A-50-14-AS-1/2-13x2	1.97	1/2-13	3.06	3.18	2.000	1.06	0.75	9/16	0.55	2240	0.14	0.15
90344331	LS.A-50-14-1/2-13x4	90349331	LS.A-50-14-AS-1/2-13x4	1.97	1/2-13	5.06	5.18	4.000	1.06	0.75	9/16	0.55	2240	0.25	0.26
90344335	LS.A-50-14-1/2-13x6	90349335	LS.A-50-14-AS-1/2-13x6	1.97	1/2-13	7.06	7.18	6.000	1.06	0.75	9/16	0.55	2240	0.34	0.35
90344523	LS.A-50-14-5/8-11x4	90349523	LS.A-50-14-AS-5/8-11x4	1.97	5/8-11	5.06	5.18	4.000	1.06	0.75	5/8	0.55	2240	0.27	0.28
90344541	LS.A-50-14-5/8-11x6	90349541	LS.A-50-14-AS-5/8-11x6	1.97	5/8-11	7.06	7.18	6.000	1.06	0.75	9/16	0.55	2240	0.36	0.37
90344565	LS.A-50-14-5/8-11x8	90349565	LS.A-50-14-AS-5/8-11x8	1.97	5/8-11	9.06	9.18	8.000	1.06	0.75	9/16	0.55	2240	0.45	0.46

* The max static load is the value above which the load applied to the element may cause some plastic material breakage, in particular conditions of use. Obviously, a factor that takes into consideration the importance and the safety level of the specific application must be applied to this value.

