

- 1 
- 2 
- 3 
- 4 
- 5 
- 6 
- 7 
- 8 
- 9 
- 10 
- 11 
- 12 
- 13 
- 14 
- 15 
- 16 
- 17 
- 18 
- 19 

BASE

High-resilience polypropylene based (PP) technopolymer, black colour, matte finish.

ARTICULATED STEM

Threaded AISI 304 stainless steel with regulation hexagon.

STANDARD EXECUTIONS

- **LS.A-PP-SST**: without no-slip disk.
- **LS.A-AS-PP-SST**: with EPDM rubber no-slip disk, hardness 70 Shore A, supplied assembled to the base.

FEATURES AND APPLICATIONS

Polypropylene levelling elements are particularly suitable for those sectors where they can be in contact with chemical agents and/or for frequent washing with acidic or basic detergent solutions, such as in the chemical, process, pharmaceutical, food, textile and paper industry. The particular assembling system of the no-slip disk to the base assures a perfect anchoring, preventing separation even in case of impact during transport or of adhesion (sticking) to the floor (see No-slip disks on page 835).

ORDER INFORMATION

The levelling feet are supplied unassembled to make carriage and storage easier. The components (base and stem) are supplied in separate packing: less volume taken and better protection from scratches and dirt.

To order bases and stems separately, see:


- table of possible combinations Bases/Stems (see page 839)
- the codes of the Bases (see page 836)
- the codes of the Stems (see page 985).

ACCESSORIES ON REQUEST

AISI 304 stainless steel nut (see Nuts NT. on page 835).



ELESA Original design



LS.A-PP-SST


INOX STAINLESS STEEL INCH

Code	Description	D	d2A	L	l	l1	h	s	Articulation Ø	Max. limit static load* [lbf]	Load at breakage** [lbf]	⚖️
90373121	LS.A-40-PP-14-SST-3/8-16X2	1.57	3/8-16	2.98	2	0.98	0.67	9/16	0.55	449.62	2248.09	0.13
90373125	LS.A-40-PP-14-SST-3/8-16X4	1.57	3/8-16	4.98	4	0.98	0.67	9/16	0.55	449.62	2248.09	0.24
90373127	LS.A-40-PP-14-SST-3/8-16X6	1.57	3/8-16	6.98	6	0.98	0.67	9/16	0.55	449.62	2248.09	0.14
90373321	LS.A-40-PP-14-SST-1/2-13X2	1.57	1/2-13	2.98	2	0.98	0.67	9/16	0.55	449.62	2248.09	0.15
90373325	LS.A-40-PP-14-SST-1/2-13X4	1.57	1/2-13	4.98	4	0.98	0.67	9/16	0.55	449.62	2248.09	0.26
90373331	LS.A-40-PP-14-SST-1/2-13X6	1.57	1/2-13	6.98	6	0.98	0.67	9/16	0.55	449.62	2248.09	0.24
90373521	LS.A-40-PP-14-SST-5/8-11X4	1.57	5/8-11	4.98	4	0.98	0.67	5/8	0.55	449.62	2248.09	0.36
90373525	LS.A-40-PP-14-SST-5/8-11X6	1.57	5/8-11	6.98	6	0.98	0.67	5/8	0.55	449.62	2248.09	0.53
90373541	LS.A-40-PP-14-SST-5/8-11X8	1.57	5/8-11	8.98	8	0.98	0.67	5/8	0.55	449.62	2248.09	0.58
90374121	LS.A-50-PP-14-SST-3/8-16X2	1.97	3/8-16	3.06	2	1.06	0.75	9/16	0.55	472.10	2697.71	0.15
90374125	LS.A-50-PP-14-SST-3/8-16X4	1.97	3/8-16	5.06	4	1.06	0.75	9/16	0.55	472.10	2697.71	0.26
90374127	LS.A-50-PP-14-SST-3/8-16X6	1.97	3/8-16	7.06	6	1.06	0.75	9/16	0.55	472.10	2697.71	0.15
90374321	LS.A-50-PP-14-SST-1/2-13X2	1.97	1/2-13	3.06	2	1.06	0.75	9/16	0.55	472.10	2697.71	0.17
90374325	LS.A-50-PP-14-SST-1/2-13X4	1.97	1/2-13	5.06	4	1.06	0.75	9/16	0.55	472.10	2697.71	0.27
90374331	LS.A-50-PP-14-SST-1/2-13X6	1.97	1/2-13	7.06	6	1.06	0.75	9/16	0.55	472.10	2697.71	0.26
90374521	LS.A-50-PP-14-SST-5/8-11X4	1.97	5/8-11	5.06	4	1.06	0.75	5/8	0.55	472.10	2697.71	0.38
90374525	LS.A-50-PP-14-SST-5/8-11X6	1.97	5/8-11	7.06	6	1.06	0.75	5/8	0.55	472.10	2697.71	0.54
90374541	LS.A-50-PP-14-SST-5/8-11X8	1.97	5/8-11	9.06	8	1.06	0.75	5/8	0.55	472.10	2697.71	0.60
90375121	LS.A-60-PP-14-SST-3/8-16X2	2.36	3/8-16	3.34	2	1.34	0.94	9/16	0.55	517.06	3034.92	0.15
90375125	LS.A-60-PP-14-SST-3/8-16X4	2.36	3/8-16	5.34	4	1.34	0.94	9/16	0.55	517.06	3034.92	0.26
90375127	LS.A-60-PP-14-SST-3/8-16X6	2.36	3/8-16	7.34	6	1.34	0.94	9/16	0.55	517.06	3034.92	0.15
90375321	LS.A-60-PP-14-SST-1/2-13X2	2.36	1/2-13	3.34	2	1.34	0.94	9/16	0.55	517.06	3034.92	0.17
90375325	LS.A-60-PP-14-SST-1/2-13X4	2.36	1/2-13	5.34	4	1.34	0.94	9/16	0.55	517.06	3034.92	0.27
90375331	LS.A-60-PP-14-SST-1/2-13X6	2.36	1/2-13	7.34	6	1.34	0.94	9/16	0.55	517.06	3034.92	0.26
90375521	LS.A-60-PP-14-SST-5/8-11X4	2.36	5/8-11	5.34	4	1.34	0.94	5/8	0.55	517.06	3034.92	0.38
90375525	LS.A-60-PP-14-SST-5/8-11X6	2.36	5/8-11	7.34	6	1.34	0.94	5/8	0.55	517.06	3034.92	0.54
90375541	LS.A-60-PP-14-SST-5/8-11X8	2.36	5/8-11	9.34	8	1.34	0.94	5/8	0.55	517.06	3034.92	0.60

* Max static load: is the value above which the load applied to the element may cause some plastic material breakage, in particular conditions of use. Obviously, a factor that takes into consideration the importance and the safety level of the specific application must be applied to this value.

** Load at breakage: is the value above which the load applied to the element may quickly cause some plastic material breakage, in particular conditions of use.





LS.A-AS-PP-SST

Code	Description	D	d2A	L	L1	l	l1	h	s	Articulation Ø	Max. limit static load* [lbf]	Load at breakage** [lbf]	⚖️
90378121	LS.A-40-PP-14-AS-SST-3/8-16X2	1.57	3/8-16	2.98	3.10	2	0.98	0.67	9/16	0.55	449.62	2248.09	0.14
90378125	LS.A-40-PP-14-AS-SST-3/8-16X4	1.57	3/8-16	4.98	5.10	4	0.98	0.67	9/16	0.55	449.62	2248.09	0.25
90378127	LS.A-40-PP-14-AS-SST-3/8-16X6	1.57	3/8-16	6.98	7.10	6	0.98	0.67	9/16	0.55	449.62	2248.09	0.15
90378321	LS.A-40-PP-14-AS-SST-1/2-13X2	1.57	1/2-13	2.98	3.10	2	0.98	0.67	9/16	0.55	449.62	2248.09	0.16
90378325	LS.A-40-PP-14-AS-SST-1/2-13X4	1.57	1/2-13	4.98	5.10	4	0.98	0.67	9/16	0.55	449.62	2248.09	0.26
90378331	LS.A-40-PP-14-AS-SST-1/2-13X6	1.57	1/2-13	6.98	7.10	6	0.98	0.67	9/16	0.55	449.62	2248.09	0.25
90378521	LS.A-40-PP-14-AS-SST-5/8-11X4	1.57	5/8-11	4.98	5.10	4	0.98	0.67	5/8	0.55	449.62	2248.09	0.37
90378525	LS.A-40-PP-14-AS-SST-5/8-11X6	1.57	5/8-11	6.98	7.10	6	0.98	0.67	5/8	0.55	449.62	2248.09	0.54
90378541	LS.A-40-PP-14-AS-SST-5/8-11X8	1.57	5/8-11	8.98	9.10	8	0.98	0.67	5/8	0.55	449.62	2248.09	0.59
90379121	LS.A-50-PP-14-AS-SST-3/8-16X2	1.97	3/8-16	3.06	3.18	2	1.06	0.75	9/16	0.55	472.10	2697.71	0.17
90379125	LS.A-50-PP-14-AS-SST-3/8-16X4	1.97	3/8-16	5.06	5.18	4	1.06	0.75	9/16	0.55	472.10	2697.71	0.27
90379127	LS.A-50-PP-14-AS-SST-3/8-16X6	1.97	3/8-16	7.06	7.18	6	1.06	0.75	9/16	0.55	472.10	2697.71	0.17
90379321	LS.A-50-PP-14-AS-SST-1/2-13X2	1.97	1/2-13	3.06	3.18	2	1.06	0.75	9/16	0.55	472.10	2697.71	0.19
90379325	LS.A-50-PP-14-AS-SST-1/2-13X4	1.97	1/2-13	5.06	5.18	4	1.06	0.75	9/16	0.55	472.10	2697.71	0.29
90379331	LS.A-50-PP-14-AS-SST-1/2-13X6	1.97	1/2-13	7.06	7.18	6	1.06	0.75	9/16	0.55	472.10	2697.71	0.27
90379521	LS.A-50-PP-14-AS-SST-5/8-11X4	1.97	5/8-11	5.06	5.18	4	1.06	0.75	5/8	0.55	472.10	2697.71	0.39
90379525	LS.A-50-PP-14-AS-SST-5/8-11X6	1.97	5/8-11	7.06	7.18	6	1.06	0.75	5/8	0.55	472.10	2697.71	0.56
90379541	LS.A-50-PP-14-AS-SST-5/8-11X8	1.97	5/8-11	9.06	9.18	8	1.06	0.75	5/8	0.55	472.10	2697.71	0.62
90380121	LS.A-60-PP-14-AS-SST-3/8-16X2	2.36	3/8-16	3.34	3.46	2	1.34	0.94	9/16	0.55	517.06	3034.92	0.19
90380125	LS.A-60-PP-14-AS-SST-3/8-16X4	2.36	3/8-16	5.34	5.46	4	1.34	0.94	9/16	0.55	517.06	3034.92	0.30
90380127	LS.A-60-PP-14-AS-SST-3/8-16X6	2.36	3/8-16	7.34	7.46	6	1.34	0.94	9/16	0.55	517.06	3034.92	0.20
90380321	LS.A-60-PP-14-AS-SST-1/2-13X2	2.36	1/2-13	3.34	3.46	2	1.34	0.94	9/16	0.55	517.06	3034.92	0.21
90380325	LS.A-60-PP-14-AS-SST-1/2-13X4	2.36	1/2-13	5.34	5.46	4	1.34	0.94	9/16	0.55	517.06	3034.92	0.32
90380331	LS.A-60-PP-14-AS-SST-1/2-13X6	2.36	1/2-13	7.34	7.46	6	1.34	0.94	9/16	0.55	517.06	3034.92	0.30
90380521	LS.A-60-PP-14-AS-SST-5/8-11X4	2.36	5/8-11	5.34	5.46	4	1.34	0.94	5/8	0.55	517.06	3034.92	0.42
90380525	LS.A-60-PP-14-AS-SST-5/8-11X6	2.36	5/8-11	7.34	7.46	6	1.34	0.94	5/8	0.55	517.06	3034.92	0.59
90380541	LS.A-60-PP-14-AS-SST-5/8-11X8	2.36	5/8-11	9.34	9.46	8	1.34	0.94	5/8	0.55	517.06	3034.92	0.64

* Max static load: is the value above which the load applied to the element may cause some plastic material breakage, in particular conditions of use. Obviously, a factor that takes into consideration the importance and the safety level of the specific application must be applied to this value.

** Load at breakage: is the value above which the load applied to the element may quickly cause some plastic material breakage, in particular conditions of use.