

THREADED BODY

Black-oxide steel.

PLUNGER

Black-oxide steel with hardened end.

Suggested tolerance for matching hole = H7.

LOCKING NUT

Black-oxide steel.

KNOB




High-resilience polyamide based (PA) technopolymer, black colour, matte finish.

STANDARD EXECUTIONS

- **GN 617.1-A:** with knob, without locking nut.
- **GN 617.1-AK:** with knob and locking nut.

ACCESSORIES ON REQUEST

AISI 303 stainless steel distance bushings GN 609.5 GN 609.5 (see page 1030) for assembling the plunger on thin sheets.



Code	Description	d1 -0008 -.0015	d2 2A	d3	e	l1	l2	l3	l4	l5	sw	Spring pressure Preload [lbf]	Spring pressure Max. load [lbf]	⚖
GN.935501	GN 617.1-5-3/8-24-A	0.2	3/8-24	0.83	0.54	2.01	0.2	0.67	0.2	0.59	0.47	2	4	0.05
GN.935511	GN 617.1-6-1/2-13-A	0.24	1/2-13	0.98	0.64	2.4	0.24	0.79	0.24	0.67	0.55	2	5	0.07
GN.935521	GN 617.1-8-5/8-11-A	0.31	5/8-11	1.22	0.86	2.97	0.28	1.02	0.28	0.91	0.75	2	7	0.17
GN.935502	GN 617.1-5-3/8-24-AK	0.2	3/8-24	0.83	0.54	2.01	0.2	0.67	0.2	0.59	0.47	2	4	0.07
GN.935512	GN 617.1-6-1/2-13-AK	0.24	1/2-13	0.98	0.64	2.4	0.24	0.79	0.24	0.67	0.55	2	5	0.11
GN.935522	GN 617.1-8-5/8-11-AK	0.31	5/8-11	1.22	0.86	2.97	0.28	1.02	0.28	0.91	0.75	2	7	0.2