

1	BASE
2	ARTICULATED STEM
3	STANDARD EXECUTIONS
4	FEATURES
5	ORDER INFORMATION
6	ACCESSORIES ON REQUEST
7	
8	
9	
10	
11	
12	
13	
14	
15	
16	
17	
18	
19	

BASE

Glass-fibre reinforced polyamide based (PA) technopolymer, black colour, matte finish.

ARTICULATED STEM

Threaded AISI 304 stainless steel with regulation hexagon.

STANDARD EXECUTIONS

- **LSQ.A-SST**: without no-slip disk.
- **LSQ.A-AS-SST**: with NBR rubber no-slip disk, hardness 70 Shore A, supplied assembled to the base.

FEATURES

The particular assembling system of the no-slip disk to the base assures a perfect anchoring, preventing separation even in case of impact during transport or of adhesion (sticking) to the floor (see No-slip disks on page 979).

ORDER INFORMATION


The levelling elements are supplied unassembled to make carriage and storage easier. The components (base and stem) are supplied in separate packing: less volume taken and better protection from scratches and dirt.

To order bases and stems separately, see:


- table of possible combinations Bases/Stems (see page 983)
- the codes of the Bases (see page 980)
- the codes of the Stems (see page 985).

ACCESSORIES ON REQUEST

AISI 304 stainless steel nut (see Nuts NT. on page 979).



ELESA Original design





LSQ.A-SST

INOX STAINLESS STEEL INCH

Code	Description	D	d2A	L	I	I1	I2	h	s	Articulation Ø	Max. limit static load* [lbf]	⚖
90360001	LSQ.A-25-8.5-SST-1/2-13x3	0.98	1/2-13	3.79	3	0.79	0.73	0.47	3/8	0.33	1124.04	0.16
90360003	LSQ.A-25-8.5-SST-1/2-13x4	0.98	1/2-13	4.79	4	0.79	0.73	0.47	3/8	0.33	1124.04	0.16
90360005	LSQ.A-25-8.5-SST-1/2-13x6	0.98	1/2-13	6.79	6	0.79	0.73	0.47	3/8	0.33	1124.04	0.16
90360033	LSQ.A-25-14-SST-5/8-11x4	0.98	5/8-11	4.94	4	0.94	0.89	0.47	1/2	0.55	1124.04	0.35
90360035	LSQ.A-25-14-SST-5/8-11x6	0.98	5/8-11	6.94	6	0.94	0.89	0.47	1/2	0.55	1124.04	0.53
90360037	LSQ.A-25-14-SST-5/8-11x8	0.98	5/8-11	8.94	8	0.94	0.89	0.47	1/2	0.55	1124.04	0.16
90360032	LSQ.A-25-14-SST-3/4-10X4	0.98	3/4-10	4.94	4	0.94	0.89	0.47	9/16	0.55	1124.04	0.16
90360034	LSQ.A-25-14-SST-3/4-10X6	0.98	3/4-10	6.94	6	0.94	0.89	0.47	9/16	0.55	1124.04	0.16
90360038	LSQ.A-25-14-SST-3/4-10X8	0.98	3/4-10	8.94	8	0.94	0.89	0.47	9/16	0.55	1124.04	0.16
90360101	LSQ.A-32-8.5-SST-1/2-13x3	1.26	1/2-13	3.91	3	0.91	0.85	0.59	3/8	0.33	1348.85	0.17
90360103	LSQ.A-32-8.5-SST-1/2-13x4	1.26	1/2-13	4.91	4	0.91	0.85	0.59	3/8	0.33	1348.85	0.17
90360105	LSQ.A-32-8.5-SST-1/2-13x6	1.26	1/2-13	6.91	6	0.91	0.85	0.59	3/8	0.33	1348.85	0.17
90360133	LSQ.A-32-14-SST-5/8-11x4	1.26	5/8-11	4.94	4	0.94	0.89	0.59	5/8	0.55	1573.66	0.37
90360135	LSQ.A-32-14-SST-5/8-11x6	1.26	5/8-11	6.94	6	0.94	0.89	0.59	5/8	0.55	1573.66	0.54
90360137	LSQ.A-32-14-SST-5/8-11x8	1.26	5/8-11	8.94	8	0.94	0.89	0.59	5/8	0.55	1573.66	0.17
90360131	LSQ.A-32-14-SST-3/4-10X4	1.26	3/4-10	4.94	4	0.94	0.89	0.59	9/16	0.55	1573.66	0.17
90360134	LSQ.A-32-14-SST-3/4-10X6	1.26	3/4-10	6.94	6	0.94	0.89	0.59	9/16	0.55	1573.66	0.17
90360136	LSQ.A-32-14-SST-3/4-10X8	1.26	3/4-10	8.94	8	0.94	0.89	0.59	9/16	0.55	1573.66	0.17
90360201	LSQ.A-40-8.5-SST-1/2-13x3	1.57	1/2-13	3.98	3	0.98	0.93	0.67	3/8	0.33	1573.66	0.18
90360203	LSQ.A-40-8.5-SST-1/2-13x4	1.57	1/2-13	4.98	4	0.98	0.93	0.67	3/8	0.33	1573.66	0.18
90360205	LSQ.A-40-8.5-SST-1/2-13x6	1.57	1/2-13	6.98	6	0.98	0.93	0.67	3/8	0.33	1573.66	0.18
90360233	LSQ.A-40-14-SST-5/8-11x4	1.57	5/8-11	4.98	4	0.98	0.93	0.67	5/8	0.55	2248.09	0.38
90360235	LSQ.A-40-14-SST-5/8-11x6	1.57	5/8-11	6.98	6	0.98	0.93	0.67	5/8	0.55	2248.09	0.55
90360237	LSQ.A-40-14-SST-5/8-11x8	1.57	5/8-11	8.98	8	0.98	0.93	0.67	5/8	0.55	2248.09	0.18
90360232	LSQ.A-40-14-SST-3/4-10X4	1.57	3/4-10	4.98	4	0.98	0.93	0.67	9/16	0.55	2248.09	0.18
90360234	LSQ.A-40-14-SST-3/4-10X6	1.57	3/4-10	6.98	6	0.98	0.93	0.67	9/16	0.55	2248.09	0.18
90360236	LSQ.A-40-14-SST-3/4-10X8	1.57	3/4-10	8.98	8	0.98	0.93	0.67	9/16	0.55	2248.09	0.18
90360301	LSQ.A-50-8.5-SST-1/2-13x3	1.97	1/2-13	4.06	3	1.06	1.00	0.75	3/8	0.33	1573.66	0.20
90360303	LSQ.A-50-8.5-SST-1/2-13x4	1.97	1/2-13	5.06	4	1.06	1.00	0.75	3/8	0.33	1573.66	0.20
90360305	LSQ.A-50-8.5-SST-1/2-13x6	1.97	1/2-13	7.06	6	1.06	1.00	0.75	3/8	0.33	1573.66	0.20
90360333	LSQ.A-50-14-SST-5/8-11x4	1.97	5/8-11	5.06	4	1.06	1.00	0.75	5/8	0.55	2248.09	0.39
90360335	LSQ.A-50-14-SST-5/8-11x6	1.97	5/8-11	7.06	6	1.06	1.00	0.75	5/8	0.55	2248.09	0.57
90360337	LSQ.A-50-14-SST-5/8-11x8	1.97	5/8-11	9.06	8	1.06	1.00	0.75	5/8	0.55	2248.09	0.19
90360332	LSQ.A-50-14-SST-3/4-10X4	1.97	3/4-10	5.06	4	1.06	1.00	0.75	9/16	0.55	2248.09	0.19
90360334	LSQ.A-50-14-SST-3/4-10X6	1.97	3/4-10	7.06	6	1.06	1.00	0.75	9/16	0.55	2248.09	0.19
90360336	LSQ.A-50-14-SST-3/4-10X8	1.97	3/4-10	9.06	8	1.06	1.00	0.75	9/16	0.55	2248.09	0.19
90360391	LSQ.A-60-14-SST-5/8-11X4	2.36	5/8-11	5.42	4	1.42	1.36	0.94	5/8	0.55	3147.33	0.42
90360393	LSQ.A-60-14-SST-5/8-11X6	2.36	5/8-11	7.42	6	1.42	1.36	0.94	5/8	0.55	3147.33	0.60
90360401	LSQ.A-60-14-SST-5/8-11X8	2.36	5/8-11	9.42	8	1.42	1.36	0.94	5/8	0.55	3147.33	0.22
90360405	LSQ.A-60-14-SST-3/4-10X4	2.36	3/4-10	5.61	4	1.61	1.52	0.94	9/16	0.55	3147.33	0.22
90360411	LSQ.A-60-14-SST-3/4-10X6	2.36	3/4-10	7.61	6	1.61	1.52	0.94	9/16	0.55	3147.33	0.22
90360413	LSQ.A-60-14-SST-3/4-10X8	2.36	3/4-10	9.61	8	1.61	1.52	0.94	9/16	0.55	3147.33	0.22

* The max static load is the value above which the load applied to the element may cause some plastic material breakage, in particular conditions of use. Obviously, a factor that takes into consideration the importance and the safety level of the specific application must be applied to this value.





LSQ.A-AS-SST



Code	Description	D	d2A	L	L1	l	l1	l2	h	s	Articulation Ø	Max. limit static load* [lbf]	⚖️
90360501	LSQ.A-25-8.5-AS-SST-1/2-13x3	0.98	1/2-13	3.79	3.91	3	0.79	0.73	0.47	3/8	0.33	1124.04	0.17
90360503	LSQ.A-25-8.5-AS-SST-1/2-13x4	0.98	1/2-13	4.79	4.91	4	0.79	0.73	0.47	3/8	0.33	1124.04	0.17
90360505	LSQ.A-25-8.5-AS-SST-1/2-13x6	0.98	1/2-13	6.79	6.91	6	0.79	0.73	0.47	3/8	0.33	1124.04	0.17
90360533	LSQ.A-25-14-AS-SST-5/8-11x4	0.98	5/8-11	4.94	5.06	4	0.94	0.89	0.47	1/2	0.55	1124.04	0.36
90360535	LSQ.A-25-14-AS-SST-5/8-11x6	0.98	5/8-11	6.94	7.06	6	0.94	0.89	0.47	1/2	0.55	1124.04	0.54
90360537	LSQ.A-25-14-AS-SST-5/8-11x8	0.98	5/8-11	8.94	9.06	8	0.94	0.89	0.47	1/2	0.55	1124.04	0.16
90360532	LSQ.A-25-14-AS-SST-3/4-10X4	0.98	3/4-10	4.94	5.06	4	0.94	0.89	0.47	9/16	0.55	1124.04	0.16
90360534	LSQ.A-25-14-AS-SST-3/4-10X6	0.98	3/4-10	6.94	7.06	6	0.94	0.89	0.47	9/16	0.55	1124.04	0.16
90360536	LSQ.A-25-14-AS-SST-3/4-10X8	0.98	3/4-10	8.94	9.06	8	0.94	0.89	0.47	9/16	0.55	1124.04	0.16
90360601	LSQ.A-32-8.5-AS-SST-1/2-13x3	1.26	1/2-13	3.91	4.42	3	0.91	0.85	0.59	3/8	0.33	1348.85	0.18
90360603	LSQ.A-32-8.5-AS-SST-1/2-13x4	1.26	1/2-13	4.91	5.02	4	0.91	0.85	0.59	3/8	0.33	1348.85	0.18
90360605	LSQ.A-32-8.5-AS-SST-1/2-13x6	1.26	1/2-13	6.91	7.02	6	0.91	0.85	0.59	3/8	0.33	1348.85	0.18
90360633	LSQ.A-32-14-AS-SST-5/8-11x4	1.26	5/8-11	4.94	5.06	4	0.94	0.89	0.59	5/8	0.55	1573.66	0.37
90360635	LSQ.A-32-14-AS-SST-5/8-11x6	1.26	5/8-11	6.94	7.06	6	0.94	0.89	0.59	5/8	0.55	1573.66	0.55
90360637	LSQ.A-32-14-AS-SST-5/8-11x8	1.26	5/8-11	8.94	9.06	8	0.94	0.89	0.59	5/8	0.55	1573.66	0.18
90360632	LSQ.A-32-14-AS-SST-3/4-10X4	1.26	3/4-10	4.94	5.06	4	0.94	0.89	0.59	9/16	0.55	1573.66	0.18
90360634	LSQ.A-32-14-AS-SST-3/4-10X6	1.26	3/4-10	6.94	7.06	6	0.94	0.89	0.59	9/16	0.55	1573.66	0.18
90360636	LSQ.A-32-14-AS-SST-3/4-10X8	1.26	3/4-10	8.94	9.06	8	0.94	0.89	0.59	9/16	0.55	1573.66	0.18
90360701	LSQ.A-40-8.5-AS-SST-1/2-13x3	1.57	1/2-13	3.98	4.10	3	0.98	0.93	0.67	3/8	0.33	1573.66	0.19
90360703	LSQ.A-40-8.5-AS-SST-1/2-13x4	1.57	1/2-13	4.98	5.10	4	0.98	0.93	0.67	3/8	0.33	1573.66	0.19
90360705	LSQ.A-40-8.5-AS-SST-1/2-13x6	1.57	1/2-13	6.98	7.10	6	0.98	0.93	0.67	3/8	0.33	1573.66	0.19
90360733	LSQ.A-40-14-AS-SST-5/8-11x4	1.57	5/8-11	4.98	5.10	4	0.98	0.93	0.67	5/8	0.55	2248.09	0.39
90360735	LSQ.A-40-14-AS-SST-5/8-11x6	1.57	5/8-11	6.98	7.10	6	0.98	0.93	0.67	5/8	0.55	2248.09	0.57
90360737	LSQ.A-40-14-AS-SST-5/8-11x8	1.57	5/8-11	8.98	9.10	8	0.98	0.93	0.67	5/8	0.55	2248.09	0.19
90360732	LSQ.A-40-14-AS-SST-3/4-10X4	1.57	3/4-10	4.98	5.10	4	0.98	0.93	0.67	9/16	0.55	2248.09	0.20
90360734	LSQ.A-40-14-AS-SST-3/4-10X6	1.57	3/4-10	6.98	7.10	6	0.98	0.93	0.67	9/16	0.55	2248.09	0.20
90360736	LSQ.A-40-14-AS-SST-3/4-10X8	1.57	3/4-10	8.98	9.10	8	0.98	0.93	0.67	9/16	0.55	2248.09	0.20
90360801	LSQ.A-50-8.5-AS-SST-1/2-13x3	1.97	1/2-13	4.06	4.18	3	1.06	1.00	0.75	3/8	0.33	1573.66	0.22
90360803	LSQ.A-50-8.5-AS-SST-1/2-13x4	1.97	1/2-13	5.06	5.18	4	1.06	1.00	0.75	3/8	0.33	1573.66	0.22
90360805	LSQ.A-50-8.5-AS-SST-1/2-13x6	1.97	1/2-13	7.06	7.18	6	1.06	1.00	0.75	3/8	0.33	1573.66	0.22
90360833	LSQ.A-50-14-AS-SST-5/8-11x4	1.97	5/8-11	5.06	5.18	4	1.06	1.00	0.75	5/8	0.55	2248.09	0.41
90360835	LSQ.A-50-14-AS-SST-5/8-11x6	1.97	5/8-11	7.06	7.18	6	1.06	1.00	0.75	5/8	0.55	2248.09	0.59
90360837	LSQ.A-50-14-AS-SST-5/8-11x8	1.97	5/8-11	9.06	9.18	8	1.06	1.00	0.75	5/8	0.55	2248.09	0.22
90360831	LSQ.A-50-14-AS-SST-3/4-10X4	1.97	3/4-10	5.06	5.18	4	1.06	1.00	0.75	9/16	0.55	2248.09	0.22
90360834	LSQ.A-50-14-AS-SST-3/4-10X6	1.97	3/4-10	7.06	7.18	6	1.06	1.00	0.75	9/16	0.55	2248.09	0.22
90360836	LSQ.A-50-14-AS-SST-3/4-10X8	1.97	3/4-10	9.06	9.18	8	1.06	1.00	0.75	9/16	0.55	2248.09	0.22
90360891	LSQ.A-60-14-AS-SST-5/8-11X4	2.36	5/8-11	5.42	5.54	4	1.42	1.36	0.94	5/8	0.55	3147.33	0.45
90360893	LSQ.A-60-14-AS-SST-5/8-11X6	2.36	5/8-11	7.42	7.54	6	1.42	1.36	0.94	5/8	0.55	3147.33	0.63
90360901	LSQ.A-60-14-AS-SST-5/8-11X8	2.36	5/8-11	9.42	9.54	8	1.42	1.36	0.94	5/8	0.55	3147.33	0.26
90360905	LSQ.A-60-14-AS-SST-3/4-10X4	2.36	3/4-10	5.61	5.73	4	1.61	1.52	0.94	9/16	0.55	3147.33	0.26
90360911	LSQ.A-60-14-AS-SST-3/4-10X6	2.36	3/4-10	7.61	7.73	6	1.61	1.52	0.94	9/16	0.55	3147.33	0.26
90360913	LSQ.A-60-14-AS-SST-3/4-10X8	2.36	3/4-10	9.61	9.73	8	1.61	1.52	0.94	9/16	0.55	3147.33	0.26

* The max static load is the value above which the load applied to the element may cause some plastic material breakage, in particular conditions of use. Obviously, a factor that takes into consideration the importance and the safety level of the specific application must be applied to this value.