




















- 1 
- 2 
- 3 
- 4 
- 5 
- 6 
- 7 
- 8 
- 9 
- 10 
- 11 
- 12 
- 13 
- 14 
- 15 
- 16 
- 17 
- 18 
- 19 

**BASE**

Glass-fibre reinforced polyamide based (PA) technopolymer, RAL 5005 blue colour, matte finish.  
Produced from FDA compliant raw material (FDA CFR.21 and EU 10/2011).

**ARTICULATED STEM**

Threaded AISI 304 stainless steel with regulation hexagon.

**STANDARD EXECUTIONS**

- **LSQ.A-SST-VD**: without no-slip disk.
- **LSQ.A-AS-SST-VD**: with NBR rubber no-slip disk, hardness 70 Shore A, supplied assembled to the base.

**FEATURES AND APPLICATIONS**

The RAL 5005 blue colour is easily visible in case of accidental food contamination.

The particular assembling system of the no-slip disk to the base assures a perfect anchoring, preventing separation even in case of impact during transport or of adhesion (sticking) to the floor (see No-slip disks on page 979).

**ORDER INFORMATION**

The levelling elements are supplied unassembled to make carriage and storage easier. The components (base and stem) are supplied in separate packing: less volume taken and better protection from scratches and dirt.

To order bases and stems separately, see:


- table of possible combinations Bases/Stems (see page 983)
- the codes of the Bases (see page 980)
- the codes of the Stems (see page 985).

**ACCESSORIES ON REQUEST**

AISI 304 stainless steel nut (see Nuts NT. on page 979).



ELESA Original design



LSQ.A-SST-VD


Code	Description	D	d2A	L	l	l1	l2	h	s	Articulation ∅	Max. limit static load* [lb]	⚖️
90187081	LSQ.A-25-8,5-SST-1/2-13X3-VD	0.98	1/2-13	3.79	3	0.79	0.73	0.47	3/8	0.33	1124.04	0.16
90187083	LSQ.A-25-8,5-SST-1/2-13X4-VD	0.98	1/2-13	4.79	4	0.79	0.73	0.47	3/8	0.33	1124.04	0.16
90187085	LSQ.A-25-8,5-SST-1/2-13X6-VD	0.98	1/2-13	6.79	6	0.79	0.73	0.47	3/8	0.33	1124.04	0.16
90187152	LSQ.A-25-14-SST-5/8-11X4-VD	0.98	5/8-11	4.94	4	0.94	0.89	0.47	1/2	0.55	1124.04	0.35
90187154	LSQ.A-25-14-SST-5/8-11X6-VD	0.98	5/8-11	6.94	6	0.94	0.89	0.47	1/2	0.55	1124.04	0.53
90187156	LSQ.A-25-14-SST-5/8-11X8-VD	0.98	5/8-11	8.94	8	0.94	0.89	0.47	1/2	0.55	1124.04	0.16
90187151	LSQ.A-25-14-SST-3/4-10X4-VD	0.98	3/4-10	4.94	4	0.94	0.89	0.47	9/16	0.55	1124.04	0.16
90187153	LSQ.A-25-14-SST-3/4-10X6-VD	0.98	3/4-10	6.94	6	0.94	0.89	0.47	9/16	0.55	1124.04	0.16
90187155	LSQ.A-25-14-SST-3/4-10X8-VD	0.98	3/4-10	8.94	8	0.94	0.89	0.47	9/16	0.55	1124.04	0.16
90187181	LSQ.A-32-8,5-SST-1/2-13X3-VD	1.26	1/2-13	3.91	3	0.91	0.85	0.59	3/8	0.33	1348.85	0.17
90187183	LSQ.A-32-8,5-SST-1/2-13X4-VD	1.26	1/2-13	4.91	4	0.91	0.85	0.59	3/8	0.33	1348.85	0.17
90187185	LSQ.A-32-8,5-SST-1/2-13X6-VD	1.26	1/2-13	6.91	6	0.91	0.85	0.59	3/8	0.33	1348.85	0.17
90187231	LSQ.A-32-14-SST-5/8-11X4-VD	1.26	5/8-11	4.94	4	0.94	0.89	0.59	5/8	0.55	1573.66	0.36
90187233	LSQ.A-32-14-SST-5/8-11X6-VD	1.26	5/8-11	6.94	6	0.94	0.89	0.59	5/8	0.55	1573.66	0.54
90187235	LSQ.A-32-14-SST-5/8-11X8-VD	1.26	5/8-11	8.94	8	0.94	0.89	0.59	5/8	0.55	1573.66	0.17
90187241	LSQ.A-32-14-SST-3/4-10X4-VD	1.26	3/4-10	4.94	4	0.94	0.89	0.59	9/16	0.55	1573.66	0.17
90187242	LSQ.A-32-14-SST-3/4-10X6-VD	1.26	3/4-10	6.94	6	0.94	0.89	0.59	9/16	0.55	1573.66	0.17
90187243	LSQ.A-32-14-SST-3/4-10X8-VD	1.26	3/4-10	8.94	8	0.94	0.89	0.59	9/16	0.55	1573.66	0.17
90187281	LSQ.A-40-8,5-SST-1/2-13X3-VD	1.57	1/2-13	3.98	3	0.98	0.93	0.67	3/8	0.33	1573.66	0.18
90187283	LSQ.A-40-8,5-SST-1/2-13X4-VD	1.57	1/2-13	4.98	4	0.98	0.93	0.67	3/8	0.33	1573.66	0.18
90187285	LSQ.A-40-8,5-SST-1/2-13X6-VD	1.57	1/2-13	6.98	6	0.98	0.93	0.67	3/8	0.33	1573.66	0.18
90187351	LSQ.A-40-14-SST-5/8-11X4-VD	1.57	5/8-11	4.98	4	0.98	0.93	0.67	5/8	0.55	2248.09	0.38
90187353	LSQ.A-40-14-SST-5/8-11X6-VD	1.57	5/8-11	6.98	6	0.98	0.93	0.67	5/8	0.55	2248.09	0.55
90187355	LSQ.A-40-14-SST-5/8-11X8-VD	1.57	5/8-11	8.98	8	0.98	0.93	0.67	5/8	0.55	2248.09	0.18
90187361	LSQ.A-40-14-SST-3/4-10X4-VD	1.57	3/4-10	4.98	4	0.98	0.93	0.67	9/16	0.55	2248.09	0.18
90187363	LSQ.A-40-14-SST-3/4-10X6-VD	1.57	3/4-10	6.98	6	0.98	0.93	0.67	9/16	0.55	2248.09	0.18
90187365	LSQ.A-40-14-SST-3/4-10X8-VD	1.57	3/4-10	8.98	8	0.98	0.93	0.67	9/16	0.55	2248.09	0.18
90187381	LSQ.A-50-8,5-SST-1/2-13X3-VD	1.97	1/2-13	4.06	3	1.06	1.00	0.75	3/8	0.33	1573.66	0.19
90187383	LSQ.A-50-8,5-SST-1/2-13X4-VD	1.97	1/2-13	5.06	4	1.06	1.00	0.75	3/8	0.33	1573.66	0.19
90187385	LSQ.A-50-8,5-SST-1/2-13X6-VD	1.97	1/2-13	7.06	6	1.06	1.00	0.75	3/8	0.33	1573.66	0.19
90187451	LSQ.A-50-14-SST-5/8-11X4-VD	1.97	5/8-11	5.06	4	1.06	1.00	0.75	5/8	0.55	2248.09	0.39
90187453	LSQ.A-50-14-SST-5/8-11X6-VD	1.97	5/8-11	7.06	6	1.06	1.00	0.75	5/8	0.55	2248.09	0.56
90187455	LSQ.A-50-14-SST-5/8-11X8-VD	1.97	5/8-11	9.06	8	1.06	1.00	0.75	5/8	0.55	2248.09	0.19
90187461	LSQ.A-50-14-SST-3/4-10X4-VD	1.97	3/4-10	5.06	4	1.06	1.00	0.75	9/16	0.55	2248.09	0.19
90187463	LSQ.A-50-14-SST-3/4-10X6-VD	1.97	3/4-10	7.06	6	1.06	1.00	0.75	9/16	0.55	2248.09	0.19
90187465	LSQ.A-50-14-SST-3/4-10X8-VD	1.97	3/4-10	9.06	8	1.06	1.00	0.75	9/16	0.55	2248.09	0.19
90187581	LSQ.A-60-14-SST-5/8-11X4-VD	2.36	5/8-11	5.42	4	1.42	1.36	0.94	5/8	0.55	3147.33	0.42
90187583	LSQ.A-60-14-SST-5/8-11X6-VD	2.36	5/8-11	7.42	6	1.42	1.36	0.94	5/8	0.55	3147.33	0.60
90187585	LSQ.A-60-14-SST-5/8-11X8-VD	2.36	5/8-11	9.42	8	1.42	1.36	0.94	5/8	0.55	3147.33	0.22
90187591	LSQ.A-60-14-SST-3/4-10X4-VD	2.36	3/4-10	5.61	4	1.61	1.52	0.94	9/16	0.55	3147.33	0.22
90187593	LSQ.A-60-14-SST-3/4-10X6-VD	2.36	3/4-10	7.61	6	1.61	1.52	0.94	9/16	0.55	3147.33	0.22
90187595	LSQ.A-60-14-SST-3/4-10X8-VD	2.36	3/4-10	9.61	8	1.61	1.52	0.94	9/16	0.55	3147.33	0.22

\* The max static load is the value above which the load applied to the element may cause some plastic material breakage, in particular conditions of use. Obviously, a factor that takes into consideration the importance and the safety level of the specific application must be applied to this value.



Levelling elements and supports

- 1
- 2
- 3
- 4
- 5
- 6
- 7
- 8
- 9
- 10
- 11
- 12
- 13
- 14
- 15
- 16
- 17
- 18
- 19



LSQ.A-AS-SST-VD

Code	Description	D	d2A	L	L1	l	l1	l2	h	s	Articulation Ø	Max. limit static load* [lbf]	Δ
90188081	LSQ.A-25-8,5-AS-SST-1/2-13X3-VD	0.98	1/2-13	3.79	3.91	3	0.79	0.73	0.47	3/8	0.33	1124.04	0.16
90188083	LSQ.A-25-8,5-AS-SST-1/2-13X4-VD	0.98	1/2-13	4.79	4.91	4	0.79	0.73	0.47	3/8	0.33	1124.04	0.16
90188085	LSQ.A-25-8,5-AS-SST-1/2-13X6-VD	0.98	1/2-13	6.79	6.91	6	0.79	0.73	0.47	3/8	0.33	1124.04	0.16
90188152	LSQ.A-25-14-AS-SST-5/8-11X4-VD	0.98	5/8-11	4.94	5.06	4	0.94	0.89	0.47	1/2	0.55	1124.04	0.36
90188154	LSQ.A-25-14-AS-SST-5/8-11X6-VD	0.98	5/8-11	6.94	7.06	6	0.94	0.89	0.47	1/2	0.55	1124.04	0.54
90188156	LSQ.A-25-14-AS-SST-5/8-11X8-VD	0.98	5/8-11	8.94	9.06	8	0.94	0.89	0.47	1/2	0.55	1124.04	0.16
90188151	LSQ.A-25-14-AS-SST-3/4-10X4-VD	0.98	3/4-10	4.94	5.06	4	0.94	0.89	0.47	9/16	0.55	1124.04	0.16
90188153	LSQ.A-25-14-AS-SST-3/4-10X6-VD	0.98	3/4-10	6.94	7.06	6	0.94	0.89	0.47	9/16	0.55	1124.04	0.16
90188155	LSQ.A-25-14-AS-SST-3/4-10X8-VD	0.98	3/4-10	8.94	9.06	8	0.94	0.89	0.47	9/16	0.55	1124.04	0.16
90188181	LSQ.A-32-8,5-AS-SST-1/2-13X3-VD	1.26	1/2-13	3.91	4.02	3	0.91	0.85	0.59	3/8	0.33	1348.85	0.17
90188183	LSQ.A-32-8,5-AS-SST-1/2-13X4-VD	1.26	1/2-13	4.91	5.02	4	0.91	0.85	0.59	3/8	0.33	1348.85	0.17
90188185	LSQ.A-32-8,5-AS-SST-1/2-13X6-VD	1.26	1/2-13	6.91	7.02	6	0.91	0.85	0.59	3/8	0.33	1348.85	0.17
90188251	LSQ.A-32-14-AS-SST-5/8-11X4-VD	1.26	5/8-11	4.94	5.06	4	0.94	0.89	0.59	5/8	0.55	1573.66	0.37
90188253	LSQ.A-32-14-AS-SST-5/8-11X6-VD	1.26	5/8-11	6.94	7.06	6	0.94	0.89	0.59	5/8	0.55	1573.66	0.55
90188255	LSQ.A-32-14-AS-SST-5/8-11X8-VD	1.26	5/8-11	8.94	9.06	8	0.94	0.89	0.59	5/8	0.55	1573.66	0.18
90188258	LSQ.A-32-14-AS-SST-3/4-10X4-VD	1.26	3/4-10	4.94	5.06	4	0.94	0.89	0.59	9/16	0.55	1573.66	0.18
90188259	LSQ.A-32-14-AS-SST-3/4-10X6-VD	1.26	3/4-10	6.94	7.06	6	0.94	0.89	0.59	9/16	0.55	1573.66	0.18
90188260	LSQ.A-32-14-AS-SST-3/4-10X8-VD	1.26	3/4-10	8.94	9.06	8	0.94	0.89	0.59	9/16	0.55	1573.66	0.18
90188281	LSQ.A-40-8,5-AS-SST-1/2-13X3-VD	1.57	1/2-13	3.98	4.10	3	0.98	0.93	0.67	3/8	0.33	1573.66	0.19
90188283	LSQ.A-40-8,5-AS-SST-1/2-13X4-VD	1.57	1/2-13	4.98	5.10	4	0.98	0.93	0.67	3/8	0.33	1573.66	0.19
90188285	LSQ.A-40-8,5-AS-SST-1/2-13X6-VD	1.57	1/2-13	6.98	7.10	6	0.98	0.93	0.67	3/8	0.33	1573.66	0.19
90188351	LSQ.A-40-14-AS-SST-5/8-11X4-VD	1.57	5/8-11	4.98	5.10	4	0.98	0.93	0.67	5/8	0.55	2248.09	0.39
90188353	LSQ.A-40-14-AS-SST-5/8-11X6-VD	1.57	5/8-11	6.98	7.10	6	0.98	0.93	0.67	5/8	0.55	2248.09	0.57
90188355	LSQ.A-40-14-AS-SST-5/8-11X8-VD	1.57	5/8-11	8.98	9.10	8	0.98	0.93	0.67	5/8	0.55	2248.09	0.19
90188361	LSQ.A-40-14-AS-SST-3/4-10X4-VD	1.57	3/4-10	4.98	5.10	4	0.98	0.93	0.67	9/16	0.55	2248.09	0.19
90188363	LSQ.A-40-14-AS-SST-3/4-10X6-VD	1.57	3/4-10	6.98	7.10	6	0.98	0.93	0.67	9/16	0.55	2248.09	0.19
90188365	LSQ.A-40-14-AS-SST-3/4-10X8-VD	1.57	3/4-10	8.98	9.10	8	0.98	0.93	0.67	9/16	0.55	2248.09	0.19
90188381	LSQ.A-50-8,5-AS-SST-1/2-13X3-VD	1.97	1/2-13	4.06	4.18	3	1.06	1.00	0.75	3/8	0.33	1573.66	0.22
90188383	LSQ.A-50-8,5-AS-SST-1/2-13X4-VD	1.97	1/2-13	5.06	5.18	4	1.06	1.00	0.75	3/8	0.33	1573.66	0.22
90188385	LSQ.A-50-8,5-AS-SST-1/2-13X6-VD	1.97	1/2-13	7.06	7.18	6	1.06	1.00	0.75	3/8	0.33	1573.66	0.22
90187457	LSQ.A-50-14-AS-SST-5/8-11X4-VD	1.97	5/8-11	5.06	5.18	4	1.06	1.00	0.75	5/8	0.55	2248.09	0.41
90188451	LSQ.A-50-14-AS-SST-5/8-11X6-VD	1.97	5/8-11	7.06	7.18	6	1.06	1.00	0.75	5/8	0.55	2248.09	0.59
90188453	LSQ.A-50-14-AS-SST-5/8-11X8-VD	1.97	5/8-11	9.06	9.18	8	1.06	1.00	0.75	5/8	0.55	2248.09	0.22
90188456	LSQ.A-50-14-AS-SST-3/4-10X4-VD	1.97	3/4-10	5.06	5.18	4	1.06	1.00	0.75	9/16	0.55	2248.09	0.22
90188457	LSQ.A-50-14-AS-SST-3/4-10X6-VD	1.97	3/4-10	7.06	7.18	6	1.06	1.00	0.75	9/16	0.55	2248.09	0.22
90188458	LSQ.A-50-14-AS-SST-3/4-10X8-VD	1.97	3/4-10	9.06	9.18	8	1.06	1.00	0.75	9/16	0.55	2248.09	0.22
90188581	LSQ.A-60-14-AS-SST-5/8-11X4-VD	2.36	5/8-11	5.42	5.54	4	1.42	1.36	0.94	5/8	0.55	3147.33	0.45
90188583	LSQ.A-60-14-AS-SST-5/8-11X6-VD	2.36	5/8-11	7.42	7.54	6	1.42	1.36	0.94	5/8	0.55	3147.33	0.63
90188585	LSQ.A-60-14-AS-SST-5/8-11X8-VD	2.36	5/8-11	9.42	9.54	8	1.42	1.36	0.94	5/8	0.55	3147.33	0.26
90188591	LSQ.A-60-14-AS-SST-3/4-10X4-VD	2.36	3/4-10	5.61	5.73	4	1.61	1.52	0.94	9/16	0.55	3147.33	0.26
90188593	LSQ.A-60-14-AS-SST-3/4-10X6-VD	2.36	3/4-10	7.61	7.73	6	1.61	1.52	0.94	9/16	0.55	3147.33	0.26
90188595	LSQ.A-60-14-AS-SST-3/4-10X8-VD	2.36	3/4-10	9.61	9.73	8	1.61	1.52	0.94	9/16	0.55	3147.33	0.26

\* The max static load is the value above which the load applied to the element may cause some plastic material breakage, in particular conditions of use. Obviously, a factor that takes into consideration the importance and the safety level of the specific application must be applied to this value.