



- 1
- 2
- 3
- 4
- 5
- 6
- 7
- 8
- 9
- 10
- 11
- 12
- 13
- 14
- 15
- 16
- 17
- 18
- 19

BASE

Glass-fibre reinforced polyamide based (PA) special conductive technopolymer, black colour, matte finish.
 Surface resistivity = $10^3 \Omega$ (ASTM D257 measuring method).
 Volume resistivity = $10^3 \Omega\text{cm}$ (ASTM D257 measuring method).

ARTICULATED STEM

Threaded zinc-plated steel with regulation hexagon.

STANDARD EXECUTIONS

- **LV.A-ESD-C**: without no-slip disk.
 - **LV.A-AS-ESD-C**: with NBR conductive rubber, hardness 70 Shore A, supplied assembled.
- Surface resistivity = $10^3 \Omega$ (ASTM D991 measuring method).
 Volume resistivity = $10^3 \Omega\text{cm}$ (ASTM D991 measuring method).

FEATURES AND APPLICATIONS

The special conductive technopolymer (ESD-C Electrostatic Discharge Conductive) prevents the accumulation of electrostatic charge. The particular assembling system of the no-slip disk to the base assures a perfect anchoring, preventing separation even in case of impact during transport or of adhesion (sticking) to the floor (see No-slip disks on page 835).
 The bases are suitable for "ESD PROTECTED AREA" (EPA) where components, which are susceptible to electrostatic discharges, are handled. The (ESD-C) indelibly printed mark on the surface of the levelling elements bases identifies the particular conductive features of the material according to EN 100015/1 and IEC 61340-5-1.

ORDER INFORMATION


The levelling elements are supplied unassembled to make carriage and storage easier. The components (base and stem) are supplied in separate packing: less volume taken and better protection from scratches and dirt.
 To order bases and stems separately, see:
 - table of possible combinations Bases/Stems (see page 839)
 - the codes of the Bases (see page 836)
 - the codes of the Stems (see page 985).

ACCESSORIES ON REQUEST

Zinc-plated steel nut (see Nuts NT. on page 835).



ELESA Original design




LV.A-ESD-C

Code	Description	D	d2A	L	l	l1	h	s	Articulation \varnothing	Max. limit static load* [lbf]	
90303121-ESD	LV.A-60-14-3/8-16X2-ESD-C	2.36	3/8-16	3.30	2	1.30	0.94	9/16	0.55	3147.33	0.17
90303125-ESD	LV.A-60-14-3/8-16X4-ESD-C	2.36	3/8-16	5.30	4	1.30	0.94	9/16	0.55	3147.33	0.22
90303127-ESD	LV.A-60-14-3/8-16X6-ESD-C	2.36	3/8-16	7.30	6	1.30	0.94	9/16	0.55	3147.33	0.23
90303321-ESD	LV.A-60-14-1/2-13X2-ESD-C	2.36	1/2-13	3.30	2	1.30	0.94	9/16	0.55	3147.33	0.21
90303325-ESD	LV.A-60-14-1/2-13X4-ESD-C	2.36	1/2-13	5.30	4	1.30	0.94	9/16	0.55	3147.33	0.29
90303331-ESD	LV.A-60-14-1/2-13X6-ESD-C	2.36	1/2-13	7.30	6	1.30	0.94	9/16	0.55	3147.33	0.28
90303521-ESD	LV.A-60-14-5/8-11X4-ESD-C	2.36	5/8-11	5.30	4	1.30	0.94	5/8	0.55	3147.33	0.40
90303525-ESD	LV.A-60-14-5/8-11X6-ESD-C	2.36	5/8-11	7.30	6	1.30	0.94	5/8	0.55	3147.33	0.55
90303541-ESD	LV.A-60-14-5/8-11X8-ESD-C	2.36	5/8-11	9.30	8	1.30	0.94	5/8	0.55	3147.33	0.61
90303621-ESD	LV.A-60-24-5/8-11X4-ESD-C	2.36	5/8-11	5.69	4	1.69	0.94	15/16	0.94	4046.56	0.52
90303626-ESD	LV.A-60-24-5/8-11X6-ESD-C	2.36	5/8-11	7.69	6	1.69	0.94	15/16	0.94	4046.56	0.71
90303641-ESD	LV.A-60-24-5/8-11X8-ESD-C	2.36	5/8-11	9.69	8	1.69	0.94	15/16	0.94	4046.56	0.84
90303726-ESD	LV.A-60-24-3/4-10X4-ESD-C	2.36	3/4-10	5.69	4	1.69	0.94	15/16	0.94	4046.56	0.70
90303741-ESD	LV.A-60-24-3/4-10X6-ESD-C	2.36	3/4-10	7.69	6	1.69	0.94	15/16	0.94	4046.56	0.90
90303761-ESD	LV.A-60-24-3/4-10X8-ESD-C	2.36	3/4-10	9.69	8	1.69	0.94	15/16	0.94	4046.56	1.10

* The max static load is the value above which the load applied to the element may cause some plastic material breakage, in particular conditions of use. Obviously, a factor that takes into consideration the importance and the safety level of the specific application must be applied to this value.

Levelling elements and supports




INCH


LV.A-ESD-C

Code	Description	D	d2A	L	l	l1	h	s	Articulation Ø	Max. limit static load* [lbf]	⚖️
90304005-ESD	LV.A-70-14-3/8-16X2-ESD-C	2.76	3/8-16	3.10	2	1.10	0.75	9/16	0.55	3147.33	0.17
90304011-ESD	LV.A-70-14-3/8-16X4-ESD-C	2.76	3/8-16	5.10	4	1.10	0.75	9/16	0.55	3147.33	0.22
90304013-ESD	LV.A-70-14-3/8-16X6-ESD-C	2.76	3/8-16	7.10	6	1.10	0.75	9/16	0.55	3147.33	0.23
90304061-ESD	LV.A-70-14-1/2-13X2-ESD-C	2.76	1/2-13	3.10	2	1.10	0.75	9/16	0.55	3147.33	0.21
90304065-ESD	LV.A-70-14-1/2-13X4-ESD-C	2.76	1/2-13	5.10	4	1.10	0.75	9/16	0.55	3147.33	0.29
90304071-ESD	LV.A-70-14-1/2-13X6-ESD-C	2.76	1/2-13	7.10	6	1.10	0.75	9/16	0.55	3147.33	0.28
90304101-ESD	LV.A-70-14-5/8-11X4-ESD-C	2.76	5/8-11	5.10	4	1.10	0.75	5/8	0.55	3147.33	0.40
90304105-ESD	LV.A-70-14-5/8-11X6-ESD-C	2.76	5/8-11	7.10	6	1.10	0.75	5/8	0.55	3147.33	0.55
90304111-ESD	LV.A-70-14-5/8-11X8-ESD-C	2.76	5/8-11	9.10	8	1.10	0.75	5/8	0.55	3147.33	0.61
90304121-ESD	LV.A-80-14-3/8-16X2-ESD-C	3.15	3/8-16	3.30	2	1.30	0.94	9/16	0.55	3596.94	0.23
90304125-ESD	LV.A-80-14-3/8-16X4-ESD-C	3.15	3/8-16	5.30	4	1.30	0.94	9/16	0.55	3596.94	0.28
90304127-ESD	LV.A-80-14-3/8-16X6-ESD-C	3.15	3/8-16	7.30	6	1.30	0.94	9/16	0.55	3596.94	0.29
90304321-ESD	LV.A-80-14-1/2-13X2-ESD-C	3.15	1/2-13	3.30	2	1.30	0.94	9/16	0.55	3596.94	0.26
90304325-ESD	LV.A-80-14-1/2-13X4-ESD-C	3.15	1/2-13	5.30	4	1.30	0.94	9/16	0.55	3596.94	0.35
90304331-ESD	LV.A-80-14-1/2-13X6-ESD-C	3.15	1/2-13	7.30	6	1.30	0.94	9/16	0.55	3596.94	0.33
90304521-ESD	LV.A-80-14-5/8-11X4-ESD-C	3.15	5/8-11	5.30	4	1.30	0.94	5/8	0.55	3596.94	0.45
90304525-ESD	LV.A-80-14-5/8-11X6-ESD-C	3.15	5/8-11	7.30	6	1.30	0.94	5/8	0.55	3596.94	0.61
90304541-ESD	LV.A-80-14-5/8-11X8-ESD-C	3.15	5/8-11	9.30	8	1.30	0.94	5/8	0.55	3596.94	0.66
90304621-ESD	LV.A-80-24-5/8-11X4-ESD-C	3.15	5/8-11	5.69	4	1.69	0.94	15/16	0.94	4046.56	0.56
90304626-ESD	LV.A-80-24-5/8-11X6-ESD-C	3.15	5/8-11	7.69	6	1.69	0.94	15/16	0.94	4046.56	0.75
90304641-ESD	LV.A-80-24-5/8-11X8-ESD-C	3.15	5/8-11	9.69	8	1.69	0.94	15/16	0.94	4046.56	0.89
90304726-ESD	LV.A-80-24-3/4-10X4-ESD-C	3.15	3/4-10	5.69	4	1.69	0.94	15/16	0.94	4046.56	0.75
90304741-ESD	LV.A-80-24-3/4-10X6-ESD-C	3.15	3/4-10	7.69	6	1.69	0.94	15/16	0.94	4046.56	0.95
90304761-ESD	LV.A-80-24-3/4-10X8-ESD-C	3.15	3/4-10	9.69	8	1.69	0.94	15/16	0.94	4046.56	1.15
90305451-ESD	LV.A-100-14-3/8-16X2-ESD-C	3.94	3/8-16	3.30	2	1.30	0.94	9/16	0.55	4046.56	0.29
90305453-ESD	LV.A-100-14-3/8-16X4-ESD-C	3.94	3/8-16	5.30	4	1.30	0.94	9/16	0.55	4046.56	0.34
90305455-ESD	LV.A-100-14-3/8-16X6-ESD-C	3.94	3/8-16	7.30	6	1.30	0.94	9/16	0.55	4046.56	0.35
90305471-ESD	LV.A-100-14-1/2-13X2-ESD-C	3.94	1/2-13	3.30	2	1.30	0.94	9/16	0.55	4046.56	0.33
90305473-ESD	LV.A-100-14-1/2-13X4-ESD-C	3.94	1/2-13	5.30	4	1.30	0.94	9/16	0.55	4046.56	0.41
90305475-ESD	LV.A-100-14-1/2-13X6-ESD-C	3.94	1/2-13	7.30	6	1.30	0.94	9/16	0.55	4046.56	0.40
90305481-ESD	LV.A-100-14-5/8-11X4-ESD-C	3.94	5/8-11	5.30	4	1.30	0.94	5/8	0.55	4046.56	0.52
90305483-ESD	LV.A-100-14-5/8-11X6-ESD-C	3.94	5/8-11	7.30	6	1.30	0.94	5/8	0.55	4046.56	0.67
90305485-ESD	LV.A-100-14-5/8-11X8-ESD-C	3.94	5/8-11	9.30	8	1.30	0.94	5/8	0.55	4046.56	0.73
90309521-ESD	LV.A-100-24-5/8-11X4-ESD-C	3.94	5/8-11	5.69	4	1.69	0.94	15/16	0.94	5620.22	0.43
90309525-ESD	LV.A-100-24-5/8-11X6-ESD-C	3.94	5/8-11	7.69	6	1.69	0.94	15/16	0.94	5620.22	0.59
90309541-ESD	LV.A-100-24-5/8-11X8-ESD-C	3.94	5/8-11	9.69	8	1.69	0.94	15/16	0.94	5620.22	0.64
90309625-ESD	LV.A-100-24-3/4-10X4-ESD-C	3.94	3/4-10	5.69	4	1.69	0.94	15/16	0.94	5620.22	0.82
90309641-ESD	LV.A-100-24-3/4-10X6-ESD-C	3.94	3/4-10	7.69	6	1.69	0.94	15/16	0.94	5620.22	1.02
90309661-ESD	LV.A-100-24-3/4-10X8-ESD-C	3.94	3/4-10	9.69	8	1.69	0.94	15/16	0.94	5620.22	1.22
90310221-ESD	LV.A-125-24-5/8-11X4-ESD-C	4.92	5/8-11	6.64	4	2.64	0.94	15/16	0.94	6294.65	0.89
90310225-ESD	LV.A-125-24-5/8-11X6-ESD-C	4.92	5/8-11	8.64	6	2.64	0.94	15/16	0.94	6294.65	1.08
90310241-ESD	LV.A-125-24-5/8-11X8-ESD-C	4.92	5/8-11	10.64	8	2.64	0.94	15/16	0.94	6294.65	1.21
90310325-ESD	LV.A-125-24-3/4-10X4-ESD-C	4.92	3/4-10	6.64	4	2.64	0.94	15/16	0.94	6294.65	1.08
90310341-ESD	LV.A-125-24-3/4-10X6-ESD-C	4.92	3/4-10	8.64	6	2.64	0.94	15/16	0.94	6294.65	1.28
90310361-ESD	LV.A-125-24-3/4-10X8-ESD-C	4.92	3/4-10	10.64	8	2.64	0.94	15/16	0.94	6294.65	1.48

* The max static load is the value above which the load applied to the element may cause some plastic material breakage, in particular conditions of use. Obviously, a factor that takes into consideration the importance and the safety level of the specific application must be applied to this value.



Levelling elements and supports




INCH

LV.A-AS-ESD-C

Code	Description	D	d2A	L	L1	l	l1	h	s	Articulation Ø	Max. limit static load* [lbf]	⚖️
90307121-ESD	LV.A-60-14-AS-3/8-16X2-ESD-C	2.36	3/8-16	3.30	3.42	2	1.30	0.94	9/16	0.55	3147.33	0.21
90307125-ESD	LV.A-60-14-AS-3/8-16X4-ESD-C	2.36	3/8-16	5.30	5.42	4	1.30	0.94	9/16	0.55	3147.33	0.25
90307127-ESD	LV.A-60-14-AS-3/8-16X6-ESD-C	2.36	3/8-16	7.30	7.42	6	1.30	0.94	9/16	0.55	3147.33	0.27
90307321-ESD	LV.A-60-14-AS-1/2-13X2-ESD-C	2.36	1/2-13	3.30	3.42	2	1.30	0.94	9/16	0.55	3147.33	0.24
90307325-ESD	LV.A-60-14-AS-1/2-13X4-ESD-C	2.36	1/2-13	5.30	5.42	4	1.30	0.94	9/16	0.55	3147.33	0.33
90307331-ESD	LV.A-60-14-AS-1/2-13X6-ESD-C	2.36	1/2-13	7.30	7.42	6	1.30	0.94	9/16	0.55	3147.33	0.31
90307521-ESD	LV.A-60-14-AS-5/8-11X4-ESD-C	2.36	5/8-11	5.30	5.42	4	1.30	0.94	5/8	0.55	3147.33	0.26
90307525-ESD	LV.A-60-14-AS-5/8-11X6-ESD-C	2.36	5/8-11	7.30	7.42	6	1.30	0.94	5/8	0.55	3147.33	0.34
90307541-ESD	LV.A-60-14-AS-5/8-11X8-ESD-C	2.36	5/8-11	9.30	9.42	8	1.30	0.94	5/8	0.55	3147.33	0.64
90307621-ESD	LV.A-60-24-AS-5/8-11X4-ESD-C	2.36	5/8-11	5.69	5.81	4	1.69	0.94	15/16	0.94	4046.56	0.56
90307626-ESD	LV.A-60-24-AS-5/8-11X6-ESD-C	2.36	5/8-11	7.69	7.81	6	1.69	0.94	15/16	0.94	4046.56	0.75
90307641-ESD	LV.A-60-24-AS-5/8-11X8-ESD-C	2.36	5/8-11	9.69	9.81	8	1.69	0.94	15/16	0.94	4046.56	0.88
90307726-ESD	LV.A-60-24-AS-3/4-10X4-ESD-C	2.36	3/4-10	5.69	5.81	4	1.69	0.94	15/16	0.94	4046.56	0.74
90307741-ESD	LV.A-60-24-AS-3/4-10X6-ESD-C	2.36	3/4-10	7.69	7.81	6	1.69	0.94	15/16	0.94	4046.56	0.94
90307761-ESD	LV.A-60-24-AS-3/4-10X8-ESD-C	2.36	3/4-10	9.69	9.81	8	1.69	0.94	15/16	0.94	4046.56	1.14
90308005-ESD	LV.A-70-14-AS-3/8-16X2-ESD-C	2.76	3/8-16	3.10	3.22	2	1.10	0.75	9/16	0.55	3147.33	0.22
90308011-ESD	LV.A-70-14-AS-3/8-16X4-ESD-C	2.76	3/8-16	5.10	5.22	4	1.10	0.75	9/16	0.55	3147.33	0.27
90308013-ESD	LV.A-70-14-AS-3/8-16X6-ESD-C	2.76	3/8-16	7.10	7.22	6	1.10	0.75	9/16	0.55	3147.33	0.28
90308061-ESD	LV.A-70-14-AS-1/2-13X2-ESD-C	2.76	1/2-13	3.10	3.22	2	1.10	0.75	9/16	0.55	3147.33	0.26
90308065-ESD	LV.A-70-14-AS-1/2-13X4-ESD-C	2.76	1/2-13	5.10	5.22	4	1.10	0.75	9/16	0.55	3147.33	0.34
90308071-ESD	LV.A-70-14-AS-1/2-13X6-ESD-C	2.76	1/2-13	7.10	7.22	6	1.10	0.75	9/16	0.55	3147.33	0.33
90308101-ESD	LV.A-70-14-AS-5/8-11X4-ESD-C	2.76	5/8-11	5.10	5.22	4	1.10	0.75	5/8	0.55	3147.33	0.45
90308105-ESD	LV.A-70-14-AS-5/8-11X6-ESD-C	2.76	5/8-11	7.10	7.22	6	1.10	0.75	5/8	0.55	3147.33	0.60
90308111-ESD	LV.A-70-14-AS-5/8-11X8-ESD-C	2.76	5/8-11	9.10	9.22	8	1.10	0.75	5/8	0.55	3147.33	0.66
90308121-ESD	LV.A-80-14-AS-3/8-16X2-ESD-C	3.15	3/8-16	3.30	3.42	2	1.30	0.94	9/16	0.55	3596.94	0.28
90308125-ESD	LV.A-80-14-AS-3/8-16X4-ESD-C	3.15	3/8-16	5.30	5.42	4	1.30	0.94	9/16	0.55	3596.94	0.32
90308127-ESD	LV.A-80-14-AS-3/8-16X6-ESD-C	3.15	3/8-16	7.30	7.42	6	1.30	0.94	9/16	0.55	3596.94	0.34
90308321-ESD	LV.A-80-14-AS-1/2-13X2-ESD-C	3.15	1/2-13	3.30	3.42	2	1.30	0.94	9/16	0.55	3596.94	0.31
90308325-ESD	LV.A-80-14-AS-1/2-13X4-ESD-C	3.15	1/2-13	5.30	5.42	4	1.30	0.94	9/16	0.55	3596.94	0.39
90308331-ESD	LV.A-80-14-AS-1/2-13X6-ESD-C	3.15	1/2-13	7.30	7.42	6	1.30	0.94	9/16	0.55	3596.94	0.38
90308521-ESD	LV.A-80-14-AS-5/8-11X4-ESD-C	3.15	5/8-11	5.30	5.42	4	1.30	0.94	5/8	0.55	3596.94	0.50
90308525-ESD	LV.A-80-14-AS-5/8-11X6-ESD-C	3.15	5/8-11	7.30	7.42	6	1.30	0.94	5/8	0.55	3596.94	0.65
90308541-ESD	LV.A-80-14-AS-5/8-11X8-ESD-C	3.15	5/8-11	9.30	9.42	8	1.30	0.94	5/8	0.55	3596.94	0.71
90308621-ESD	LV.A-80-24-AS-5/8-11X4-ESD-C	3.15	5/8-11	5.69	5.81	4	1.69	0.94	15/16	0.94	4046.56	0.62
90308626-ESD	LV.A-80-24-AS-5/8-11X6-ESD-C	3.15	5/8-11	7.69	7.81	6	1.69	0.94	15/16	0.94	4046.56	0.81
90308641-ESD	LV.A-80-24-AS-5/8-11X8-ESD-C	3.15	5/8-11	9.69	9.81	8	1.69	0.94	15/16	0.94	4046.56	0.94
90308726-ESD	LV.A-80-24-AS-3/4-10X4-ESD-C	3.15	3/4-10	5.69	5.81	4	1.69	0.94	15/16	0.94	4046.56	0.80
90308741-ESD	LV.A-80-24-AS-3/4-10X6-ESD-C	3.15	3/4-10	7.69	7.81	6	1.69	0.94	15/16	0.94	4046.56	1.00
90308761-ESD	LV.A-80-24-AS-3/4-10X8-ESD-C	3.15	3/4-10	9.69	9.81	8	1.69	0.94	15/16	0.94	4046.56	1.20

* The max static load is the value above which the load applied to the element may cause some plastic material breakage, in particular conditions of use. Obviously, a factor that takes into consideration the importance and the safety level of the specific application must be applied to this value.



INCH

LV.A-AS-ESD-C

Code	Description	D	d2A	L	L1	l	l1	h	s	Articulation Ø	Max. limit static load* [lbf]	⚖️
90309451-ESD	LV.A-100-14-AS-3/8-16X2-ESD-C	3.94	3/8-16	3.30	3.42	2	1.30	0.94	9/16	0.55	4046.56	0.38
90309453-ESD	LV.A-100-14-AS-3/8-16X4-ESD-C	3.94	3/8-16	5.30	5.42	4	1.30	0.94	9/16	0.55	4046.56	0.43
90309455-ESD	LV.A-100-14-AS-3/8-16X6-ESD-C	3.94	3/8-16	7.30	7.42	6	1.30	0.94	9/16	0.55	4046.56	0.44
90309471-ESD	LV.A-100-14-AS-1/2-13X2-ESD-C	3.94	1/2-13	3.30	3.42	2	1.30	0.94	9/16	0.55	4046.56	0.41
90309473-ESD	LV.A-100-14-AS-1/2-13X4-ESD-C	3.94	1/2-13	5.30	5.42	4	1.30	0.94	9/16	0.55	4046.56	0.93
90309475-ESD	LV.A-100-14-AS-1/2-13X6-ESD-C	3.94	1/2-13	7.30	7.42	6	1.30	0.94	9/16	0.55	4046.56	1.02
90309481-ESD	LV.A-100-14-AS-5/8-11X4-ESD-C	3.94	5/8-11	5.30	5.42	4	1.30	0.94	5/8	0.55	4046.56	1.13
90309483-ESD	LV.A-100-14-AS-5/8-11X6-ESD-C	3.94	5/8-11	7.30	7.42	6	1.30	0.94	5/8	0.55	4046.56	1.22
90309485-ESD	LV.A-100-14-AS-5/8-11X8-ESD-C	3.94	5/8-11	9.30	9.42	8	1.30	0.94	5/8	0.55	4046.56	1.33
90309522-ESD	LV.A-100-24-AS-5/8-11X4-ESD-C	3.94	5/8-11	5.69	5.81	4	1.69	0.94	15/16	0.94	5620.22	0.89
90309526-ESD	LV.A-100-24-AS-5/8-11X6-ESD-C	3.94	5/8-11	7.69	7.81	6	1.69	0.94	15/16	0.94	5620.22	1.25
90309542-ESD	LV.A-100-24-AS-5/8-11X8-ESD-C	3.94	5/8-11	9.69	9.81	8	1.69	0.94	15/16	0.94	5620.22	1.06
90309626-ESD	LV.A-100-24-AS-3/4-10X4-ESD-C	3.94	3/4-10	5.69	5.81	4	1.69	0.94	15/16	0.94	5620.22	0.93
90309642-ESD	LV.A-100-24-AS-3/4-10X6-ESD-C	3.94	3/4-10	7.69	7.81	6	1.69	0.94	15/16	0.94	5620.22	1.13
90309662-ESD	LV.A-100-24-AS-3/4-10X8-ESD-C	3.94	3/4-10	9.69	9.81	8	1.69	0.94	15/16	0.94	5620.22	1.33
90310222-ESD	LV.A-125-24-AS-5/8-11X4-ESD-C	4.92	5/8-11	6.64	6.76	4	2.64	0.94	15/16	0.94	6294.65	1.06
90310226-ESD	LV.A-125-24-AS-5/8-11X6-ESD-C	4.92	5/8-11	8.64	8.76	6	2.64	0.94	15/16	0.94	6294.65	1.25
90310242-ESD	LV.A-125-24-AS-5/8-11X8-ESD-C	4.92	5/8-11	10.64	10.76	8	2.64	0.94	15/16	0.94	6294.65	1.38
90310326-ESD	LV.A-125-24-AS-3/4-10X4-ESD-C	4.92	3/4-10	6.64	6.76	4	2.64	0.94	15/16	0.94	6294.65	1.24
90310342-ESD	LV.A-125-24-AS-3/4-10X6-ESD-C	4.92	3/4-10	8.64	8.76	6	2.64	0.94	15/16	0.94	6294.65	1.44
90310362-ESD	LV.A-125-24-AS-3/4-10X8-ESD-C	4.92	3/4-10	10.64	10.76	8	2.64	0.94	15/16	0.94	6294.65	1.64

* The max static load is the value above which the load applied to the element may cause some plastic material breakage, in particular conditions of use. Obviously, a factor that takes into consideration the importance and the safety level of the specific application must be applied to this value.



Levelling elements and supports