

BASE

Glass-fibre reinforced polyamide based (PA) technopolymer, black colour, matte finish.

ARTICULATED STEM

Threaded AISI 304 stainless steel with regulation hexagon.

STANDARD EXECUTIONS

- LV.A-SST: without no-slip disk.
- LV.A-AS-SST: with NBR rubber no-slip disk, hardness 70 Shore A, supplied assembled to the base.

FEATURES

The special knurling under the lower lip of the base provides excellent stability and grip when using the levelling element without no-slip disk even on surfaces that are not perfectly flat.

The particular assembling system of the no-slip disk to the base assures a perfect anchoring, preventing separation even in case of impact during transport or of adhesion (sticking) to the floor (see No-slip disks on page 1283).

ORDER INFORMATION

The levelling elements are supplied unassembled to make carriage and storage easier. The components (base and stem) are supplied in separate packing: less volume taken and better protection from scratches and dirt.

To order bases and stems separately, see:


- table of possible combinations Bases/Stems (see page 1291)
- the codes of the Bases (see page 1288)
- the codes of the Stems (see page 1290).

ACCESSORIES ON REQUEST

AISI 304 stainless steel nut (see Nuts NT. on page 1283).



ELESA Original design




LV.A-SST

LV.A-AS-SST

Code	Description	Code	Description	D	d2A	L	L#	I	I#	h	s	Articulation Ø	Max. limit static load* [lb f]	Δ	Δ #
90323221	LV.A-60-14-SST-3/8-16x2	90327221	LV.A-60-14-AS-SST-3/8-16x2	2.36	3/8-16	3.3	3.42	2.000	1.3	0.94	9/16	0.55	3136	0.16	0.2
90323231	LV.A-60-14-SST-3/8-16x4	90327231	LV.A-60-14-AS-SST-3/8-16x4	2.36	3/8-16	5.3	5.42	4.000	1.3	0.94	9/16	0.55	3136	0.2	0.24
90323235	LV.A-60-14-SST-3/8-16x6	90327235	LV.A-60-14-AS-SST-3/8-16x6	2.36	3/8-16	7.3	7.42	6.000	1.3	0.94	9/16	0.55	3136	0.24	0.29
90323321	LV.A-60-14-SST-1/2-13x2	90327321	LV.A-60-14-AS-SST-1/2-13x2	2.36	1/2-13	3.3	3.42	2.000	1.3	0.94	9/16	0.55	3136	0.18	0.22
90323331	LV.A-60-14-SST-1/2-13x4	90327331	LV.A-60-14-AS-SST-1/2-13x4	2.36	1/2-13	5.3	5.42	4.000	1.3	0.94	9/16	0.55	3136	0.22	0.27
90323335	LV.A-60-14-SST-1/2-13x6	90327335	LV.A-60-14-AS-SST-1/2-13x6	2.36	1/2-13	7.3	7.42	6.000	1.3	0.94	9/16	0.55	3136	0.27	0.31
90323523	LV.A-60-14-SST-5/8-11x4	90327523	LV.A-60-14-AS-SST-5/8-11x4	2.36	5/8-11	5.3	5.42	4.000	1.3	0.94	5/8	0.55	3136	0.24	0.29
90323541	LV.A-60-14-SST-5/8-11x6	90327541	LV.A-60-14-AS-SST-5/8-11x6	2.36	5/8-11	7.3	7.42	6.000	1.3	0.94	5/8	0.55	3136	0.29	0.33
90323565	LV.A-60-14-SST-5/8-11x8	90327565	LV.A-60-14-AS-SST-5/8-11x8	2.36	5/8-11	5.3	5.42	8.000	1.3	0.94	5/8	0.94	3136	0.33	0.37
90323625	LV.A-60-24-SST-5/8-11x4	90327625	LV.A-60-24-AS-SST-5/8-11x4	2.36	5/8-11	7.3	7.42	4.000	1.3	0.94	15/16	0.94	4032	0.49	0.53
90323645	LV.A-60-24-SST-5/8-11x6	90327645	LV.A-60-24-AS-SST-5/8-11x6	2.36	5/8-11	9.3	9.42	6.000	1.3	0.94	15/16	0.94	4032	0.52	0.56
90323665	LV.A-60-24-SST-5/8-11x8	90327665	LV.A-60-24-AS-SST-5/8-11x8	2.36	5/8-11	5.69	5.81	8.000	1.3	0.94	15/16	0.94	4032	0.55	0.59
90323725	LV.A-60-24-SST-3/4-10x4	90327725	LV.A-60-24-AS-SST-3/4-10x4	2.36	3/4-10	7.69	7.81	4.000	1.3	0.94	15/16	0.94	4032	0.58	0.62
90323745	LV.A-60-24-SST-3/4-10x6	90327745	LV.A-60-24-AS-SST-3/4-10x6	2.36	3/4-10	9.69	9.81	6.000	1.3	0.94	15/16	0.94	4032	0.62	0.66
90323781	LV.A-60-24-SST-3/4-10x8	90327781	LV.A-60-24-AS-SST-3/4-10x8	2.36	3/4-10	5.69	5.81	8.000	1.3	0.94	15/16	0.94	4032	0.65	0.69

* The max static load is the value above which the load applied to the element may cause some plastic material breakage, in particular conditions of use. Obviously, a factor that takes into consideration the importance and the safety level of the specific application must be applied to this value.



LV.A-SST

LV.A-AS-SST

Code	Description	Code	Description	D	d2A	L	L#	l	l1	h	s	Articulation Ø	Max. limit static load* [lbf]	#
90324021	LV.A-70-14-SST-3/8-16x2	90328021	LV.A-70-14-AS-SST-3/8-16x2	2.76	3/8-16	3.1	3.22	2.000	1.1	0.75	9/16	0.55	3136	0.16 0.2
90324031	LV.A-70-14-SST-3/8-16x4	90328031	LV.A-70-14-AS-SST-3/8-16x4	2.76	3/8-16	5.11	5.23	4.000	1.1	0.75	9/16	0.55	3136	0.18 0.22
90324035	LV.A-70-14-SST-3/8-16x6	90328035	LV.A-70-14-AS-SST-3/8-16x6	2.76	3/8-16	7.1	7.22	8.000	1.1	0.75	9/16	0.55	3136	0.2 0.24
90324061	LV.A-70-14-SST-1/2-13x2	90328061	LV.A-70-14-AS-SST-1/2-13x2	2.76	1/2-13	3.1	3.22	2.000	1.1	0.75	9/16	0.55	3136	0.17 0.21
90324071	LV.A-70-14-SST-1/2-13x4	90328071	LV.A-70-14-AS-SST-1/2-13x4	2.76	1/2-13	5.1	5.22	4.000	1.1	0.75	9/16	0.55	3136	0.19 0.23
90324075	LV.A-70-14-SST-1/2-13x6	90328075	LV.A-70-14-AS-SST-1/2-13x6	2.76	1/2-13	7.1	7.22	6.000	1.1	0.75	9/16	0.55	3136	0.21 0.25
90324111	LV.A-70-14-SST-5/8-11x4	90328111	LV.A-70-14-AS-SST-5/8-11x4	2.76	5/8-11	5.1	5.22	4.000	1.1	0.75	5/8	0.55	3136	0.2 0.24
90324123	LV.A-70-14-SST-5/8-11x6	90328123	LV.A-70-14-AS-SST-5/8-11x6	2.76	5/8-11	7.1	7.22	6.000	1.1	0.75	5/8	0.55	3136	0.22 0.26
90324165	LV.A-70-14-SST-5/8-11x8	90328165	LV.A-70-14-AS-SST-5/8-11x8	2.76	5/8-11	9.1	9.22	8.000	1.1	0.75	5/8	0.55	3136	0.27 0.31
90324221	LV.A-80-14-SST-3/8-16x2	90328221	LV.A-80-14-AS-SST-3/8-16x2	3.15	3/8-16	3.3	3.42	2.000	1.3	0.94	9/16	0.55	3584	0.21 0.25
90324231	LV.A-80-14-SST-3/8-16x4	90328231	LV.A-80-14-AS-SST-3/8-16x4	3.15	3/8-16	5.3	5.42	4.000	1.3	0.94	9/16	0.55	3584	0.24 0.28
90324235	LV.A-80-14-SST-3/8-16x6	90328235	LV.A-80-14-AS-SST-3/8-16x6	3.15	3/8-16	7.3	7.42	6.000	1.3	0.94	9/16	0.55	3584	0.27 0.31
90324321	LV.A-80-14-SST-1/2-13x2	90328321	LV.A-80-14-AS-SST-1/2-13x2	3.15	1/2-13	5.3	5.42	2.000	1.3	0.94	9/16	0.55	3584	0.23 0.27
90324331	LV.A-80-14-SST-1/2-13x4	90328331	LV.A-80-14-AS-SST-1/2-13x4	3.15	1/2-13	7.3	7.42	4.000	1.3	0.94	9/16	0.55	3584	0.26 0.3
90324335	LV.A-80-14-SST-1/2-13x6	90328335	LV.A-80-14-AS-SST-1/2-13x6	3.15	1/2-13	9.3	9.42	6.000	1.3	0.94	9/16	0.55	3584	0.29 0.33
90324523	LV.A-80-14-SST-5/8-11x4	90328523	LV.A-80-14-AS-SST-5/8-11x4	3.15	5/8-11	5.69	5.81	4.000	1.3	0.94	9/16	0.55	3584	0.29 0.33
90324541	LV.A-80-14-SST-5/8-11x6	90328541	LV.A-80-14-AS-SST-5/8-11x6	3.15	5/8-11	7.69	7.81	6.000	1.3	0.94	9/16	0.55	3584	0.32 0.36
90324565	LV.A-80-14-SST-5/8-11x8	90328565	LV.A-80-14-AS-SST-5/8-11x8	3.15	5/8-11	9.69	9.81	8.000	1.3	0.94	9/16	0.55	3584	0.35 0.39
90324625	LV.A-80-24-SST-5/8-11x4	90328625	LV.A-80-24-AS-SST-5/8-11x4	3.15	5/8-11	5.69	5.81	4.000	1.69	0.94	15/16	0.94	4032	0.32 0.36
90324645	LV.A-80-24-SST-5/8-11x6	90328645	LV.A-80-24-AS-SST-5/8-11x6	3.15	5/8-11	7.69	7.81	6.000	1.69	0.94	15/16	0.94	4032	0.35 0.39
90324665	LV.A-80-24-SST-5/8-11x8	90328665	LV.A-80-24-AS-SST-5/8-11x8	3.15	5/8-11	9.69	9.81	8.000	1.69	0.94	15/16	0.94	4032	0.37 0.42
90324725	LV.A-80-24-SST-3/4-10x4	90328725	LV.A-80-24-AS-SST-3/4-10x4	3.15	3/4-10	5.69	5.81	4.000	1.69	0.94	15/16	0.94	4032	0.38 0.42
90324745	LV.A-80-24-SST-3/4-10x6	90328745	LV.A-80-24-AS-SST-3/4-10x6	3.15	3/4-10	7.69	7.81	6.000	1.69	0.94	15/16	0.94	4032	0.41 0.45
90324781	LV.A-80-24-SST-3/4-10x8	90328781	LV.A-80-24-AS-SST-3/4-10x8	3.15	3/4-10	9.69	9.81	8.000	1.69	0.94	15/16	0.94	4032	0.45 0.49
90325203	LV.A-100-14-SST-3/8-16x2	90329303	LV.A-100-14-AS-SST-3/8-16x2	3.94	3/8-16	3.3	3.42	2.000	1.3	0.94	9/16	0.94	4032	0.22 0.34
90325205	LV.A-100-14-SST-3/8-16x4	90329305	LV.A-100-14-AS-SST-3/8-16x4	3.94	3/8-16	5.3	5.42	4.000	1.3	0.94	9/16	0.94	4032	0.25 0.37
90325207	LV.A-100-14-SST-3/8-16x6	90329307	LV.A-100-14-AS-SST-3/8-16x6	3.94	3/8-16	7.3	7.42	6.000	1.3	0.94	9/16	0.94	4032	0.3 0.42
90325213	LV.A-100-14-SST-1/2-13x2	90329313	LV.A-100-14-AS-SST-1/2-13x2	3.94	1/2-13	3.3	3.42	2.000	1.3	0.94	9/16	0.94	4032	0.24 0.37
90325215	LV.A-100-14-SST-1/2-13x4	90329315	LV.A-100-14-AS-SST-1/2-13x4	3.94	1/2-13	5.3	5.42	4.000	1.3	0.94	9/16	0.94	4032	0.33 0.45
90325217	LV.A-100-14-SST-1/2-13x6	90329317	LV.A-100-14-AS-SST-1/2-13x6	3.94	1/2-13	7.3	7.42	6.000	1.3	0.94	9/16	0.94	4032	0.38 0.5
90325325	LV.A-100-14-SST-5/8-11x4	90329325	LV.A-100-14-AS-SST-5/8-11x4	3.94	5/8-11	5.3	5.42	4.000	1.3	0.94	9/16	0.94	4032	0.5 5.02
90325345	LV.A-100-14-SST-5/8-11x6	90329345	LV.A-100-14-AS-SST-5/8-11x6	3.94	5/8-11	7.3	7.42	6.000	1.69	0.94	9/16	0.94	4032	0.61 0.73
90325365	LV.A-100-14-SST-5/8-11x8	90329365	LV.A-100-14-AS-SST-5/8-11x8	3.94	5/8-11	9.3	9.42	8.000	1.69	0.94	9/16	0.94	4032	0.76 0.86
90325525	LV.A-100-24-SST-5/8-11x4	90329525	LV.A-100-24-AS-SST-5/8-11x4	3.94	5/8-11	5.69	5.81	4.000	1.69	0.94	15/16	0.94	5600	0.61 0.73
90325545	LV.A-100-24-SST-5/8-11x6	90329545	LV.A-100-24-AS-SST-5/8-11x6	3.94	5/8-11	7.69	7.81	6.000	1.69	0.94	15/16	0.94	5600	0.64 0.76
90325565	LV.A-100-24-SST-5/8-11x8	90329565	LV.A-100-24-AS-SST-5/8-11x8	3.94	5/8-11	9.69	9.81	8.000	1.69	0.94	15/16	0.94	5600	0.68 0.8
90325625	LV.A-100-24-SST-3/4-10x4	90329625	LV.A-100-24-AS-SST-3/4-10x4	3.94	3/4-10	5.69	5.81	4.000	1.69	0.94	15/16	0.94	5600	0.66 0.78
90325645	LV.A-100-24-SST-3/4-10x6	90329645	LV.A-100-24-AS-SST-3/4-10x6	3.94	3/4-10	7.69	7.81	6.000	1.69	0.94	15/16	0.94	5600	0.69 0.81
90325681	LV.A-100-24-SST-3/4-10x8	90329681	LV.A-100-24-AS-SST-3/4-10x8	3.94	3/4-10	9.69	9.81	8.000	1.69	0.94	15/16	0.94	5600	0.72 0.84
90326525	LV.A-125-24-SST-5/8-11x4	90330225	LV.A-125-24-AS-SST-5/8-11x4	4.92	5/8-11	6.64	6.76	4.000	2.64	1.81	15/16	0.94	627	0.91 1.19
90326545	LV.A-125-24-SST-5/8-11x6	90330245	LV.A-125-24-AS-SST-5/8-11x6	4.92	5/8-11	8.64	8.76	6.000	2.64	1.81	15/16	0.94	627	0.93 1.21
90326565	LV.A-125-24-SST-5/8-11x8	90330265	LV.A-125-24-AS-SST-5/8-11x8	4.92	5/8-11	10.64	10.76	8.000	2.64	1.81	15/16	0.94	627	0.96 1.24
90326625	LV.A-125-24-SST-3/4-10x4	90330325	LV.A-125-24-AS-SST-3/4-10x4	4.92	3/4-10	6.64	6.76	4.000	2.64	1.81	15/16	0.94	627	0.98 1.26
90326645	LV.A-125-24-SST-3/4-10x6	90330345	LV.A-125-24-AS-SST-3/4-10x6	4.92	3/4-10	8.64	8.76	6.000	2.64	1.81	15/16	0.94	627	1.02 1.3
90326681	LV.A-125-24-SST-3/4-10x8	90330381	LV.A-125-24-AS-SST-3/4-10x8	4.92	3/4-10	10.64	10.76	8.000	2.64	1.81	15/16	0.94	627	1.05 1.33

* The max static load is the value above which the load applied to the element may cause some plastic material breakage, in particular conditions of use. Obviously, a factor that takes into consideration the importance and the safety level of the specific application must be applied to this value.