

- 1 
- 2 
- 3 
- 4 
- 5 
- 6 
- 7 
- 8 
- 9 
- 10 
- 11 
- 12** 
- 13 
- 14 
- 15 
- 16 
- 17 
- 18 
- 19 

BASE

Glass-fibre reinforced polyamide based (PA) technopolymer, RAL 5005 blue colour, matte finish.
Produced from FDA compliant raw material (FDA CFR.21 and EU 10/2011).

ARTICULATED STEM

Threaded AISI 304 stainless steel with regulation hexagon.

STANDARD EXECUTIONS

- **LS.A-SST-VD**: without no-slip disk.
- **LS.A-AS-SST-VD**: with NBR rubber no-slip disk, hardness 70 Shore A, supplied assembled to the base.

FEATURES AND APPLICATIONS

The RAL 5005 blue colour is easily visible in case of accidental food contamination.
The particular assembling system of the no-slip disk to the base assures a perfect anchoring, preventing separation even in case of impact during transport or of adhesion (sticking) to the floor (see No-slip disks on page 835).

ORDER INFORMATION


The levelling feet are supplied unassembled to make carriage and storage easier. The components (base and stem) are supplied in separate packing: less volume taken and better protection from scratches and dirt.
To order bases and stems separately, see:
- table of possible combinations Bases/Stems (see page 839)
- the codes of the Bases (see page 836)
- the codes of the Stems (see page 985).

ACCESSORIES ON REQUEST

AISI 304 stainless steel nut (see Nuts NT. on page 835).



ELESA Original design




LS.A-SST-VD

Code	Description	D	d2A	L	l	l1	h	s	Articulation Ø	Max. limit static load* [lbf]	⚖
90187101	LS.A-25-14-SST-3/8-16X2-VD	0.98	3/8-16	2.94	2	0.94	0.47	9/16	0.55	1573.66	0.11
90187103	LS.A-25-14-SST-3/8-16X4-VD	0.98	3/8-16	4.94	4	0.94	0.47	9/16	0.55	1573.66	0.21
90187105	LS.A-25-14-SST-3/8-16X6-VD	0.98	3/8-16	6.94	6	0.94	0.47	9/16	0.55	1573.66	0.11
90187121	LS.A-25-14-SST-1/2-13X2-VD	0.98	1/2-13	2.94	2	0.94	0.47	9/16	0.55	1573.66	0.13
90187123	LS.A-25-14-SST-1/2-13X4-VD	0.98	1/2-13	4.94	4	0.94	0.47	9/16	0.55	1573.66	0.23
90187125	LS.A-25-14-SST-1/2-13X6-VD	0.98	1/2-13	6.94	6	0.94	0.47	9/16	0.55	1573.66	0.21
90187141	LS.A-25-14-SST-5/8-11X4-VD	0.98	5/8-11	4.94	4	0.94	0.47	5/8	0.55	1573.66	0.34
90187143	LS.A-25-14-SST-5/8-11X6-VD	0.98	5/8-11	6.94	6	0.94	0.47	5/8	0.55	1573.66	0.50
90187145	LS.A-25-14-SST-5/8-11X8-VD	0.98	5/8-11	8.94	8	0.94	0.47	5/8	0.55	1573.66	0.56
90187201	LS.A-32-14-SST-3/8-16X2-VD	1.26	3/8-16	2.98	2	0.98	0.59	9/16	0.55	2023.28	0.11
90187202	LS.A-32-14-SST-3/8-16X4-VD	1.26	3/8-16	4.98	4	0.98	0.59	9/16	0.55	2023.28	0.22
90187203	LS.A-32-14-SST-3/8-16X6-VD	1.26	3/8-16	6.98	6	0.98	0.59	9/16	0.55	2023.28	0.12
90187221	LS.A-32-14-SST-1/2-13X2-VD	1.26	1/2-13	2.98	2	0.98	0.59	9/16	0.55	2023.28	0.13
90187222	LS.A-32-14-SST-1/2-13X4-VD	1.26	1/2-13	4.98	4	0.98	0.59	9/16	0.55	2023.28	0.24
90187223	LS.A-32-14-SST-1/2-13X6-VD	1.26	1/2-13	6.98	6	0.98	0.59	9/16	0.55	2023.28	0.22
90187211	LS.A-32-14-SST-5/8-11X4-VD	1.26	5/8-11	4.98	4	0.98	0.59	5/8	0.55	2023.28	0.34
90187212	LS.A-32-14-SST-5/8-11X6-VD	1.26	5/8-11	6.98	6	0.98	0.59	5/8	0.55	2023.28	0.51
90187213	LS.A-32-14-SST-5/8-11X8-VD	1.26	5/8-11	8.98	8	0.98	0.59	5/8	0.55	2023.28	0.56
90187301	LS.A-40-14-SST-3/8-16X2-VD	1.57	3/8-16	2.98	2	0.98	0.67	9/16	0.55	2922.52	0.13
90187303	LS.A-40-14-SST-3/8-16X4-VD	1.57	3/8-16	4.98	4	0.98	0.67	9/16	0.55	2922.52	0.23
90187305	LS.A-40-14-SST-3/8-16X6-VD	1.57	3/8-16	6.98	6	0.98	0.67	9/16	0.55	2922.52	0.13
90187321	LS.A-40-14-SST-1/2-13X2-VD	1.57	1/2-13	2.98	2	0.98	0.67	9/16	0.55	2922.52	0.15
90187323	LS.A-40-14-SST-1/2-13X4-VD	1.57	1/2-13	4.98	4	0.98	0.67	9/16	0.55	2922.52	0.25
90187325	LS.A-40-14-SST-1/2-13X6-VD	1.57	1/2-13	6.98	6	0.98	0.67	9/16	0.55	2922.52	0.23
90187341	LS.A-40-14-SST-5/8-11X4-VD	1.57	5/8-11	4.98	4	0.98	0.67	5/8	0.55	2922.52	0.35
90187343	LS.A-40-14-SST-5/8-11X6-VD	1.57	5/8-11	6.98	6	0.98	0.67	5/8	0.55	2922.52	0.52
90187345	LS.A-40-14-SST-5/8-11X8-VD	1.57	5/8-11	8.98	8	0.98	0.67	5/8	0.55	2922.52	0.58
90187401	LS.A-50-14-SST-3/8-16X2-VD	1.97	3/8-16	3.06	2	1.06	0.75	9/16	0.55	2922.52	0.14
90187403	LS.A-50-14-SST-3/8-16X4-VD	1.97	3/8-16	5.06	4	1.06	0.75	9/16	0.55	2922.52	0.25
90187405	LS.A-50-14-SST-3/8-16X6-VD	1.97	3/8-16	7.06	6	1.06	0.75	9/16	0.55	2922.52	0.14
90187421	LS.A-50-14-SST-1/2-13X2-VD	1.97	1/2-13	3.06	2	1.06	0.75	9/16	0.55	2922.52	0.16
90187423	LS.A-50-14-SST-1/2-13X4-VD	1.97	1/2-13	5.06	4	1.06	0.75	9/16	0.55	2922.52	0.26
90187425	LS.A-50-14-SST-1/2-13X6-VD	1.97	1/2-13	7.06	6	1.06	0.75	9/16	0.55	2922.52	0.25
90187441	LS.A-50-14-SST-5/8-11X4-VD	1.97	5/8-11	5.06	4	1.06	0.75	5/8	0.55	2922.52	0.37
90187443	LS.A-50-14-SST-5/8-11X6-VD	1.97	5/8-11	7.06	6	1.06	0.75	5/8	0.55	2922.52	0.53
90187445	LS.A-50-14-SST-5/8-11X8-VD	1.97	5/8-11	9.06	8	1.06	0.75	5/8	0.55	2922.52	0.59
90187501	LS.A-60-14-SST-3/8-16X2-VD	2.36	3/8-16	3.30	2	1.30	0.94	9/16	0.55	3147.33	0.17
90187503	LS.A-60-14-SST-3/8-16X4-VD	2.36	3/8-16	5.30	4	1.30	0.94	9/16	0.55	3147.33	0.28
90187505	LS.A-60-14-SST-3/8-16X6-VD	2.36	3/8-16	7.30	6	1.30	0.94	9/16	0.55	3147.33	0.18
90187521	LS.A-60-14-SST-1/2-13X2-VD	2.36	1/2-13	3.30	2	1.30	0.94	9/16	0.55	3147.33	0.19
90187523	LS.A-60-14-SST-1/2-13X4-VD	2.36	1/2-13	5.30	4	1.30	0.94	9/16	0.55	3147.33	0.29
90187525	LS.A-60-14-SST-1/2-13X6-VD	2.36	1/2-13	7.30	6	1.30	0.94	9/16	0.55	3147.33	0.28
90187541	LS.A-60-14-SST-5/8-11X4-VD	2.36	5/8-11	5.30	4	1.30	0.94	5/8	0.55	3147.33	0.40
90187543	LS.A-60-14-SST-5/8-11X6-VD	2.36	5/8-11	7.30	6	1.30	0.94	5/8	0.55	3147.33	0.57
90187545	LS.A-60-14-SST-5/8-11X8-VD	2.36	5/8-11	9.30	8	1.30	0.94	5/8	0.55	3147.33	0.62
90187553	LS.A-60-24-SST-5/8-11X4-VD	2.36	5/8-11	5.69	4	1.69	0.94	15/16	0.94	4046.56	0.57
90187555	LS.A-60-24-SST-5/8-11X6-VD	2.36	5/8-11	7.69	6	1.69	0.94	15/16	0.94	4046.56	0.69
90187557	LS.A-60-24-SST-5/8-11X8-VD	2.36	5/8-11	9.69	8	1.69	0.94	15/16	0.94	4046.56	0.75
90187561	LS.A-60-24-SST-3/4-10X4-VD	2.36	3/4-10	5.69	4	1.69	0.94	15/16	0.94	4046.56	0.74
90187563	LS.A-60-24-SST-3/4-10X6-VD	2.36	3/4-10	7.69	6	1.69	0.94	15/16	0.94	4046.56	0.91
90187565	LS.A-60-24-SST-3/4-10X8-VD	2.36	3/4-10	9.69	8	1.69	0.94	15/16	0.94	4046.56	1.19

* The max static load is the value above which the load applied to the element may cause some plastic material breakage, in particular conditions of use. Obviously, a factor that takes into consideration the importance and the safety level of the specific application must be applied to this value.

- 1
- 2
- 3
- 4
- 5
- 6
- 7
- 8
- 9
- 10
- 11
- 12
- 13
- 14
- 15
- 16
- 17
- 18
- 19



INOX STAINLESS STEEL INCH

LS.A-AS-SST-VD

Code	Description	D	d2A	L	L1	l	l1	h	s	Articulation Ø	Max. limit static load* [lb]	⚖
90188101	LS.A-25-14-AS-SST-3/8-16X2-VD	0.98	3/8-16	2.94	3.06	2	0.94	0.47	9/16	0.55	1573.66	0.11
90188103	LS.A-25-14-AS-SST-3/8-16X4-VD	0.98	3/8-16	4.94	5.06	4	0.94	0.47	9/16	0.55	1573.66	0.22
90188105	LS.A-25-14-AS-SST-3/8-16X6-VD	0.98	3/8-16	6.94	7.06	6	0.94	0.47	9/16	0.55	1573.66	0.11
90188121	LS.A-25-14-AS-SST-1/2-13X2-VD	0.98	1/2-13	2.94	3.06	2	0.94	0.47	9/16	0.55	1573.66	0.13
90188123	LS.A-25-14-AS-SST-1/2-13X4-VD	0.98	1/2-13	4.94	5.06	4	0.94	0.47	9/16	0.55	1573.66	0.23
90188125	LS.A-25-14-AS-SST-1/2-13X6-VD	0.98	1/2-13	6.94	7.06	6	0.94	0.47	9/16	0.55	1573.66	0.22
90188141	LS.A-25-14-AS-SST-5/8-11X4-VD	0.98	5/8-11	4.94	5.06	4	0.94	0.47	5/8	0.55	1573.66	0.34
90188143	LS.A-25-14-AS-SST-5/8-11X6-VD	0.98	5/8-11	6.94	7.06	6	0.94	0.47	5/8	0.55	1573.66	0.50
90188145	LS.A-25-14-AS-SST-5/8-11X8-VD	0.98	5/8-11	8.94	9.06	8	0.94	0.47	5/8	0.55	1573.66	0.56
90188201	LS.A-32-14-AS-SST-3/8-16X2-VD	1.26	3/8-16	2.98	3.10	2	0.98	0.59	9/16	0.55	2023.28	0.12
90188203	LS.A-32-14-AS-SST-3/8-16X4-VD	1.26	3/8-16	4.98	5.10	4	0.98	0.59	9/16	0.55	2023.28	0.23
90188211	LS.A-32-14-AS-SST-3/8-16X6-VD	1.26	3/8-16	6.98	7.10	6	0.98	0.59	9/16	0.55	2023.28	0.13
90188221	LS.A-32-14-AS-SST-1/2-13X2-VD	1.26	1/2-13	2.98	3.10	2	0.98	0.59	9/16	0.55	2023.28	0.14
90188223	LS.A-32-14-AS-SST-1/2-13X4-VD	1.26	1/2-13	4.98	5.10	4	0.98	0.59	9/16	0.55	2023.28	0.25
90188225	LS.A-32-14-AS-SST-1/2-13X6-VD	1.26	1/2-13	6.98	7.10	6	0.98	0.59	9/16	0.55	2023.28	0.23
90188241	LS.A-32-14-AS-SST-5/8-11X4-VD	1.26	5/8-11	4.98	5.10	4	0.98	0.59	5/8	0.55	2023.28	0.35
90188243	LS.A-32-14-AS-SST-5/8-11X6-VD	1.26	5/8-11	6.98	7.10	6	0.98	0.59	5/8	0.55	2023.28	0.52
90188245	LS.A-32-14-AS-SST-5/8-11X8-VD	1.26	5/8-11	8.98	9.10	8	0.98	0.59	5/8	0.55	2023.28	0.57
90188301	LS.A-40-14-AS-SST-3/8-16X2-VD	1.57	3/8-16	2.98	3.10	2	0.98	0.67	9/16	0.55	2922.52	0.14
90188303	LS.A-40-14-AS-SST-3/8-16X4-VD	1.57	3/8-16	4.98	5.10	4	0.98	0.67	9/16	0.55	2922.52	0.25
90188305	LS.A-40-14-AS-SST-3/8-16X6-VD	1.57	3/8-16	6.98	7.10	6	0.98	0.67	9/16	0.55	2922.52	0.15
90188321	LS.A-40-14-AS-SST-1/2-13X2-VD	1.57	1/2-13	2.98	3.10	2	0.98	0.67	9/16	0.55	2922.52	0.16
90188323	LS.A-40-14-AS-SST-1/2-13X4-VD	1.57	1/2-13	4.98	5.10	4	0.98	0.67	9/16	0.55	2922.52	0.26
90188325	LS.A-40-14-AS-SST-1/2-13X6-VD	1.57	1/2-13	6.98	7.10	6	0.98	0.67	9/16	0.55	2922.52	0.25
90188341	LS.A-40-14-AS-SST-5/8-11X4-VD	1.57	5/8-11	4.98	5.10	4	0.98	0.67	5/8	0.55	2922.52	0.37
90188343	LS.A-40-14-AS-SST-5/8-11X6-VD	1.57	5/8-11	6.98	7.10	6	0.98	0.67	5/8	0.55	2922.52	0.54
90188345	LS.A-40-14-AS-SST-5/8-11X8-VD	1.57	5/8-11	8.98	9.10	8	0.98	0.67	5/8	0.55	2922.52	0.59
90188401	LS.A-50-14-AS-SST-3/8-16X2-VD	1.97	3/8-16	3.06	3.18	2	1.06	0.75	9/16	0.55	2922.52	0.16
90188403	LS.A-50-14-AS-SST-3/8-16X4-VD	1.97	3/8-16	5.06	5.18	4	1.06	0.75	9/16	0.55	2922.52	0.27
90188405	LS.A-50-14-AS-SST-3/8-16X6-VD	1.97	3/8-16	7.06	7.18	6	1.06	0.75	9/16	0.55	2922.52	0.17
90188421	LS.A-50-14-AS-SST-1/2-13X2-VD	1.97	1/2-13	3.06	3.18	2	1.06	0.75	9/16	0.55	2922.52	0.18
90188423	LS.A-50-14-AS-SST-1/2-13X4-VD	1.97	1/2-13	5.06	5.18	4	1.06	0.75	9/16	0.55	2922.52	0.29
90188425	LS.A-50-14-AS-SST-1/2-13X6-VD	1.97	1/2-13	7.06	7.18	6	1.06	0.75	9/16	0.55	2922.52	0.27
90188441	LS.A-50-14-AS-SST-5/8-11X4-VD	1.97	5/8-11	5.06	5.18	4	1.06	0.75	5/8	0.55	2922.52	0.39
90188443	LS.A-50-14-AS-SST-5/8-11X6-VD	1.97	5/8-11	7.06	7.18	6	1.06	0.75	5/8	0.55	2922.52	0.56
90188445	LS.A-50-14-AS-SST-5/8-11X8-VD	1.97	5/8-11	9.06	9.18	8	1.06	0.75	5/8	0.55	2922.52	0.62
90188501	LS.A-60-14-AS-SST-3/8-16X2-VD	2.36	3/8-16	3.30	3.42	2	1.30	0.94	9/16	0.55	3147.33	0.21
90188503	LS.A-60-14-AS-SST-3/8-16X4-VD	2.36	3/8-16	5.30	5.42	4	1.30	0.94	9/16	0.55	3147.33	0.31
90188505	LS.A-60-14-AS-SST-3/8-16X6-VD	2.36	3/8-16	7.30	7.42	6	1.30	0.94	9/16	0.55	3147.33	0.21
90188521	LS.A-60-14-AS-SST-1/2-13X2-VD	2.36	1/2-13	3.30	3.42	2	1.30	0.94	9/16	0.55	3147.33	0.22
90188523	LS.A-60-14-AS-SST-1/2-13X4-VD	2.36	1/2-13	5.30	5.42	4	1.30	0.94	9/16	0.55	3147.33	0.33
90188525	LS.A-60-14-AS-SST-1/2-13X6-VD	2.36	1/2-13	7.30	7.42	6	1.30	0.94	9/16	0.55	3147.33	0.31
90188541	LS.A-60-14-AS-SST-5/8-11X4-VD	2.36	5/8-11	5.30	5.42	4	1.30	0.94	5/8	0.55	3147.33	0.43
90188543	LS.A-60-14-AS-SST-5/8-11X6-VD	2.36	5/8-11	7.30	7.42	6	1.30	0.94	5/8	0.55	3147.33	0.60
90188545	LS.A-60-14-AS-SST-5/8-11X8-VD	2.36	5/8-11	9.30	9.42	8	1.30	0.94	5/8	0.55	3147.33	0.65
90188551	LS.A-60-24-AS-SST-5/8-11X4-VD	2.36	5/8-11	5.69	5.81	4	1.69	0.94	15/16	0.94	4046.56	0.57
90188553	LS.A-60-24-AS-SST-5/8-11X6-VD	2.36	5/8-11	7.69	7.81	6	1.69	0.94	15/16	0.94	4046.56	0.69
90188555	LS.A-60-24-AS-SST-5/8-11X8-VD	2.36	5/8-11	9.69	9.81	8	1.69	0.94	15/16	0.94	4046.56	0.75
90188561	LS.A-60-24-AS-SST-3/4-10X4-VD	2.36	3/4-10	5.69	5.81	4	1.69	0.94	15/16	0.94	4046.56	0.74
90188563	LS.A-60-24-AS-SST-3/4-10X6-VD	2.36	3/4-10	7.69	7.81	6	1.69	0.94	15/16	0.94	4046.56	0.91
90188565	LS.A-60-24-AS-SST-3/4-10X8-VD	2.36	3/4-10	9.69	9.81	8	1.69	0.94	15/16	0.94	4046.56	1.19

* The max static load is the value above which the load applied to the element may cause some plastic material breakage, in particular conditions of use. Obviously, a factor that takes into consideration the importance and the safety level of the specific application must be applied to this value.