

- 1
- 2
- 3
- 4
- 5
- 6
- 7
- 8
- 9
- 10
- 11
- 12
- 13
- 14
- 15
- 16
- 17
- 18
- 19

BASE

Glass-fibre reinforced polyamide based (PA) technopolymer, RAL 5005 blue colour, matte finish.
 Produced from FDA compliant raw material (FDA CFR.21 and EU 10/2011).

ARTICULATED STEM

Threaded AISI 304 stainless steel with adjusting square.

STANDARD EXECUTIONS

- LVQ.A-SST-VD: without no-slip disk.
- LVQ.A-AS-SST-VD: with NBR rubber no-slip disk, hardness 70 Shore A, supplied assembled to the base.

FEATURES AND APPLICATIONS

The RAL 5005 blue colour is easily visible in case of accidental food contamination.
 The special knurling under the lower lip of the base provides excellent stability and grip when using the levelling element without no-slip disk even on surfaces that are not perfectly flat.
 The particular assembling system of the no-slip disk to the base assures a perfect anchoring, preventing separation even in case of impact during transport or of adhesion (sticking) to the floor (see No-slip disks on page 835).

ORDER INFORMATION


The levelling elements are supplied unassembled to make carriage and storage easier. The components (base and stem) are supplied in separate packing: less volume taken and better protection from scratches and dirt.
 To order bases and stems separately, see:
 - table of possible combinations Bases/Stems (see page 839)
 - the codes of the Bases (see page 836)
 - the codes of the Stems (see page 985).

ACCESSORIES ON REQUEST

AISI 304 stainless steel nut (see Nuts NT. on page 835).



ELESA Original design




LVQ.A-SST-VD

INOX STAINLESS STEEL INCH


Code	Description	D	d2A	L	l	l1	l2	h	s	Articulation Ø	Max. limit static load* [lbf]	⚖️
90183181	LVQ.A-60-14-SST-5/8-11X4-VD	2.36	5/8-11	5.34	4	1.34	1.28	0.94	1/2	0.55	3147.33	0.43
90183183	LVQ.A-60-14-SST-5/8-11X6-VD	2.36	5/8-11	7.34	6	1.34	1.28	0.94	1/2	0.55	3147.33	0.60
90183185	LVQ.A-60-14-SST-5/8-11X8-VD	2.36	5/8-11	9.34	8	1.34	1.28	0.94	1/2	0.55	3147.33	0.23
90183191	LVQ.A-60-14-SST-3/4-10X4-VD	2.36	3/4-10	5.54	4	1.54	1.44	0.94	9/16	0.55	3147.33	0.23
90183193	LVQ.A-60-14-SST-3/4-10X6-VD	2.36	3/4-10	7.54	6	1.54	1.44	0.94	9/16	0.55	3147.33	0.23
90183195	LVQ.A-60-14-SST-3/4-10X8-VD	2.36	3/4-10	9.54	8	1.54	1.44	0.94	9/16	0.55	3147.33	0.23
90183251	LVQ.A-70-14-SST-5/8-11X4-VD	2.76	5/8-11	5.14	4	1.14	1.08	0.75	1/2	0.55	3147.33	0.43
90183253	LVQ.A-70-14-SST-5/8-11X6-VD	2.76	5/8-11	7.14	6	1.14	1.08	0.75	1/2	0.55	3147.33	0.60
90183255	LVQ.A-70-14-SST-5/8-11X8-VD	2.76	5/8-11	9.14	8	1.14	1.08	0.75	1/2	0.55	3147.33	0.23
90183261	LVQ.A-70-14-SST-3/4-10X4-VD	2.76	3/4-10	5.34	4	1.34	1.24	0.75	9/16	0.55	3147.33	0.23
90183263	LVQ.A-70-14-SST-3/4-10X6-VD	2.76	3/4-10	7.34	6	1.34	1.24	0.75	9/16	0.55	3147.33	0.23
90183265	LVQ.A-70-14-SST-3/4-10X8-VD	2.76	3/4-10	9.34	8	1.34	1.24	0.75	9/16	0.55	3147.33	0.23
90183381	LVQ.A-80-14-SST-5/8-11X4-VD	3.15	5/8-11	5.34	4	1.34	1.28	0.94	1/2	0.55	3596.94	0.49
90183383	LVQ.A-80-14-SST-5/8-11X6-VD	3.15	5/8-11	7.34	6	1.34	1.28	0.94	1/2	0.55	3596.94	0.66
90183385	LVQ.A-80-14-SST-5/8-11X8-VD	3.15	5/8-11	9.34	8	1.34	1.28	0.94	1/2	0.55	3596.94	0.29
90183391	LVQ.A-80-14-SST-3/4-10X4-VD	3.15	3/4-10	5.54	4	1.54	1.44	0.94	9/16	0.55	3596.94	0.29
90183393	LVQ.A-80-14-SST-3/4-10X6-VD	3.15	3/4-10	7.54	6	1.54	1.44	0.94	9/16	0.55	3596.94	0.29
90183395	LVQ.A-80-14-SST-3/4-10X8-VD	3.15	3/4-10	9.54	8	1.54	1.44	0.94	9/16	0.55	3596.94	0.29
90183481	LVQ.A-100-14-SST-5/8-11X4-VD	3.94	5/8-11	5.34	4	1.34	1.28	0.94	1/2	0.55	3596.94	0.55
90183483	LVQ.A-100-14-SST-5/8-11X6-VD	3.94	5/8-11	7.34	6	1.34	1.28	0.94	1/2	0.55	3596.94	0.73
90183485	LVQ.A-100-14-SST-5/8-11X8-VD	3.94	5/8-11	9.34	8	1.34	1.28	0.94	1/2	0.55	3596.94	0.35
90183491	LVQ.A-100-14-SST-3/4-10X4-VD	3.94	3/4-10	5.54	4	1.54	1.44	0.94	9/16	0.55	3596.94	0.35
90183493	LVQ.A-100-14-SST-3/4-10X6-VD	3.94	3/4-10	7.54	6	1.54	1.44	0.94	9/16	0.55	3596.94	0.35
90183495	LVQ.A-100-14-SST-3/4-10X8-VD	3.94	3/4-10	9.54	8	1.54	1.44	0.94	9/16	0.55	3596.94	0.35

* The max static load is the value above which the load applied to the element may cause some plastic material breakage, in particular conditions of use. Obviously, a factor that takes into consideration the importance and the safety level of the specific application must be applied to this value.



Levelling elements and supports

- 1
- 2
- 3
- 4
- 5
- 6
- 7
- 8
- 9
- 10
- 11
- 12
- 13
- 14
- 15
- 16
- 17
- 18
- 19



INOX STAINLESS STEEL **INCH**

LVQ.A-AS-SST-VD

Code	Description	D	d2A	L	L1	l	l1	l2	h	s	Articulation ∅	Max. limit static load* [lbf]	ΔΔ
90184181	LVQ.A-60-14-AS-SST-5/8-11X4-VD	2.36	5/8-11	5.34	5.46	4	1.34	1.28	0.94	1/2	0.55	3147.33	0.47
90184183	LVQ.A-60-14-AS-SST-5/8-11X6-VD	2.36	5/8-11	7.34	7.46	6	1.34	1.28	0.94	1/2	0.55	3147.33	0.64
90184185	LVQ.A-60-14-AS-SST-5/8-11X8-VD	2.36	5/8-11	9.34	9.46	8	1.34	1.28	0.94	1/2	0.55	3147.33	0.27
90184191	LVQ.A-60-14-AS-SST-3/4-10X4-VD	2.36	3/4-10	5.54	5.65	4	1.54	1.44	0.94	9/16	0.55	3147.33	0.27
90184193	LVQ.A-60-14-AS-SST-3/4-10X6-VD	2.36	3/4-10	7.54	7.65	6	1.54	1.44	0.94	9/16	0.55	3147.33	0.27
90184195	LVQ.A-60-14-AS-SST-3/4-10X8-VD	2.36	3/4-10	9.54	9.65	8	1.54	1.44	0.94	9/16	0.55	3147.33	0.27
90184251	LVQ.A-70-14-AS-SST-5/8-11X4-VD	2.76	5/8-11	5.14	5.26	4	1.14	1.08	0.75	1/2	0.55	3147.33	0.48
90184253	LVQ.A-70-14-AS-SST-5/8-11X6-VD	2.76	5/8-11	7.14	7.26	6	1.14	1.08	0.75	1/2	0.55	3147.33	0.65
90184255	LVQ.A-70-14-AS-SST-5/8-11X8-VD	2.76	5/8-11	9.14	9.26	8	1.14	1.08	0.75	1/2	0.55	3147.33	0.28
90184261	LVQ.A-70-14-AS-SST-3/4-10X4-VD	2.76	3/4-10	5.34	5.46	4	1.34	1.24	0.75	9/16	0.55	3147.33	0.28
90184263	LVQ.A-70-14-AS-SST-3/4-10X6-VD	2.76	3/4-10	7.34	7.46	6	1.34	1.24	0.75	9/16	0.55	3147.33	0.28
90184265	LVQ.A-70-14-AS-SST-3/4-10X8-VD	2.76	3/4-10	9.34	9.46	8	1.34	1.24	0.75	9/16	0.55	3147.33	0.28
90184381	LVQ.A-80-14-AS-SST-5/8-11X4-VD	3.15	5/8-11	5.34	5.46	4	1.34	1.28	0.94	1/2	0.55	3596.94	0.53
90184383	LVQ.A-80-14-AS-SST-5/8-11X6-VD	3.15	5/8-11	7.34	7.46	6	1.34	1.28	0.94	1/2	0.55	3596.94	0.71
90184385	LVQ.A-80-14-AS-SST-5/8-11X8-VD	3.15	5/8-11	9.34	9.46	8	1.34	1.28	0.94	1/2	0.55	3596.94	0.33
90184391	LVQ.A-80-14-AS-SST-3/4-10X4-VD	3.15	3/4-10	5.54	5.65	4	1.54	1.44	0.94	9/16	0.55	3596.94	0.33
90184393	LVQ.A-80-14-AS-SST-3/4-10X6-VD	3.15	3/4-10	7.54	7.65	6	1.54	1.44	0.94	9/16	0.55	3596.94	0.33
90184395	LVQ.A-80-14-AS-SST-3/4-10X8-VD	3.15	3/4-10	9.54	9.65	8	1.54	1.44	0.94	9/16	0.55	3596.94	0.33
90184481	LVQ.A-100-14-AS-SST-5/8-11X4-VD	3.94	5/8-11	5.34	5.46	4	1.34	1.28	0.94	1/2	0.55	3596.94	0.64
90184483	LVQ.A-100-14-AS-SST-5/8-11X6-VD	3.94	5/8-11	7.34	7.46	6	1.34	1.28	0.94	1/2	0.55	3596.94	0.82
90184485	LVQ.A-100-14-AS-SST-5/8-11X8-VD	3.94	5/8-11	9.34	9.46	8	1.34	1.28	0.94	1/2	0.55	3596.94	0.45
90184491	LVQ.A-100-14-AS-SST-3/4-10X4-VD	3.94	3/4-10	5.54	5.65	4	1.54	1.44	0.94	9/16	0.55	3596.94	0.45
90184493	LVQ.A-100-14-AS-SST-3/4-10X6-VD	3.94	3/4-10	7.54	7.65	6	1.54	1.44	0.94	9/16	0.55	3596.94	0.45
90184495	LVQ.A-100-14-AS-SST-3/4-10X8-VD	3.94	3/4-10	9.54	9.65	8	1.54	1.44	0.94	9/16	0.55	3596.94	0.45

* The max static load is the value above which the load applied to the element may cause some plastic material breakage, in particular conditions of use. Obviously, a factor that takes into consideration the importance and the safety level of the specific application must be applied to this value.

Levelling elements and supports