




METRIC



ELESA Original design



METRIC

BASE

Glass-fibre reinforced polyamide based (PA) technopolymer, RAL 5005 blue colour, matte finish.

Produced from FDA compliant raw material (FDA CFR.21 and EU 10/2011).

ARTICULATED STEM

Glass-fibre reinforced polyamide based (PA) SUPER-technopolymer, RAL 5005 blue colour, with hexagonal socket and regulation hexagon.

Produced from FDA compliant raw material (FDA CFR.21 and EU 10/2011).

STANDARD EXECUTIONS

- **LS.A-STP-VD**: without no-slip disk.

- **LS.A-AS-STP-VD**: with NBR rubber no-slip disk, hardness 70 Shore A, supplied assembled to the base, suitable for food contact (FDA CFR.21 and EU 10/2011).

FEATURES

The RAL 5005 blue colour is easily visible in case of accidental food contamination.

Thanks to the property of the SUPER-technopolymer stem, high rigidity and mechanical resistance are obtained in addition to natural resistance to corrosion.

The particular assembling system of the no-slip disk to the base assures a perfect anchoring, preventing separation even in case of impact during transport or of adhesion (sticking) to the floor (see No-slip disks on page).

ORDER INFORMATION

The levelling feet are supplied unassembled to make carriage and storage easier. The components (base and stem) are supplied in separate packing: less volume taken and better protection from scratches and dirt.

To order bases and stems separately, see:

- table of possible combinations Bases/Stems (see page 839)
- the codes of the Bases (see page 836)
- the codes of the Stems (see page ...).

ACCESSORIES ON REQUEST


NT. (see page -): AISI 304 stainless steel or zinc-plated steel nut.

LS.A-STP-VD

Code	Description	D	d	L	l	l1	l2	h	s	s1	Articulation Ø	Max. limit static load* [N]	
187102	LS.A-25-14-STP-M8x44-VD	25	M8	68	44	24	5	12	16	3	14	2500	10
187104	LS.A-25-14-STP-M8x69-VD	25	M8	93	69	24	5	12	16	3	14	2500	12
187112	LS.A-25-14-STP-M10x44-VD	25	M10	68	44	24	6	12	16	4	14	3500	12
187114	LS.A-25-14-STP-M10x69-VD	25	M10	93	69	24	6	12	16	4	14	3500	14
187116	LS.A-25-14-STP-M10x99-VD	25	M10	123	99	24	6	12	16	4	14	3500	17
187122	LS.A-25-14-STP-M12x44-VD	25	M12	68	44	24	7	12	16	5	14	4500	13
187124	LS.A-25-14-STP-M12x69-VD	25	M12	93	69	24	7	12	16	5	14	4500	17
187126	LS.A-25-14-STP-M12x99-VD	25	M12	123	99	24	7	12	16	5	14	4500	21
187142	LS.A-25-14-STP-M16x69-VD	25	M16	96	69	27	7	12	22	6	14	5500	27
187144	LS.A-25-14-STP-M16x109-VD	25	M16	136	109	27	7	12	22	6	14	5500	37
187146	LS.A-25-14-STP-M16x149-VD	25	M16	176	149	27	7	12	22	6	14	5000	46
187148	LS.A-25-14-STP-M16x169-VD	25	M16	196	169	27	7	12	22	6	14	5000	51
187202	LS.A-32-14-STP-M8x44-VD	32	M8	70	44	25	5	15	16	3	14	2500	15
187204	LS.A-32-14-STP-M8x69-VD	32	M8	95	69	25	5	15	16	3	14	2500	16
187212	LS.A-32-14-STP-M10x44-VD	32	M10	70	44	25	6	15	16	4	14	3500	16
187214	LS.A-32-14-STP-M10x69-VD	32	M10	95	69	25	6	15	16	4	14	3500	18
187216	LS.A-32-14-STP-M10x99-VD	32	M10	125	99	25	6	15	16	4	14	3500	21
187222	LS.A-32-14-STP-M12x44-VD	32	M12	70	44	25	7	15	16	5	14	4500	18
187224	LS.A-32-14-STP-M12x69-VD	32	M12	95	69	25	7	15	16	5	14	4500	21
187226	LS.A-32-14-STP-M12x99-VD	32	M12	125	99	25	7	15	16	5	14	4500	25
187242	LS.A-32-14-STP-M16x69-VD	32	M16	97	69	28	7	15	22	6	14	5500	31
187244	LS.A-32-14-STP-M16x109-VD	32	M16	137	109	28	7	15	22	6	14	5500	42
187246	LS.A-32-14-STP-M16x149-VD	32	M16	177	149	28	7	15	22	6	14	5000	50
187248	LS.A-32-14-STP-M16x169-VD	32	M16	197	169	28	7	15	22	6	14	5000	55

* The max static load is the value above which the load applied to the element may cause some plastic material breakage, in particular conditions of use. Obviously, a factor that takes into consideration the importance and the safety level of the specific application must be applied to this value.

Conversion Table	
1 mm = 0.039 inch	
D	
mm	inch
25	0.98
32	1.25
40	1.56
50	1.95
60	2.34




LS.A-STP-VD

METRIC

Code	Description	D	d	L	l	l1	l2	h	s	s1	Articulation Ø	Max. limit static load* [N]	⚖
187302	LS.A-40-14-STP-M8x44-VD	40	M8	69	44	25	5	16.5	16	3	14	2500	20
187304	LS.A-40-14-STP-M8x69-VD	40	M8	94	69	25	5	16.5	16	3	14	2500	21
187312	LS.A-40-14-STP-M10x44-VD	40	M10	69	44	25	6	16.5	16	4	14	3500	21
187314	LS.A-40-14-STP-M10x69-VD	40	M10	94	69	25	6	16.5	16	4	14	3500	24
187316	LS.A-40-14-STP-M10x99-VD	40	M10	124	99	25	6	16.5	16	4	14	3500	27
187322	LS.A-40-14-STP-M12x44-VD	40	M12	69	44	25	7	16.5	16	5	14	4500	23
187324	LS.A-40-14-STP-M12x69-VD	40	M12	94	69	25	7	16.5	16	5	14	4500	26
187326	LS.A-40-14-STP-M12x99-VD	40	M12	124	99	25	7	16.5	16	5	14	4500	31
187342	LS.A-40-14-STP-M16x69-VD	40	M16	96.5	69	27.5	7	16.5	22	6	14	5500	36
187344	LS.A-40-14-STP-M16x109-VD	40	M16	136.5	109	27.5	7	16.5	22	6	14	5500	47
187346	LS.A-40-14-STP-M16x149-VD	40	M16	176.5	149	27.5	7	16.5	22	6	14	5000	55
187348	LS.A-40-14-STP-M16x169-VD	40	M16	196.5	169	27.5	7	16.5	22	6	14	5000	60
187402	LS.A-50-14-STP-M8x44-VD	50	M8	72	44	28	5	18	16	3	14	2500	26
187404	LS.A-50-14-STP-M8x69-VD	50	M8	97	69	28	5	18	16	3	14	2500	27
187412	LS.A-50-14-STP-M10x44-VD	50	M10	72	44	28	6	18	16	4	14	3500	27
187414	LS.A-50-14-STP-M10x69-VD	50	M10	97	69	28	6	18	16	4	14	3500	29
187416	LS.A-50-14-STP-M10x99-VD	50	M10	127	99	28	6	18	16	4	14	3500	32
187422	LS.A-50-14-STP-M12x44-VD	50	M12	72	44	28	7	18	16	5	14	4500	29
187424	LS.A-50-14-STP-M12x69-VD	50	M12	97	69	28	7	18	16	5	14	4500	32
187426	LS.A-50-14-STP-M12x99-VD	50	M12	127	99	28	7	18	16	5	14	4500	36
187442	LS.A-50-14-STP-M16x69-VD	50	M16	99	69	30	7	18	22	6	14	5500	42
187444	LS.A-50-14-STP-M16x109-VD	50	M16	139	109	30	7	18	22	6	14	5500	53
187446	LS.A-50-14-STP-M16x149-VD	50	M16	179	149	30	7	18	22	6	14	5000	61
187448	LS.A-50-14-STP-M16x169-VD	50	M16	199	169	30	7	18	22	6	14	5000	66
187502	LS.A-60-14-STP-M8x44-VD	60	M8	79	44	33	5	24	16	3	14	2500	39
187504	LS.A-60-14-STP-M8x69-VD	60	M8	104	69	33	5	24	16	3	14	2500	40
187512	LS.A-60-14-STP-M10x44-VD	60	M10	79	44	33	6	24	16	4	14	3500	40
187514	LS.A-60-14-STP-M10x69-VD	60	M10	104	69	33	6	24	16	4	14	3500	43
187516	LS.A-60-14-STP-M10x99-VD	60	M10	134	99	33	6	24	16	4	14	3500	43
187522	LS.A-60-14-STP-M12x44-VD	60	M12	79	44	33	7	24	16	5	14	4500	43
187524	LS.A-60-14-STP-M12x69-VD	60	M12	104	69	33	7	24	16	5	14	4500	45
187526	LS.A-60-14-STP-M12x99-VD	60	M12	134	99	33	7	24	16	5	14	4500	49
187542	LS.A-60-14-STP-M16x69-VD	60	M16	106	69	37	7	24	22	6	14	5500	55
187544	LS.A-60-14-STP-M16x109-VD	60	M16	146	109	37	7	24	22	6	14	5500	66
187546	LS.A-60-14-STP-M16x149-VD	60	M16	186	149	37	7	24	22	6	14	5000	74
187548	LS.A-60-14-STP-M16x169-VD	60	M16	206	169	37	7	24	22	6	14	5000	79


* The max static load is the value above which the load applied to the element may cause some plastic material breakage, in particular conditions of use. Obviously, a factor that takes into consideration the importance and the safety level of the specific application must be applied to this value.





Levelling feet and supports

Conversion Table	
1 mm = 0,039 inch	
D	
mm	inch
25	0.98
32	1.25
40	1.56
50	1.95
60	2.34




METRIC

LS.A-AS-STP-VD

Code	Description	D	d	L	L1	l	l1	l2	h	s	s1	Articulation Ø	Max. limit static load* [N]	⚖️
188102	LS.A-25-14-AS-STP-M8x44-VD	25	M8	69	72	44	25	5	12	16	3	14	2500	13
188104	LS.A-25-14-AS-STP-M8x69-VD	25	M8	94	97	69	25	5	12	16	3	14	2500	14
188112	LS.A-25-14-AS-STP-M10x44-VD	25	M10	69	72	44	25	6	12	16	4	14	3500	14
188114	LS.A-25-14-AS-STP-M10x69-VD	25	M10	94	97	69	25	6	12	16	4	14	3500	17
188116	LS.A-25-14-AS-STP-M10x99-VD	25	M10	124	127	99	25	6	12	16	4	14	3500	19
188122	LS.A-25-14-AS-STP-M12x44-VD	25	M12	69	72	44	25	7	12	16	5	14	4500	16
188124	LS.A-25-14-AS-STP-M12x69-VD	25	M12	94	97	69	25	7	12	16	5	14	4500	19
188126	LS.A-25-14-AS-STP-M12x99-VD	25	M12	124	127	99	25	7	12	16	5	14	4500	23
188142	LS.A-25-14-AS-STP-M16x69-VD	25	M16	96	99	69	27	7	12	22	6	14	5500	29
188144	LS.A-25-14-AS-STP-M16x109-VD	25	M16	136	139	109	27	7	12	22	6	14	5500	40
188146	LS.A-25-14-AS-STP-M16x149-VD	25	M16	176	179	149	27	7	12	22	6	14	5000	48
188148	LS.A-25-14-AS-STP-M16x169-VD	25	M16	196	199	169	27	7	12	22	6	14	5000	53
188202	LS.A-32-14-AS-STP-M8x44-VD	32	M8	70	73	44	26	5	15	16	3	14	2500	19
188204	LS.A-32-14-AS-STP-M8x69-VD	32	M8	95	98	69	26	5	15	16	3	14	2500	21
188212	LS.A-32-14-AS-STP-M10x44-VD	32	M10	70	73	44	26	6	15	16	4	14	3500	21
188214	LS.A-32-14-AS-STP-M10x69-VD	32	M10	95	98	69	26	6	15	16	4	14	3500	23
188216	LS.A-32-14-AS-STP-M10x99-VD	32	M10	125	128	99	26	6	15	16	4	14	3500	26
188222	LS.A-32-14-AS-STP-M12x44-VD	32	M12	70	73	44	26	7	15	16	5	14	4500	22
188224	LS.A-32-14-AS-STP-M12x69-VD	32	M12	95	98	69	26	7	15	16	5	14	4500	25
188226	LS.A-32-14-AS-STP-M12x99-VD	32	M12	125	128	99	26	7	15	16	5	14	4500	30
188242	LS.A-32-14-AS-STP-M16x69-VD	32	M16	97	100	69	28	7	15	22	6	14	5500	36
188244	LS.A-32-14-AS-STP-M16x109-VD	32	M16	137	140	109	28	7	15	22	6	14	5500	46
188246	LS.A-32-14-AS-STP-M16x149-VD	32	M16	177	180	149	28	7	15	22	6	14	5000	55
188248	LS.A-32-14-AS-STP-M16x169-VD	32	M16	197	200	169	28	7	15	22	6	14	5000	59

* The max static load is the value above which the load applied to the element may cause some plastic material breakage, in particular conditions of use. Obviously, a factor that takes into consideration the importance and the safety level of the specific application must be applied to this value.

Conversion Table	
1 mm = 0.039 inch	
D	
mm	inch
25	0.98
32	1.25
40	1.56
50	1.95
60	2.34



LS.A-AS-STP-VD

METRIC

Code	Description	D	d	L	L1	I	I1	I2	h	s	s1	Articulation Ø	Max. limit static load* [N]	
188302	LS.A-40-14-AS-STP-M8x44-VD	40	M8	69.5	72.5	44	25.5	5	16.5	16	3	14	2500	27
188304	LS.A-40-14-AS-STP-M8x69-VD	40	M8	94.5	97.5	69	25.5	5	16.5	16	3	14	2500	28
188312	LS.A-40-14-AS-STP-M10x44-VD	40	M10	69.5	72.5	44	25.5	6	16.5	16	4	14	3500	28
188314	LS.A-40-14-AS-STP-M10x69-VD	40	M10	94.5	97.5	69	25.5	6	16.5	16	4	14	3500	31
188316	LS.A-40-14-AS-STP-M10x99-VD	40	M10	124.5	127.5	99	25.5	6	16.5	16	4	14	3500	34
188322	LS.A-40-14-AS-STP-M12x44-VD	40	M12	69.5	72.5	44	25.5	7	16.5	16	5	14	4500	30
188324	LS.A-40-14-AS-STP-M12x69-VD	40	M12	94.5	97.5	69	25.5	7	16.5	16	5	14	4500	33
188326	LS.A-40-14-AS-STP-M12x99-VD	40	M12	124.5	127.5	99	25.5	7	16.5	16	5	14	4500	38
188342	LS.A-40-14-AS-STP-M16x69-VD	40	M16	96.5	99.5	69	27.5	7	16.5	22	6	14	5500	44
188344	LS.A-40-14-AS-STP-M16x109-VD	40	M16	136.5	139.5	109	27.5	7	16.5	22	6	14	5500	54
188346	LS.A-40-14-AS-STP-M16x149-VD	40	M16	176.5	179.5	149	27.5	7	16.5	22	6	14	5000	62
188348	LS.A-40-14-AS-STP-M16x169-VD	40	M16	196.5	199.5	169	27.5	7	16.5	22	6	14	5000	67
188402	LS.A-50-14-AS-STP-M8x44-VD	50	M8	72	75	44	28	5	18	16	3	14	2500	31
188404	LS.A-50-14-AS-STP-M8x69-VD	50	M8	97	100	69	28	5	18	16	3	14	2500	32
188412	LS.A-50-14-AS-STP-M10x44-VD	50	M10	72	75	44	28	6	18	16	4	14	3500	32
188414	LS.A-50-14-AS-STP-M10x69-VD	50	M10	97	100	69	28	6	18	16	4	14	3500	34
188416	LS.A-50-14-AS-STP-M10x99-VD	50	M10	127	130	99	28	6	18	16	4	14	3500	37
188422	LS.A-50-14-AS-STP-M12x44-VD	50	M12	72	75	44	28	7	18	16	5	14	4500	34
188424	LS.A-50-14-AS-STP-M12x69-VD	50	M12	97	100	69	28	7	18	16	5	14	4500	37
188426	LS.A-50-14-AS-STP-M12x99-VD	50	M12	127	130	99	28	7	18	16	5	14	4500	41
188442	LS.A-50-14-AS-STP-M16x69-VD	50	M16	99	102	69	30	7	18	22	6	14	5500	47
188444	LS.A-50-14-AS-STP-M16x109-VD	50	M16	139	142	109	30	7	18	22	6	14	5500	57
188446	LS.A-50-14-AS-STP-M16x149-VD	50	M16	179	182	149	30	7	18	22	6	14	5000	66
188448	LS.A-50-14-AS-STP-M16x169-VD	50	M16	199	202	169	30	7	18	22	6	14	5000	71
188502	LS.A-60-14-AS-STP-M8x44-VD	60	M8	79	82	44	35	5	24	16	3	14	2500	60
188504	LS.A-60-14-AS-STP-M8x69-VD	60	M8	104	107	69	35	5	24	16	3	14	2500	62
188512	LS.A-60-14-AS-STP-M10x44-VD	60	M10	79	82	44	35	6	24	16	4	14	3500	62
188514	LS.A-60-14-AS-STP-M10x69-VD	60	M10	104	107	69	35	6	24	16	4	14	3500	64
188516	LS.A-60-14-AS-STP-M10x99-VD	60	M10	134	137	99	35	6	24	16	4	14	3500	67
188522	LS.A-60-14-AS-STP-M12x44-VD	60	M12	79	82	44	35	7	24	16	5	14	4500	63
188524	LS.A-60-14-AS-STP-M12x69-VD	60	M12	104	107	69	35	7	24	16	5	14	4500	67
188526	LS.A-60-14-AS-STP-M12x99-VD	60	M12	134	137	99	35	7	24	16	5	14	4500	71
188542	LS.A-60-14-AS-STP-M16x69-VD	60	M16	106	109	69	37	7	24	22	6	14	5500	77
188544	LS.A-60-14-AS-STP-M16x109-VD	60	M16	146	149	109	37	7	24	22	6	14	5500	87
188546	LS.A-60-14-AS-STP-M16x149-VD	60	M16	186	189	149	37	7	24	22	6	14	5000	96
188548	LS.A-60-14-AS-STP-M16x169-VD	60	M16	206	209	169	37	7	24	22	6	14	5000	100

* The max static load is the value above which the load applied to the element may cause some plastic material breakage, in particular conditions of use. Obviously, a factor that takes into consideration the importance and the safety level of the specific application must be applied to this value.