





MATERIAL

Anodised aluminium bracket, black colour.
Screw and centering bushings MM-CC (see page -) in black-oxide steel.
Zinc-plated steel washers.

FEATURES

The mounting brackets allow a quick and effective assembly of the pneumatic fastening clamps MM-BL (see page -), MM-BI (see page -) or MM-BC (see page -) for the different applications.
The bearings surface is used for the purpose of positioning the brackets precisely, while the centering bushings MM-CC (included in the supply) ensure the correct axially of the loads with respect to the bearing surface.



Conversion Table			
1 mm = 0.039 inch			
l1		l2	
mm	inch	mm	inch
51.35	2.02	38	1.26
61.35	2.42	48	1.65
72.35	2.85	58	2.44

Code	Description	d1	d2	d4 H8 / h6	l1	l2	l3	l4	l5	l6	l7	m1	m2	△
MM.22020	MM-SBA-20	28	M8	11	51.35	38	39	36	35	16	16	26	25.85	200
MM.22032	MM-SBA-32	40	M10	13	61.35	48	54	51	39	21	21	38	29.35	560
MM.22040	MM-SBA-40	50	M12	16	72.35	58	64	61	47	26	26	45	33.85	800