



1

LEVER BODY

Glass-fibre reinforced polyamide based (PA) technopolymer, RAL 7021 grey-black colour, RAL 2004 (C2-C1) orange colour, matte finish.



2

PUSH BUTTON

Technopolymer, black colour, matte finish.



3

STANDARD EXECUTIONS

Glass-fibre reinforced technopolymer clamping element with retaining pin, black colour, with knurling on the protruding part to make initial tightening easier. AISI 302 stainless steel return spring.

- **MRX-B:** brass boss, threaded blind hole.
- **MRX-SST:** AISI 303 stainless steel boss, threaded blind hole.
- **MRX-p:** zinc-plated steel threaded stud, chamfered flat end ISO 4753 (see Technical Data on page A-11).
- **MRX-SST-p:** AISI 303 stainless steel threaded stud, chamfered flat end ISO 4753 (see Technical Data on page A-11).



4



5



6



7



8



9



10



11



12



13



14



15



16



17



18




19



20



ELESA Original design **if**
Hannover

**MRX-B****INCH**

Code	Description	R	d6H	L	D	H	H1	h	h1	h2	h3	d1	Teeth no.	
941131	MRX.40 B-10-24	1.65	10-24	1.97	0.71	1.26	1.4	0.39	1.14	0.24	0.55	0.47	18	0.02
941131-C2-C1	MRX.40-C2-B-10-24-C1	1.65	10-24	1.97	0.71	1.26	1.4	0.39	1.14	0.24	0.55	0.47	18	0.02
941133	MRX.40 B-10-32	1.65	10-32	1.97	0.71	1.26	1.4	0.39	1.14	0.24	0.55	0.47	18	0.02
941133-C2-C1	MRX.40-C2-B-10-32-C1	1.65	10-32	1.97	0.71	1.26	1.4	0.39	1.14	0.24	0.55	0.47	18	0.02
941141	MRX.40 B-1/4-20	1.65	1/4-20	1.97	0.71	1.26	1.4	0.39	1.14	0.24	0.55	0.47	18	0.03
941141-C2-C1	MRX.40-C2-B-1/4-20-C1	1.65	1/4-20	1.97	0.71	1.26	1.4	0.39	1.14	0.24	0.55	0.47	18	0.03
941411	MRX.63 B-1/4-20	2.48	1/4-20	2.87	0.91	1.69	1.83	0.47	1.46	0.31	0.67	0.59	20	0.05
941411-C2-C1	MRX.63-C2-B-1/4-20-C1	2.48	1/4-20	2.87	0.91	1.69	1.83	0.47	1.46	0.31	0.67	0.59	20	0.05
941421	MRX.63 B-5/16-18	2.48	5/16-18	2.87	0.91	1.69	1.83	0.51	1.46	0.31	0.67	0.59	20	0.05
941421-C2-C1	MRX.63-C2-B-5/16-18-C1	2.48	5/16-18	2.87	0.91	1.69	1.83	0.51	1.46	0.31	0.67	0.59	20	0.05
942111	MRX.80 B-5/16-18	3.15	5/16-18	3.62	1.1	2.13	2.3	0.71	1.85	0.39	0.87	0.75	24	0.1
942111-C2-C1	MRX.80-C2-B-5/16-18-C1	3.15	5/16-18	3.62	1.1	2.13	2.3	0.71	1.85	0.39	0.87	0.75	24	0.1
942121	MRX.80 B-3/8-16	3.15	3/8-16	3.62	1.1	2.13	2.3	0.67	1.85	0.39	0.87	0.75	24	0.11
942121-C2-C1	MRX.80-C2-B-3/8-16-C1	3.15	3/8-16	3.62	1.1	2.13	2.3	0.67	1.85	0.39	0.87	0.75	24	0.11
942131	MRX.80 B-1/2-13	3.15	1/2-13	3.62	1.1	2.13	2.3	0.67	1.85	0.39	0.87	0.75	24	0.11
942131-C2-C1	MRX.80-C2-B-1/2-13-C1	3.15	1/2-13	3.62	1.1	2.13	2.3	0.67	1.85	0.39	0.87	0.75	24	0.11
942501	MRX.100 B-3/8-16	3.94	3/8-16	4.49	1.3	2.56	2.74	0.79	2.13	0.47	0.98	0.98	28	0.17
942501-C2-C1	MRX.100-C2-B-3/8-16-C1	3.94	3/8-16	4.49	1.3	2.56	2.74	0.79	2.13	0.47	0.98	0.98	28	0.17
942511	MRX.100 B-1/2-13	3.94	1/2-13	4.49	1.3	2.56	2.74	0.79	2.13	0.47	0.98	0.98	28	0.18
942511-C2-C1	MRX.100-C2-B-1/2-13-C1	3.94	1/2-13	4.49	1.3	2.56	2.74	0.79	2.13	0.47	0.98	0.98	28	0.18

MRX-SST**INOX STAINLESS STEEL****INCH**

Code	Description	R	d6H	L	D	H	H1	h	h1	h2	h3	d1	Teeth no.	
941191	MRX.40-SST-1/4-20	1.65	1/4-20	1.97	0.71	1.26	1.4	0.39	1.14	0.24	0.55	0.47	18	0.03
941191-C2-C1	MRX.40-C2-SST-1/4-20-C1	1.65	1/4-20	1.97	0.71	1.26	1.4	0.39	1.14	0.24	0.55	0.47	18	0.03
941431	MRX.63-SST-5/16-18	2.48	5/16-18	2.87	0.91	1.69	1.83	0.51	1.46	0.31	0.67	0.59	20	0.05
941431-C2-C1	MRX.63-C2-SST-5/16-18-C1	2.48	5/16-18	2.87	0.91	1.69	1.83	0.51	1.46	0.31	0.67	0.59	20	0.05
942151	MRX.80-SST-3/8-16	3.15	3/8-16	3.62	1.1	2.13	2.3	0.67	1.85	0.39	0.87	0.75	24	0.1
942151-C2-C1	MRX.80-C2-SST-3/8-16-C1	3.15	3/8-16	3.62	1.1	2.13	2.3	0.67	1.85	0.39	0.87	0.75	24	0.1





1



2



3



4



5



6



7



8



9



10



11



12



13



14



15



16



17






18



19



20

MRX-p
MRX-SST-p

MRX-p

INCH

Code	Description	R	d2A	L	D	H	H1	h1	h2	h3	d1	l	Teeth nr	⚖
941221	MRX.40 p-10-24x3/4	1.65	10-24	1.97	0.71	1.26	1.4	1.14	0.24	0.55	0.47	0.750	18	0.03
941221-C2-C1	MRX.40-C2-p-10-24x3/4-C1	1.65	10-24	1.97	0.71	1.26	1.4	1.14	0.24	0.55	0.47	0.750	18	0.03
941241	MRX.40 p-10-32x1/2	1.65	10-32	1.97	0.71	1.26	1.4	1.14	0.24	0.55	0.47	0.500	18	0.02
941241-C2-C1	MRX.40-C2-p-10-32x1/2-C1	1.65	10-32	1.97	0.71	1.26	1.4	1.14	0.24	0.55	0.47	0.500	18	0.02
941243	MRX.40 p-10-32x3/4	1.65	10-32	1.97	0.71	1.26	1.4	1.14	0.24	0.55	0.47	0.750	18	0.02
941243-C2-C1	MRX.40-C2-p-10-32x3/4-C1	1.65	10-32	1.97	0.71	1.26	1.4	1.14	0.24	0.55	0.47	0.750	18	0.02
941301	MRX.40 p-1/4-20x1/2	1.65	1/4-20	1.97	0.71	1.26	1.4	1.14	0.24	0.55	0.47	0.500	18	0.03
941301-C2-C1	MRX.40-C2-p-1/4-20x1/2 -C1	1.65	1/4-20	1.97	0.71	1.26	1.4	1.14	0.24	0.55	0.47	0.500	18	0.03
941321	MRX.40 p-1/4-20x3/4	1.65	1/4-20	1.97	0.71	1.26	1.4	1.14	0.24	0.55	0.47	0.750	18	0.03
941321-C2-C1	MRX.40-C2-p-1/4-20x3/4 -C1	1.65	1/4-20	1.97	0.71	1.26	1.4	1.14	0.24	0.55	0.47	0.750	18	0.03
941331	MRX.40 p-1/4-20x1	1.65	1/4-20	1.97	0.71	1.26	1.4	1.14	0.24	0.55	0.47	1.000	18	0.04
941331-C2-C1	MRX.40-C2-p-1/4-20x1-C1	1.65	1/4-20	1.97	0.71	1.26	1.4	1.14	0.24	0.55	0.47	1.000	18	0.04
941341	MRX.40 p-1/4-20x1.1/2	1.65	1/4-20	1.97	0.71	1.26	1.4	1.14	0.24	0.55	0.47	1.500	18	0.04
941341-C2-C1	MRX.40-C2-p-1/4-20x1.1/2-C1	1.65	1/4-20	1.97	0.71	1.26	1.4	1.14	0.24	0.55	0.47	1.500	18	0.04
941441	MRX.63 p-1/4-20x1/2	2.48	1/4-20	2.87	0.91	1.69	1.83	1.46	0.31	0.67	0.59	0.500	20	0.06
941441-C2-C1	MRX.63-C2-p-1/4-20x1/2-C1	2.48	1/4-20	2.87	0.91	1.69	1.83	1.46	0.31	0.67	0.59	0.500	20	0.06
941451	MRX.63 p-1/4-20x3/4	2.48	1/4-20	2.87	0.91	1.69	1.83	1.46	0.31	0.67	0.59	0.750	20	0.06
941451-C2-C1	MRX.63-C2-p-1/4-20x3/4-C1	2.48	1/4-20	2.87	0.91	1.69	1.83	1.46	0.31	0.67	0.59	0.750	20	0.06
941461	MRX.63 p-1/4-20x1	2.48	1/4-20	2.87	0.91	1.69	1.83	1.46	0.31	0.67	0.59	1.000	20	0.07
941461-C2-C1	MRX.63-C2-p-1/4-20x1-C1	2.48	1/4-20	2.87	0.91	1.69	1.83	1.46	0.31	0.67	0.59	1.000	20	0.07
941471	MRX.63 p-1/4-20x1.1/2	2.48	1/4-20	2.87	0.91	1.69	1.83	1.46	0.31	0.67	0.59	1.500	20	0.07
941471-C2-C1	MRX.63-C2-p-1/4-20x1.1/2-C1	2.48	1/4-20	2.87	0.91	1.69	1.83	1.46	0.31	0.67	0.59	1.500	20	0.07
941501	MRX.63 p-5/16-18x1/2	2.48	5/16-18	2.87	0.91	1.69	1.83	1.46	0.31	0.67	0.59	0.500	20	0.06
941501-C2-C1	MRX.63-C2-p-5/16-18x1/2-C1	2.48	5/16-18	2.87	0.91	1.69	1.83	1.46	0.31	0.67	0.59	0.500	20	0.06
941511	MRX.63 p-5/16-18x3/4	2.48	5/16-18	2.87	0.91	1.69	1.83	1.46	0.31	0.67	0.59	0.750	20	0.07
941511-C2-C1	MRX.63-C2-p-5/16-18x3/4 -C1	2.48	5/16-18	2.87	0.91	1.69	1.83	1.46	0.31	0.67	0.59	0.750	20	0.07
941521	MRX.63 p-5/16-18x1	2.48	5/16-18	2.87	0.91	1.69	1.83	1.46	0.31	0.67	0.59	1.000	20	0.07
941521-C2-C1	MRX.63-C2-p-5/16-18x1-C1	2.48	5/16-18	2.87	0.91	1.69	1.83	1.46	0.31	0.67	0.59	1.000	20	0.07
941531	MRX.63 p-5/16-18x1.1/4	2.48	5/16-18	2.87	0.91	1.69	1.83	1.46	0.31	0.67	0.59	1.250	20	0.08
941531-C2-C1	MRX.63-C2-p-5/16-18x1.1/4-C1	2.48	5/16-18	2.87	0.91	1.69	1.83	1.46	0.31	0.67	0.59	1.250	20	0.08
941541	MRX.63 p-5/16-18x1.1/2	2.48	5/16-18	2.87	0.91	1.69	1.83	1.46	0.31	0.67	0.59	1.500	20	0.09
941541-C2-C1	MRX.63-C2-p-5/16-18x1.1/2-C1	2.48	5/16-18	2.87	0.91	1.69	1.83	1.46	0.31	0.67	0.59	1.500	20	0.09
941561	MRX.63 p-5/16-18x2	2.48	5/16-18	2.87	0.91	1.69	1.83	1.46	0.31	0.67	0.59	2.000	20	0.09
941561-C2-C1	MRX.63-C2-p-5/16-18x2-C1	2.48	5/16-18	2.87	0.91	1.69	1.83	1.46	0.31	0.67	0.59	2.000	20	0.09

MRX-p

INCH

Code	Description	R	d2A	L	D	H	H1	h1	h2	h3	d1	l	Teeth nr	
942201	MRX.80 p-3/8-16x3/4	3.15	3/8-16	3.62	1.1	2.13	2.3	1.85	0.39	0.87	0.75	0.750	24	0.13
942201-C2-C1	MRX.80-C2-p-3/8-16x3/4-C1	3.15	3/8-16	3.62	1.1	2.13	2.3	1.85	0.39	0.87	0.75	0.750	24	0.13
942211	MRX.80 p-3/8-16x1	3.15	3/8-16	3.62	1.1	2.13	2.3	1.85	0.39	0.87	0.75	1.000	24	0.14
942211-C2-C1	MRX.80-C2-p-3/8-16x1-C1	3.15	3/8-16	3.62	1.1	2.13	2.3	1.85	0.39	0.87	0.75	1.000	24	0.14
942221	MRX.80 p-3/8-16x1¼	3.15	3/8-16	3.62	1.1	2.13	2.3	1.85	0.39	0.87	0.75	1.250	24	0.15
942221-C2-C1	MRX.80-C2-p-3/8-16x1¼-C1	3.15	3/8-16	3.62	1.1	2.13	2.3	1.85	0.39	0.87	0.75	1.250	24	0.15
942231	MRX.80 p-3/8-16x1.1/2	3.15	3/8-16	3.62	1.1	2.13	2.3	1.85	0.39	0.87	0.75	1.500	24	0.15
942231-C2-C1	MRX.80-C2-p-3/8-16x1½-C1	3.15	3/8-16	3.62	1.1	2.13	2.3	1.85	0.39	0.87	0.75	1.500	24	0.15
942241	MRX.80 p-3/8-16x2	3.15	3/8-16	3.62	1.1	2.13	2.3	1.85	0.39	0.87	0.75	2.000	24	0.17
942241-C2-C1	MRX.80-C2-p-3/8-16x2-C1	3.15	3/8-16	3.62	1.1	2.13	2.3	1.85	0.39	0.87	0.75	2.000	24	0.17
942321	MRX.80 p-1/2-13x1¼	3.15	1/2-13	3.62	1.1	2.13	2.3	1.85	0.39	0.87	0.75	1.250	24	0.18
942321-C2-C1	MRX.80-C2-p-1/2-13x1¼-C1	3.15	1/2-13	3.62	1.1	2.13	2.3	1.85	0.39	0.87	0.75	1.250	24	0.18
942331	MRX.80 p-1/2-13x1½	3.15	1/2-13	3.62	1.1	2.13	2.3	1.85	0.39	0.87	0.75	1.500	24	0.18
942331-C2-C1	MRX.80-C2-p-1/2-13x1½-C1	3.15	1/2-13	3.62	1.1	2.13	2.3	1.85	0.39	0.87	0.75	1.500	24	0.18
942341	MRX.80 p-1/2-13x2	3.15	1/2-13	3.62	1.1	2.13	2.3	1.85	0.39	0.87	0.75	2.000	24	0.21
942341-C2-C1	MRX.80-C2-p-1/2-13x2-C1	3.15	1/2-13	3.62	1.1	2.13	2.3	1.85	0.39	0.87	0.75	2.000	24	0.21
942601	MRX.100 p-1/2-13x1¼	3.94	1/2-13	4.49	1.3	2.56	2.74	2.13	0.47	0.98	0.98	1.250	28	0.24
942601-C2-C1	MRX.100-C2-p-1/2-13x1¼-C1	3.94	1/2-13	4.49	1.3	2.56	2.74	2.13	0.47	0.98	0.98	1.250	28	0.24
942631	MRX.100 p-1/2-13x1.1/2	3.94	1/2-13	4.49	1.3	2.56	2.74	2.13	0.47	0.98	0.98	1.500	28	0.26
942631-C2-C1	MRX.100-C2-p-1/2-13x1½-C1	3.94	1/2-13	4.49	1.3	2.56	2.74	2.13	0.47	0.98	0.98	1.500	28	0.26
942651	MRX.100 p-1/2-13x2	3.94	1/2-13	4.49	1.3	2.56	2.74	2.13	0.47	0.98	0.98	2.000	28	0.29
942651-C2-C1	MRX.100-C2-p-1/2-13x2-C1	3.94	1/2-13	4.49	1.3	2.56	2.74	2.13	0.47	0.98	0.98	2.000	28	0.29

MRX-SST-p

INOX STAINLESS STEEL

INCH

Code	Description	R	d2A	L	D	H	H1	h1	h2	h3	d1	l	Teeth nr	
941361	MRX.40-SST-p-1/4-20x1/2	1.65	1/4-20	1.97	0.71	1.26	1.4	1.14	0.24	0.55	0.47	0.500	18	0.03
941361-C2-C1	MRX.40-C2-SST-p-1/4-20x 1/2-C1	1.65	1/4-20	1.97	0.71	1.26	1.4	1.14	0.24	0.55	0.47	0.500	18	0.03
941365	MRX.40-SST-p-1/4-20x3/4	1.65	1/4-20	1.97	0.71	1.26	1.4	1.14	0.24	0.55	0.47	0.750	18	0.04
941365-C2-C1	MRX.40-C2-SST-p-1/4-20x 3/4-C1	1.65	1/4-20	1.97	0.71	1.26	1.4	1.14	0.24	0.55	0.47	0.750	18	0.04
941371	MRX.40-SST-p-1/4-20x1	1.65	1/4-20	1.97	0.71	1.26	1.4	1.14	0.24	0.55	0.47	1.000	18	0.04
941371-C2-C1	MRX.40-C2-SST-p-1/4-20x 1-C1	1.65	1/4-20	1.97	0.71	1.26	1.4	1.14	0.24	0.55	0.47	1.000	18	0.04
941611	MRX.63-SST-p-5/16-18x3/4	2.48	5/16-18	2.87	0.91	1.69	1.83	1.46	0.31	0.67	0.59	0.750	20	0.07
941611-C2-C1	MRX.63-C2-SST-p-5/16-18x3/4-C1	2.48	5/16-18	2.87	0.91	1.69	1.83	1.46	0.31	0.67	0.59	0.750	20	0.07
941615	MRX.63-SST-p-5/16-18x1	2.48	5/16-18	2.87	0.91	1.69	1.83	1.46	0.31	0.67	0.59	1.000	20	0.07
941615-C2-C1	MRX.63-C2-SST-p-5/16-18x1-C1	2.48	5/16-18	2.87	0.91	1.69	1.83	1.46	0.31	0.67	0.59	1.000	20	0.07
941621	MRX.63-SST-p-5/16-18x1¼	2.48	5/16-18	2.87	0.91	1.69	1.83	1.46	0.31	0.67	0.59	1.250	20	0.08
941621-C2-C1	MRX.63-C2-SST-p-5/16-18x1¼-C1	2.48	5/16-18	2.87	0.91	1.69	1.83	1.46	0.31	0.67	0.59	1.250	20	0.08
941631	MRX.63-SST-P-5/16-18X1½	2.48	5/16-18	2.87	0.91	1.69	1.83	1.46	0.31	0.67	0.59	1.500	20	0.08
941631-C2-C1	MRX.63-C2-SST-p-5/16-18x1½-C1	2.48	5/16-18	2.87	0.91	1.69	1.83	1.46	0.31	0.67	0.59	1.500	20	0.08
941635	MRX.63-SST-p-5/16-18X2	2.48	5/16-18	2.87	0.91	1.69	1.83	1.46	0.31	0.67	0.59	2.000	20	0.09
941635-C2-C1	MRX.63-C2-SST-p-5/16-18x2-C1	2.48	5/16-18	2.87	0.91	1.69	1.83	1.46	0.31	0.67	0.59	2.000	20	0.09
942381	MRX.80-SST-p-3/8-16x1	3.15	3/8-16	3.62	1.1	2.13	2.3	1.85	0.39	0.87	0.75	1.000	24	0.14
942381-C2-C1	MRX.80-C2-SST-p-3/8-16x1-C1	3.15	3/8-16	3.62	1.1	2.13	2.3	1.85	0.39	0.87	0.75	1.000	24	0.14
942385	MRX.80-SST-p-3/8-16x1.1/4	3.15	3/8-16	3.62	1.1	2.13	2.3	1.85	0.39	0.87	0.75	1.250	24	0.15
942385-C2-C1	MRX.80-C2-SST-p-3/8-16x1.1/4-C1	3.15	3/8-16	3.62	1.1	2.13	2.3	1.85	0.39	0.87	0.75	1.250	24	0.15
942391	MRX.80-SST-p-3/8-16X1.1/2	3.15	3/8-16	3.62	1.1	2.13	2.3	1.85	0.39	0.87	0.75	1.500	24	0.15
942391-C2-C1	MRX.80-C2-SST-p-3/8-16x 1½-C1	3.15	3/8-16	3.62	1.1	2.13	2.3	1.85	0.39	0.87	0.75	1.500	24	0.15
942401	MRX.80-SST-p-3/8-16x2	3.15	3/8-16	3.62	1.1	2.13	2.3	1.85	0.39	0.87	0.75	2.000	24	0.17
942401-C2-C1	MRX.80-C2-SST-p-3/8-16x2-C1	3.15	3/8-16	3.62	1.1	2.13	2.3	1.85	0.39	0.87	0.75	2.000	24	0.17