

MATERIAL

AISI 304 stainless steel.

RIVETS

AISI 304 stainless steel.

PULLING HOOK

Perpendicular to clamping arm, AISI 304 stainless steel.

OSCILLATING PIN AND NUTS

AISI 303 stainless steel.

HANDLE

Polyurethane, red colour.

ANTI RELEASE LEVER

AISI 303 stainless steel

LEVER ANTI-RELEASE COVERING

Polyvinylchloride (PVC).

SPRING





AISI 302 stainless steel.

FEATURES AND APPLICATIONS

Anti-release lever to prevent accidental opening in the presence of strong vibrations. All articulated joints are lubricated with special grease. MTD-S-SST clamps ensure tight closing of any cover. The position of the pulling hook can be adjusted in length according to the specific applications.

ACCESSORIES ON REQUEST

TRU: U-shaped pulling hooks of various dimensions (see page).



Code	Description	a	b1	b2	b3	b4	d1	d2	h1	h2	l1	m1	m2	m3	r	s	w Stroke	FH* [N]	Δ
GG.AS654	MTD-S.160-T3LX	5	26	35	25.5	14	M4	4.3	37	10	68	22	13	14.3	49.5+58	2	22+29	1600	112
GG.AS658	MTD-S.320-T3LX	8	36	44	37	22	M6	6.5	53	15	106	25.5	19	20.5	75+95	3	39+49	3200	346
GG.AS662	MTD-S.700-T3LX	13	52	54	48.5	26	M8	8.5	66	23	147	36.5	32	27	98+122	3.5	50+62	7500	762

* Holding force.