

STANDARD EXECUTIONS

- **MM-BC-NK**: nickel-plated steel.
- **MM-BC-PTFE**: steel with teflon (PTFE) coating.

MAXIMUM WORKING PRESSURE

10 bar.

FEATURES

MM-BC pneumatic fastening clamps are characterised by a "double effect" pneumatic cylinder which transmits a rotating movement to the clamping arms.

The maximum locking momentum is achieved when the clamping arm arrives at the stroke end and through pneumatic actuation only.

Under specific tests the pneumatic fastening clamps showed constant performances for more than 20 million cycles.

The teflon (PTFE) coating provides high resistance to weld spatter and corrosion.

See Pneumatic fastening clamp features (on page -).

SPECIAL EXECUTIONS ON REQUEST


- Fastening clamps with FKM sealing gasket resistant to max working temperatures up to 270°C.
- Fastening clamps with arm rotating movement and locking in the 20° position.
- Fastening clamps with arm rotating movement and locking in the 45° position.

ACCESSORIES ON REQUEST

Brackets, fixing elements and nickel-plated steel sensors (see table of possible configurations)..



Possible configurations of pneumatic fastening clamp MM-BC					
2 x MM-A-RG-NK		2 x MM-A-RG1-NK			
1x MM-SI		1x MM-SI			
4 x MM-RG		2 x MM-RG			
2 x MM-A-SC-NK		2 x MM-A-SCL-NK			
1 x MM-SI		1 x MM-SI			
2 x MM-SC		2 x MM-SC			
2 x MM-GBK		2 x MM-GBK			



MM-BC-NK

Code	Description	a	b	d1	d2	d3	d4	d5	l1	l2	l3	l4	l5	l6	s	s1	m1	m2	m3	m4	m5	r	t	FH	FS	M#	Δ
		-0.2	h8	H8	H8	H8	H8	H8	-0.5	-0.5							±0.01		±0.01	±0.01			[N]	[N]	[Nm]		
MM.05020-NK	MM-BC-20-NK	21	10	28	M5	7	4.2	M5	138	160	57.5	24.5	5	89	32	38	12	7.5	17	22	13	48	13	1150	630	60	635
MM.05032-NK	MM-BC-32-NK	31	12	40	M6	9	5	G 1/8	206	237	91	31	6	72.5	42	-	18	10	25	30	22	67.5	15	1520	1110	150	1569
MM.05040-NK	MM-BC-40-NK	37	16	50	M8	11	6.8	G 1/8	244	282	104	38	7.5	89.5	52	-	22	13	30	37	25	82.5	18	2000	1800	300	2900

MM-BC-PTFE

Code	Description	a	b	d1	d2	d3	d4	d5	l1	l2	l3	l4	l5	l6	s	s1	m1	m2	m3	m4	m5	r	t	FH	FS	M#	Δ	
		-0.2	h8	H8	H8	H8	H8	H8	-0.5	-0.5							±0.01		±0.01	±0.01			[N]	[N]	[Nm]			
MM.05020-PTFE	MM-BC-20-PTFE	21	10	28	M5	7	4.2	M5	138	160	57.5	24.5	5	5	89	32	38	12	7.5	17	22	13	48	13	1150	630	60	635
MM.05032-PTFE	MM-BC-32-PTFE	31	12	40	M6	9	5	G 1/8	206	237	91	31	6	72.5	42	-	18	10	25	30	22	67.5	15	1520	1110	150	1569	
MM.05040-PTFE	MM-BC-40-PTFE	37	16	50	M8	11	6.8	G 1/8	244	282	104	38	7.5	89.5	52	-	22	13	30	37	25	82.5	18	2000	1800	300	2900	

Maximum tightening moment at 6 bar.