

- 1
- 2
- 3
- 4
- 5
- 6
- 7
- 8
- 9
- 10
- 11
- 12
- 13
- 14
- 15
- 16
- 17
- 18
- 19

MATERIAL

Polyamide based (PA) technopolymer.

- Cap: semi-matte finish, black colour, with "fill" symbol.
- Threaded connector and external anti-splash semi-discs, black colour.

PACKING RINGS

NBR synthetic rubber.

FLAT DIPSTICK

Flat section phosphatised steel.

On request and for sufficient quantities dipstick can be supplied in different lengths and/or complete with MAX-MIN level lines.

STANDARD EXECUTIONS

- **SFX+a**: without air filter.
- **SFX+F+a**: with "tech-foam" air filter in polyurethane foam mesh (polyester base), air filtration 40 µ.
- **SFX+P+a**: with anti-splash semi-discs, without air filter.
- **SFX+P+F+a**: with anti-splash semi-discs and "tech-foam" air filter in polyurethane foam mesh (polyester base), air filtration 40 µ.

MAXIMUM CONTINUOUS WORKING TEMPERATURE

100°C.

FEATURES AND APPLICATIONS

The SFX+a breather caps are made with a special internal geometry (Elesa patent) that prevents the leakage of fluids through a linear labyrinth (splash guard effect) and promotes condensation of the outgoing vapours.

The external snap-on anti-splash semi-discs (execution+P) located at the mouth of the threaded fitting hole, are made up of fins offset from each other so as to constitute an additional labyrinth in the most critical cases of strong fluid projections.

TECHNICAL DATA



Air flow rate for each model can be determined from the graph here below by calculating the difference between the pressure inside and outside the reservoir.

SPECIAL EXECUTIONS ON REQUEST




- Neutral cap without symbols.
- Cap in RAL 3000 red colour.



ELESA Original design



Conversion Table 1 mm = 0.039 inch	
D	
mm	inch
31	1.22
42	1.65
57	2.24



METRIC

SFX+a

Code	Description	D	d	a#	L	d2	h	⚖️
53362	SFX.30-1/4+a	31	G 1/4	188	29.5	8	9.5	26
53402	SFX.30-3/8+a	31	G 3/8	188	29.5	10	9.5	26
53442	SFX.30-1/2+a	31	G 1/2	188	29.5	12	9.5	26
53482	SFX.40-3/8+a	31	G 3/8	184	29.5	10	11.5	35
53522	SFX.40-1/2+a	42	G 1/2	184	36.5	12	11.5	35
53562	SFX.40-3/4+a	42	G 3/4	184	36.5	17	11.5	35
53602	SFX.40-1+a	57	G 1	184	42	23	11.5	35
53642	SFX.57-3/4+a	57	G 3/4	184	42	18	14	49
53682	SFX.57-1+a	57	G 1	184	42	23	14	49
53722	SFX.57-1¼+a	57	G 1 1/4	184	44	32	16	49
53762	SFX.57-1½+a	57	G 1 1/2	184	44	38	16	49
53006	SFX.30-M16x1.5+a	31	M16x1.5	188	29.5	10	9.5	26
53026	SFX.30-M18x1.5+a	31	M18x1.5	188	29.5	10	9.5	26
53046	SFX.30-M20x1.5+a	31	M20x1.5	188	29.5	12	9.5	26
53066	SFX.30-M22x1.5+a	31	M22x1.5	188	29.5	12	9.5	26
53086	SFX.40-M24x1.5+a	42	M24x1.5	184	36.5	18	11.5	35
53106	SFX.40-M26x1.5+a	42	M26x1.5	184	36.5	18	11.5	35
53126	SFX.57-M30x1.5+a	57	M30x1.5	184	42	23	14	49

SFX+F+a

Code	Description	D	d	a#	L	d2	h	⚖️
53366	SFX.30-1/4+F+a	31	G 1/4	188	29.5	8	9.5	26
53406	SFX.30-3/8+F+a	31	G 3/8	188	29.5	10	9.5	26
53446	SFX.30-1/2+F+a	31	G 1/2	188	29.5	12	9.5	39
53486	SFX.40-3/8+F+a	31	G 3/8	184	29.5	10	11.5	35
53526	SFX.40-1/2+F+a	42	G 1/2	184	36.5	12	11.5	35
53566	SFX.40-3/4+F+a	42	G 3/4	184	36.5	17	11.5	35
53606	SFX.40-1+F+a	57	G 1	184	42	23	11.5	35
53646	SFX.57-3/4+F+a	57	G 3/4	184	42	18	14	49
53686	SFX.57-1+F+a	57	G 1	184	42	23	14	49
53726	SFX.57-1¼+F+a	57	G 1 1/4	184	44	32	16	49
53766	SFX.57-1½+F+a	57	G 1 1/2	184	44	38	16	49
53036	SFX.30-M18x1.5+F+a	31	M18x1.5	188	29.5	10	9.5	26
53056	SFX.30-M20x1.5+F+a	31	M20x1.5	188	29.5	12	9.5	38
53076	SFX.30-M22x1.5+F+a	31	M22x1.5	188	29.5	12	9.5	26
53096	SFX.40-M24x1.5+F+a	42	M24x1.5	184	36.5	18	11.5	35
53116	SFX.40-M26x1.5+F+a	42	M26x1.5	184	36.5	18	11.5	35
53136	SFX.57-M30x1.5+F+a	57	M30x1.5	184	42	23	14	49

You can choose lengths other than the standard option and/or add MAX-MIN level markings. To request customization, select an item and follow the wizard on the web.





Accessories for hydraulic systems

- 1
- 2
- 3
- 4
- 5
- 6
- 7
- 8
- 9
- 10
- 11
- 12
- 13
- 14
- 15
- 16
- 17
- 18
- 19

Conversion Table
1 mm = 0.039 inch

D	
mm	inch
31	1.22
42	1.65
57	2.24



METRIC

SFX+P+a

Code	Description	D	d	a#	L	d2	d3	l1	h	⚖
53462	SFX.30-1/2+P+a	31	G 1/2	188	29.5	12	18	26	9.5	26
53542	SFX.40-1/2+P+a	42	G 1/2	184	36.5	12	18	28.5	11.5	35
53582	SFX.40-3/4+P+a	42	G 3/4	184	36.5	17	23	28.5	11.5	35
53622	SFX.40-1+P+a	57	G 1	184	42	23	30	28.5	11.5	35
53662	SFX.57-3/4+P+a	57	G 3/4	184	42	18	23	31	14	49
53702	SFX.57-1+P+a	57	G 1	184	42	23	30	31	14	49
53742	SFX.57-1¼+P+a	57	G 1 1/4	184	44	32	30	33	16	49
53782	SFX.57-1½+P+a	57	G 1 1/2	184	44	38	30	33	16	49
53246	SFX.30-M20x1.5+P+a	31	M20x1.5	188	29.5	12	18	26	9.5	26
53266	SFX.30-M22x1.5+P+a	31	M22x1.5	188	29.5	12	18	26	9.5	26
53286	SFX.40-M24x1.5+P+a	42	M24x1.5	184	36.5	18	18	28.5	11.5	35
53306	SFX.40-M26x1.5+P+a	42	M26x1.5	184	36.5	18	23	28.5	11.5	35
53326	SFX.57-M30x1.5+P+a	57	M30x1.5	184	42	23	23	31	14	49

SFX+P+F+a

Code	Description	D	d	a#	L	d2	d3	l1	h	⚖
53466	SFX.30-1/2+P+F+a	31	G 1/2	188	29.5	12	18	26	9.5	26
53546	SFX.40-1/2+P+F+a	42	G 1/2	184	36.5	12	18	28.5	11.5	35
53586	SFX.40-3/4+P+F+a	42	G 3/4	184	36.5	17	23	28.5	11.5	35
53626	SFX.40-1+P+F+a	57	G 1	184	42	23	30	28.5	11.5	35
53666	SFX.57-3/4+P+F+a	57	G 3/4	184	42	18	23	31	14	49
53706	SFX.57-1+P+F+a	57	G 1	184	42	23	30	31	14	49
53746	SFX.57-1¼+P+F+a	57	G 1 1/4	184	44	32	30	33	16	49
53786	SFX.57-1½+P+F+a	57	G 1 1/2	184	44	38	30	33	16	49
53256	SFX.30-M20x1.5+P+F+a	31	M20x1.5	188	29.5	12	18	26	9.5	26
53276	SFX.30-M22x1.5+P+F+a	31	M22x1.5	188	29.5	12	18	26	9.5	26
53296	SFX.40-M24x1.5+P+F+a	42	M24x1.5	184	36.5	18	18	28.5	11.5	35
53316	SFX.40-M26x1.5+P+F+a	42	M26x1.5	184	36.5	18	23	28.5	11.5	35
53336	SFX.57-M30x1.5+P+F+a	57	M30x1.5	184	42	23	23	31	14	49

Accessories for hydraulic systems

You can choose lengths other than the standard option and/or add MAX-MIN level markings. To request customization, select an item and follow the wizard on the web.