

MATERIAL



Polyamide based (PA) technopolymer, natural colour.

FEATURES AND APPLICATIONS

The spacer sleeve ensures a constant distance between two structural elements, at the same time creating both thermal and electrical insulation between the components.


It is made entirely from insulating material that is resistant to corrosion and chemicals. It is suitable for applications in the electronics industry and in all cases where weight reduction is required.

The product is tested for mechanical and dimensional performance. Slight colour variations are perfectly normal and do not affect the quality of the product.



METRIC

Code	Description	d	d1	h	⚖️
504048	SPC-4.3-8.0-5.0-TP-N	4.5	8	5	1
504049	SPC-4.3-8.0-10.0-TP-N	4.5	8	10	1
504043	SPC-4.3-8.0-15.0-TP-N	4.5	8	15	1
504044	SPC-4.3-8.0-20.0-TP-N	4.5	8	20	1
504045	SPC-4.3-8.0-25.0-TP-N	4.5	8	25	1
504046	SPC-4.3-8.0-30.0-TP-N	4.5	8	30	1.5
504058	SPC-5.3-10.0-5.0-TP-N	5.5	10	5	1
504059	SPC-5.3-10.0-10.0-TP-N	5.5	10	10	1
504053	SPC-5.3-10.0-15.0-TP-N	5.5	10	15	1
504054	SPC-5.3-10.0-20.0-TP-N	5.5	10	20	2
504055	SPC-5.3-10.0-25.0-TP-N	5.5	10	25	1.5
504056	SPC-5.3-10.0-30.0-TP-N	5.5	10	30	3
504068	SPC-5.3-12.0-5.0-TP-N	5.5	12	5	1
504069	SPC-5.3-12.0-10.0-TP-N	5.5	12	10	1
504063	SPC-5.3-12.0-15.0-TP-N	5.5	12	15	1
504064	SPC-5.3-12.0-20.0-TP-N	5.5	12	20	2
504065	SPC-5.3-12.0-25.0-TP-N	5.5	12	25	2.5
504066	SPC-5.3-12.0-30.0-TP-N	5.5	12	30	3
504071	SPC-6.4-10.0-5.0-TP-N	6.5	10	5	1
504072	SPC-6.4-10.0-10.0-TP-N	6.5	10	10	1
504073	SPC-6.4-10.0-15.0-TP-N	6.5	10	15	1
504074	SPC-6.4-10.0-20.0-TP-N	6.5	10	20	1
504075	SPC-6.4-10.0-25.0-TP-N	6.5	10	25	1
504076	SPC-6.4-10.0-30.0-TP-N	6.5	10	30	1.5
504081	SPC-6.4-15.0-5.0-TP-N	6.5	15	5	1
504082	SPC-6.4-15.0-10.0-TP-N	6.5	15	10	1.5
504083	SPC-6.4-15.0-15.0-TP-N	6.5	15	15	2
504084	SPC-6.4-15.0-20.0-TP-N	6.5	15	20	3
504085	SPC-6.4-15.0-25.0-TP-N	6.5	15	25	4
504086	SPC-6.4-15.0-30.0-TP-N	6.5	15	30	4.5
504091	SPC-6.4-20.0-5.0-TP-N	6.5	20	5	1.5
504092	SPC-6.4-20.0-10.0-TP-N	6.5	20	10	3
504093	SPC-6.4-20.0-15.0-TP-N	6.5	20	15	4.5
504094	SPC-6.4-20.0-20.0-TP-N	6.5	20	20	6
504095	SPC-6.4-20.0-25.0-TP-N	6.5	20	25	7
504096	SPC-6.4-20.0-30.0-TP-N	6.5	20	30	9



METRIC

Code	Description	d	d1	h	⚖️
504101	SPC-8.4-15.0-5.0-TP-N	8.5	15	5	1
504102	SPC-8.4-15.0-10.0-TP-N	8.5	15	10	1.5
504103	SPC-8.4-15.0-15.0-TP-N	8.5	15	15	2
504104	SPC-8.4-15.0-20.0-TP-N	8.5	15	20	2.5
504105	SPC-8.4-15.0-25.0-TP-N	8.5	15	25	3.5
504106	SPC-8.4-15.0-30.0-TP-N	8.5	15	30	4
504118	SPC-8.4-20.0-5.0-TP-N	8.5	20	5	1.5
504119	SPC-8.4-20.0-10.0-TP-N	8.5	20	10	2.5
504113	SPC-8.4-20.0-15.0-TP-N	8.5	20	15	4
504114	SPC-8.4-20.0-20.0-TP-N	8.5	20	20	6
504115	SPC-8.4-20.0-25.0-TP-N	8.5	20	25	7
504116	SPC-8.4-20.0-30.0-TP-N	8.5	20	30	8.5
504128	SPC-8.4-25.0-5.0-TP-N	8.5	25	5	2.5
504129	SPC-8.4-25.0-10.0-TP-N	8.5	25	10	4.5
504123	SPC-8.4-25.0-15.0-TP-N	8.5	25	15	7
504124	SPC-8.4-25.0-20.0-TP-N	8.5	25	20	9.5
504125	SPC-8.4-25.0-25.0-TP-N	8.5	25	25	12
504126	SPC-8.4-25.0-30.0-TP-N	8.5	25	30	14.5
504138	SPC-10.5-15.0-5.0-TP-N	10.5	15	5	1
504139	SPC-10.5-15.0-10.0-TP-N	10.5	15	10	1
504133	SPC-10.5-15.0-15.0-TP-N	10.5	15	15	1.4
504134	SPC-10.5-15.0-20.0-TP-N	10.5	15	20	2
504135	SPC-10.5-15.0-25.0-TP-N	10.5	15	25	2.5
504136	SPC-10.5-15.0-30.0-TP-N	10.5	15	30	3
504148	SPC-10.5-21.0-5.0-TP-N	10.5	20	5	1
504149	SPC-10.5-21.0-10.0-TP-N	10.5	20	10	1.5
504143	SPC-10.5-21.0-15.0-TP-N	10.5	20	15	1.5
504144	SPC-10.5-21.0-20.0-TP-N	10.5	20	20	2
504145	SPC-10.5-21.0-25.0-TP-N	10.5	20	25	2.5
504146	SPC-10.5-21.0-30.0-TP-N	10.5	20	30	2.5
504158	SPC-10.5-30.0-5.0-TP-N	10.5	30	5	1.5
504159	SPC-10.5-30.0-10.0-TP-N	10.5	30	10	1.5
504153	SPC-10.5-30.0-15.0-TP-N	10.5	30	15	2
504154	SPC-10.5-30.0-20.0-TP-N	10.5	30	20	2.5
504155	SPC-10.5-30.0-25.0-TP-N	10.5	30	25	3
504156	SPC-10.5-30.0-30.0-TP-N	10.5	30	30	3.5
504160	SPC-12.2-18.0-5.0-TP-N	12	32	5	1
504162	SPC-12.2-18.0-10.0-TP-N	12	32	10	1.5
504163	SPC-12.2-18.0-15.0-TP-N	12	32	15	2.5
504164	SPC-12.2-18.0-20.0-TP-N	12	32	20	3
504165	SPC-12.2-18.0-25.0-TP-N	12	32	25	4
504166	SPC-12.2-18.0-30.0-TP-N	12	32	30	4.5
504171	SPC-16.2-32.0-5.0-TP-N	16	32	5	3.4
504172	SPC-16.2-32.0-10.0-TP-N	16	32	10	6.5
504173	SPC-16.2-32.0-15.0-TP-N	16	32	15	9
504174	SPC-16.2-32.0-20.0-TP-N	16	32	20	12.5
504175	SPC-16.2-32.0-25.0-TP-N	16	32	25	16
504176	SPC-16.2-32.0-30.0-TP-N	16	32	30	19

