

- 1
- 2
- 3
- 4
- 5
- 6
- 7
- 8
- 9
- 10
- 11
- 12
- 13
- 14
- 15
- 16
- 17
- 18

MATERIAL

Polyamide based (PA) technopolymer, black colour RAL 9005 (C9) or orange colour RAL 2004 (C2), matte finish.

PACKING RINGS

Two NBR synthetic rubber O-rings.

STANDARD EXECUTIONS

- **TP-C**: without side hole.
- **TP-CF**: with side breather hole.

MAXIMUM CONTINUOUS WORKING TEMPERATURE

100°C.

GRAPHIC SYMBOL "FILL"

According to DIN regulations.



MOUNTING

Push-fit avoids the need to screw/unscrew.



ELESA Original design

Conversion Table	
1 mm = 0.039 inch	
d+0.2	
mm	inch
12	0.47
18	0.71
20	0.79
26	1.02



C9 RAL9005
 C2 RAL2004

TP-C

Code	Description	d	h	D	L	h1	h2	Mounting hole d+0.2	⚖
59851-R-C9	TP-C.12-C9	12	11	20	26	4	8	12	7
59851-R-C2	TP-C.12-C2	12	11	20	26	4	8	12	7
59853-R-C9	TP-C.18-C9	18	13	26	28	4.5	10	18	12
59853-R-C2	TP-C.18-C2	18	13	26	28	4.5	10	18	12
59861-R-C9	TP-C.20-C9	20	14	30	29	5	11	20	15
59861-R-C2	TP-C.20-C2	20	14	30	29	5	11	20	15
59881-R-C9	TP-C.26-C9	26	14	35	29.5	5	11	26	20
59881-R-C2	TP-C.26-C2	26	14	35	29.5	5	11	26	20

METRIC

TP-CF

Code	Description	d	h	D	L	h1	h2	Mounting hole d+0.2	⚖
59891-R-C9	TP-CF.12-C9	12	11	20	26	4	8	12	7
59891-R-C2	TP-CF.12-C2	12	11	20	26	4	8	12	7
59893-R-C9	TP-CF.18-C9	18	13	26	28	4.5	10	18	12
59893-R-C2	TP-CF.18-C2	18	13	26	28	4.5	10	18	12
59901-R-C9	TP-CF.20-C9	20	14	30	29	5	11	20	15
59901-R-C2	TP-CF.20-C2	20	14	30	29	5	11	20	15
59921-R-C9	TP-CF.26-C9	26	14	35	29.5	5	11	26	20
59921-R-C2	TP-CF.26-C2	26	14	35	29.5	5	11	26	20

METRIC

Accessories for hydraulic systems