

MATERIAL

- Cover: steel sheet, with chrome plating superficial treatment.
- Flange: zinc-plated steel sheet.
- Threaded connector: zinc-plated steel.

RING SHAPE AIR FILTER

Tech-foam 10 µ or 40 µ.

FILTER SETTING SPRING

Zinc-plated steel.

STANDARD EXECUTIONS



- **SMN-F10 (inch)**: air filtration 10 µ.
- **SMN-F40 (inch)**: air filtration 40 µ.

MAXIMUM CONTINUOUS WORKING TEMPERATURE

212°F (100°C).

TECHNICAL DATA

Air flow rate for the different executions of breather caps can be obtained from the diagram on the basis of the difference of air pressure inside and outside the reservoir.



SMN-F10 (inch)

Code	Description	D	d	L	d2	h	h1	△△
956832	SMN.46-1/4 NPT-F10	1.85	1/4 NPT	2.16	0.28	0.39	0.2	0.13
956882	SMN.80-3/4 NPT-F10	3.19	3/4 NPT	2.91	0.67	0.63	0.47	0.53

SMN-F40 (inch)

Code	Description	D	d	L	d2	h	h1	△△
956833	SMN.46-1/4 NPT-F40	1.85	1/4 NPT	2.16	0.28	0.39	0.2	0.13
956883	SMN.80-3/4 NPT-F40	3.19	3/4 NPT	2.91	0.67	0.63	0.47	0.53

NPT