

## Elesa IP65 latches for specialist cabinet locking systems



From wall mounted cases to free standing cabinets, Elesa are now offering lever latches, swinghandles and recessed push handle latches to suit specialist housings for industrial, electrical and office use.

Their ELCK lever operated quarter turn latch is a combination lock with 400 possibilities from the ERGOSTYLE® design studio, available in L/R handed format and with master keyed locks if required.

For larger cabinets the CLT and CLC swinghandles offer black or black-and-chrome appearance with the ability to operate a rod control system for multi-point door security up to IP65. Key locks and two-wing groove inserts are available to suit appropriate applications.

An alternative approach to cabinet locking systems is shown in the Elesa IP65 CSMH compression latch with push handle which simply pops out of the flush fit escutcheon mechanism so that it may be used as a 90° T handle. Compression range of the CSMH is a 5mm stroke with adjustable depth between 13mm to 75mm. A padlockable version is available for 9mm dia. hasps.

Further information regarding Elesa products may be found at: [www.elesa.com](http://www.elesa.com) or follow them on twitter: [www.twitter.com/ElesaUK](https://twitter.com/ElesaUK).



## Press Box

**Elesa Contact:** Daniel Hodson  
**E-mail:** [marketing@elesa.co.uk](mailto:marketing@elesa.co.uk)

**ELESA (UK) Ltd.**  
26 Moorlands Estate – Metheringham, Lincolnshire LN4 3HX  
tel. 01526 32 26 70 – [sales@elesa.co.uk](mailto:sales@elesa.co.uk)

[www.elesa.com](http://www.elesa.com)  
**STANDARD MACHINE ELEMENTS WORLDWIDE**

**Ref:** ELES3185 – IP65 latches

**Editor's PR Contact:** Ian Deavin  
@The Industrial Marketing Agency

**E-mail:** [ian@theindustrialmarketingagency.co.uk](mailto:ian@theindustrialmarketingagency.co.uk)  
tel. 01462 850040  
Mobile. 07860 218334

1941 - 2016  
**75**  
Elesa Anniversary

**elesa**®