

Press Release

Soft Polyurethane Wheeled Castors from Elesa



Continuously moving loads will benefit from these [soft polyurethane wheeled castors](#) from Elesa as their 75 Shore A moulded-on wheels coupled to ball bearing hubs give exceptionally smooth rollability coupled with excellent maneuverability and zero maintenance.

The [RE.F2-N castors and wheels](#) are suitable for tiled or cement-resin floors. With a robust pressure die cast aluminium wheel body they provide a capacity of up to 2000N – well suited to light industrial carriages, continuously moving equipment, transfer stillages and instrument mounting trollies.

These soft wheeled castors use robust plated steel carriage brackets with fixed, swivel and swivel-with-brake options.

Further information regarding Elesa products may be found at: www.elesa.com or follow them on twitter: www.twitter.com/ElesaUK.



Press Box

Contact: Daniel Hodson
E-mail: marketing@elesa.co.uk

ELESA (UK) Ltd.
26 Moorlands Estate – Metherringham, Lincolnshire LN4 3HX
tel. 01526 32 26 70 – sales@elesa.co.uk

www.elesa.com
STANDARD MACHINE ELEMENTS WORLDWIDE

Ref: ELES3265 – wheeled castors

Editor's PR Contact: Ian Deavin
@The Industrial Marketing Agency

E-mail: ian@theindustrialmarketingagency.co.uk
tel. 01462 850040
Mobile. 07860 218334

