

Elesa twin wheel castor – low height high load capacity

The Elesa RE.C6-G twin polyurethane wheeled castors provide a low height installation with more than double the load carrying capacity of a single wheel, so enabling more equipment to be packed within the same ceiling space, e.g. more servers for a given external rack height.

Its high grade zinc plated chassis with injected polyurethane wheels make the RE.C6 suitable for institutional, corporate, industrial and even wash down environments where its total lock braking system and retractable pedal aid health and safety considerations, especially in public locations.

Further information regarding Elesa products may be found at: www.elesa.co.uk or follow them on twitter: [www.twitter.com/ElesaUK](https://twitter.com/ElesaUK) – also see www.youtube.com/elesauk.



Press Box

Contact:	Nigel Pritchett
Phone:	+44 (0)1526 322669
E-mail:	marketing@elesa.co.uk

Elesa (UK) Ltd
26 Moorlands Estate, Metherringham,
Lincolnshire, LN4 3HX, U.K.
www.elesa.co.uk – e-mail: sales@elesa.co.uk

