

# Press Release

## New Elesa pneumatic fastening clamps speed manufacturing processes



As international component manufacturers of high quality items from handwheels to positioning indicators, Elesa know what helps to ensure best practice in production. They are therefore pleased to launch this powerful [new MM range of pneumatic clamps](#) (up to 475Nm) which offer fast repetitive clamping cycles on manual or automated production lines to aid achievement of lower costs and more efficient output.

The MM range is available in [side locking](#), [axial locking](#) and [axial centre locking \(twin jaw\)](#) designs to suit the many variations required for handling of jigs and components in all orientations. They are produced in robust black oxide finished steel housings readily fitted to production machines of all types using an extensive selection of accessories. These provide many clamping adaptations quickly and easily with stock components to aid correct set up and to minimise down time.

Accessories include "I" brackets which enable mounting of jaw blocks and "Y" brackets to accept clamping screws, so that correct installation may be executed in a simple fashion; also right angled brackets, jaw blocks, shim kits, centre bushings, mounting brackets and rear protective shields. Correct positioning at speed may be controlled with Elesa MM proximity switches connected to the clamping controller.

MM series pneumatic fastening clamps are characterised by a "double effect" pneumatic



## Press Box

**Elesa Contact:** Daniel Hodson  
**E-mail:** [marketing@elesa.co.uk](mailto:marketing@elesa.co.uk)

**ELESA (UK) Ltd.**  
26 Moorlands Estate – Metheringham, Lincolnshire LN4 3HX  
tel. 01526 32 26 70 – [sales@elesa.co.uk](mailto:sales@elesa.co.uk)

[www.elesa.com](http://www.elesa.com)

**STANDARD MACHINE ELEMENTS WORLDWIDE**

**Ref: ELES3527 – pneumatic clamps**

**Editor's PR Contact:** Ian Deavin  
@The Industrial Marketing Agency

**E-mail:** [ian@theindustrialmarketingagency.co.uk](mailto:ian@theindustrialmarketingagency.co.uk)  
tel. 01462 850040  
Mobile. 07860 218334

**Follow Elesa UK on social media:**  
[www.twitter.com/ElesaUK](https://www.twitter.com/ElesaUK)  
[www.facebook.com/ElesaUK/](https://www.facebook.com/ElesaUK/)  
[www.linkedin.com/company/elesa-uk](https://www.linkedin.com/company/elesa-uk)



cylinder which transmits a rotating movement to the clamping arm and achieves a maximum locking momentum when the clamping arm arrives at the stroke end. Under test these pneumatic fastening clamps have shown consistent performance for more than 20 million cycles.

Further options include Teflon coating for high temperature and corrosion applications, FKM sealing gasket resistant to max working temperatures up to 270°C, plus fastening clamps with arm rotating movement and locking in the 20° position or in the 45° position.

Further information regarding Elesa products may be found at: [www.elesa.com](http://www.elesa.com).



## Press Box

**Elesa Contact:** Daniel Hodson  
**E-mail:** [marketing@elesa.co.uk](mailto:marketing@elesa.co.uk)

**ELESA (UK) Ltd.**  
26 Moorlands Estate – Metheringham, Lincolnshire LN4 3HX  
tel. 01526 32 26 70 – [sales@elesa.co.uk](mailto:sales@elesa.co.uk)

[www.elesa.com](http://www.elesa.com)

**STANDARD MACHINE ELEMENTS WORLDWIDE**

**Ref: ELES3527 – pneumatic clamps**

**Editor's PR Contact:** Ian Deavin  
@The Industrial Marketing Agency

**E-mail:** [ian@theindustrialmarketingagency.co.uk](mailto:ian@theindustrialmarketingagency.co.uk)  
tel. 01462 850040  
Mobile. 07860 218334

**Follow Elesa UK on social media:**

[www.twitter.com/ElesaUK](http://www.twitter.com/ElesaUK)  
[www.facebook.com/ElesaUK/](http://www.facebook.com/ElesaUK/)  
[www.linkedin.com/company/elesa-uk](http://www.linkedin.com/company/elesa-uk)

**elesa**®