

Press Release

14/12/2017

New vibration-damping elements for food and medical sectors



Elesa new vibration-damping elements DVF.6 and DVF.7 with conical shape are in **silicon rubber (MVQ) RAL 7040 grey colour**, hardness 55 Shore A ± 5 with **AISI 304 stainless steel base and inserts**.

The use of AISI 304 stainless steel inserts combined with **FDA** (U.S. Food and Drugs Administrations) **compliant** silicon rubber, makes them particularly suitable for applications in the **food processing industry** and **medical environments** to prevent unfavourable vibrations which can cause noise, machines malfunctioning and danger to operators' health.

These new products complete the well-known series made of Natural Rubber NR, black colour, available in different hardness, various dimensions and with cylindrical, conical, parabolic, hourglass or bell shape.

DVF. dampers are characterised by **high resistance to corrosion, chemicals, ageing, high or low temperatures**. In fact, DVF. elements resist to temperatures between 200 °C and -50 °C.

Furthermore, special executions with hardness 40, 70 Shore A ± 5 are available.

This new solution comes from Elesa's commitment to keep on extending its product range with innovative products to meet specific market needs and applications.

Product technical data sheets, along with drawings and tables with codes and dimensions, are available on our website elesa.com.



DVF.6



DVF.7



Elesa vibration-damping elements range

Press Box

Contact: Daniel Hodson
E-mail: marketing@elesa.co.uk

Elesa (UK) Ltd
26 Moorlands Estate, Metheringham Lincolnshire
LN4 3HX
Tel 01526 322670 – sales@elesa.co.uk

elesa.com
STANDARD MACHINE ELEMENTS WORLDWIDE

