

MATERIAL

Aluminium, epoxy resin coating, black colour, glossy finish.

STANDARD EXECUTIONS

H7 reamed blind hole, fitting to shaft by means of a supplied grub screw with hexagon socket and cup end UNI 5929-85.

- **VAK-GXX**: for gravity indicators.


- **VAK-PXX**: for positive drive indicators.

Rear flange with internal crown gear wheel in acetal resin based (POM) technopolymer. Black-oxide steel screw and anchor pin.

INDICATOR CHOICE (TO BE ORDERED SEPARATELY)

To choose the indicator see the table below for possible assembly with indicators.

See also "Assembly instructions" for gravity indicators type G (on page 460) or positive drive indicators type P (on page 462).



VAK-GXX

Code	Description	D	L	dH7	h	d1	d3	f	h1	l1	Δ	Indicator combinations
CE.28001	VAK.60-GXX1-1/4	58.5	51	1/4"	23	22	56.5	M5	7.9	19	100	GA01 - GA11
CE.28051	VAK.85-GXX2-5/16	85.5	55	5/16"	25	35	78	M6	6.3	21	250	GA02 - GA12 - GW12

VAK-PXX

Code	Description	D	L	dH7	h	d1	d3	d5	f	f1	h1	l1	l2	l4	R	Δ	Indicator combinations
CE.28002	VAK.60-PXX1-1/4	58.5	51	1/4"	23	20	56.5	6	M5	M4	6	19	11	14	19	130	PA01 - PA11
CE.28052	VAK.85-PXX2-5/16	85.5	55	5/16"	25	30	78	6	M6	M4	6.3	21	13	12	28.5	290	PA02 - PA12 - PW12