

Components for
medical equipment,
precision instruments,
rehab and disability aids

STANDARD MACHINE ELEMENTS WORLDWIDE

elesa®

ELESA presents an extensive range of components in **engineering plastics and metal designed for medical equipment, precision instruments, rehab and disability aids** even for applications requiring the use of corrosion resistant materials in compliance with the most rigorous hygienic laws.



The Trademark "100% GREEN" guarantees that the subjects authorised to make use of it, the Users, consume electricity produced by the A2A Group from renewable sources guaranteed by certificates of origin and marketed through one of the Group's companies.



ELESA provide over 45,000 product codes, annual production of tens of millions of pieces, more than 200 patents worldwide, 43 international awards in Industrial Design, alongside ISO 9001, ISO 14001, BS OHSAS 18001 and AEO certifications. With over 75 years of leadership, ELESA is the global reference point for designers and manufacturers worldwide. With 12 global branches, and a close collaboration with the most prestigious distributors worldwide, ELESA ensure an efficient and timely service, coupled with the guarantee of free technical consultancy.

Points of strength

- 200 PATENTS AND REGISTERED DESIGNS
- 43 INDUSTRIAL DESIGN AWARDS
- WORLDWIDE DISTRIBUTION
- FULL STOCK AVAILABILITY
- CUSTOMISED SOLUTIONS
- TECHNICAL COMPETENCE AT THE CUSTOMER'S SERVICE
- ISO 9001 - ISO 14001 - BS OHSAS 18001



FM 23747



EMS 518430



OHS 584384

elesa[®]



White colour with dirt-proof surfaces

CLEAN line

The white colour RAL 9002 is particularly suitable in medical environments, as it allows prompt identification of any dust or dirt traces, giving operators and patients a sense of sterility and cleanliness. Stainless steel inserts are available for applications subject to legal requirements, where mandatory, to use corrosion-resistant materials. Compact shapes, smooth surface and glossy finishing prevent any deposit of dirt, dust or machining residues.




Corrosion Resistance

INOX line

ELESA offers a wide range of products in plastic with AISI 303, AISI 304 and AISI 316 stainless steel inserts or entirely made in AISI stainless steel. Ideal for applications where provisions of law make it mandatory to use special corrosion-resistant materials.

ELESA offers a wide range of products in plastic with AISI 303, AISI 304 and AISI 316 stainless steel inserts or entirely made in AISI stainless steel. Ideal for applications where provisions of law make it mandatory to use special corrosion-resistant materials.





Safe, comfortable and non-slip grip

SOFT-TOUCH line

The SOFT-TOUCH thermoplastic elastomer coating certified under FDA (U.S. Food and Drug administration) provides a secure and comfortable grip, even under poor conditions subject to moisture and grease. Comfort for the operator's hand is paramount within this range, allowing absorption of any harsh vibrations during operation. Special additions of colour in the moulding material or coloured plastic caps and covers, allow a total aesthetic combination to customers' specific applications, too.



Sanitisation against microbes, bacteria and fungi

SAN-Antimicrobial line

Components in a special technopolymer with silver ion additives on an inorganic base (without active pharmaceutical ingredients, antibiotics or pesticides) which prevents the proliferation of unhealthy organisms such as microbes, bacteria and fungi by penetrating the surface of the unwanted and attacking their DNA.

The controlled release mechanism of the silver ions ensures that after numerous washing cycles, the product guarantees antimicrobial characteristic of the SAN-Antimicrobial line.

SAN-Antimicrobial products are available in technopolymer RAL 7021 grey-black or in the new RAL 9016 white colours.

The laser-engraved logo is clearly recognisable on the matte surface.

Laboratory tests

Laboratory tests show that 98.9% of bacteria are eliminated over the course of 24 hours (ISO 22196: 2011). All components of SAN-Antimicrobial line are provided with the Statement of Compliance "Antimicrobial Properties of Materials". Tests were carried out by CSI S.p.A., an accredited and recognised laboratory by ACCREDIA (n.0006), being the National Accreditation Body. The laboratory complies with the requirements of UNI CEI EN ISO / EC 17025. Certificate identification: C0144 \ FPM \ FOOD \ 19_1_2.



Strains used

- Staphylococcus Aureus ATCC® 25923™ (antimicrobial activity 99,9%)
- Escherichia Coli ATCC® 25922™ (antimicrobial activity 99,9%)
- Klebsiella Pneumoniae ATCC® 13883™ (antimicrobial activity 99,8%)
- Pseudomonas Aeruginosa ATCC® 27853™ (antimicrobial activity 99,9%)
- Candida Albicans ATCC® 10231™ (antimicrobial activity 98,9%)



Ergonomics and Design. The service of functionality and security

Ergostyle® elements were initially conceived for a series of new market segment applications including hospital and medical equipment, sports and leisure equipment, scientific instrumentation and office furniture. Today, Ergostyle elements are applied in more traditional industrial sectors, where machines and equipment require aesthetic renovation. Elements with modern, elegant shapes with inserts in 7 ELECOLORS® allow the components to be better integrated on machinery from an aesthetical point of view contributing to enhance their value. In addition, the coloured inserts can be used to differentiate machinery functions, too.

The 7 ELECOLORS® colours



ERGOSTYLE®
by ELESa



CT.476, VC.692, VB.639




VRTP+I, ERX., PMT.100



MBT., GN 607.2




Clamping knobs and wing knobs in technopolymer with stainless steel inserts.



Manoeuvring, clamping and positioning elements in technopolymer and SUPER-Technopolymer.



Clamping knobs and positioning elements in technopolymer and zinc-plated inserts.



ELESA. More and more...



elesa®

ELESA (UK) LTD
26 Moorlands Estate
Metheringham
Lincolnshire LN4 3HX
Phone +44 (0) 1526 322670
Fax +44 (0) 1526 322669

sales@elesa.co.uk

elesa.com