



Wireless spindle
positioning system



STANDARD MACHINE ELEMENTS WORLDWIDE

elesa®

Wireless spindle positioning system



The wireless system, consisting of **UC-RF** control unit and up to 36 electronic position indicators **DD52R-E-RF**, is designed for an efficient manual spindle positioning.

DD52R-E-RF position indicators (Elesa Patent) are networked to **UC-RF** control unit via radio frequency (RF), so that connecting cables are not required for an easy and quick installation.

Current and target positions are transmitted via RF, from and to the control unit, facilitating machine set-up.

Efficient Machine Set-Up

The system allows to save time during the format alignment process.

- Once the set-up profile has been called up by PLC, UC-RF control unit transmits the target position to each DD52R-E-RF position indicator.
- The current / target position is displayed on LCD display of DD52R-E-RF indicator.
- The operator manually sets the position of the spindles following the arrow displayed on LCD display (clockwise/anti-clockwise rotation).
- Once all the spindles are correctly set, UC-RF control unit communicates to PLC of the machine that the set-up has been completed.


Easy installation

Up to 36 position indicators can be networked (via radio frequency) to the control unit.

No cables required to connect the position indicators to the control unit.

Safety

The system prevents the machine from starting up until the machine set-up is completed, avoiding production issues.





EtherNet/IP

Modbus

PROFI
BUS

**BASE AND CASE**

High-resistance polyamide based (PA) technopolymer.

Black base.

Case in the following colours:

- **C2:** RAL 2004 orange, glossy finish.

- **C3:** RAL 7035 grey, glossy finish.

Available on request in RAL 7021 grey-black colour (C1).

Cover with perfectly sealed gasket and AISI 304 stainless steel UNI 6955 type self-tapping screws with six-lobe socket TORX®T06 (registered trademark by TEXTRON INC.).

The ultrasonic welding between the base and the case prevents separation and avoids dust and liquid penetration.

BOSS

AISI 304 stainless steel with Ø 20 mm H7 reamed hole, fitting to shaft by means of AISI 304 stainless steel grub screw, hexagon socket and cup end UNI 5929-85, included in the supply.

WINDOW

Transparent polyamide based (PA-T) technopolymer, moulded over the case and with a perfect seal. Resistant to solvents, oils, greases and other chemical agents (avoid contact with alcohol during cleaning operations).

DISPLAY

- 6-digit LCD of 12,0 mm height and special characters.

The visualization parameters can be set and modified by the operator by means of appropriate keys:

- values displayed in mm, inches or degrees
- display of mode for use (absolute or incremental mode)
- reading orientation (right or reverse).

KEYBOARD

Polyester membrane. Resistant to solvents, alcohol, acids, alkalis.

INTERNAL GASKET

O-ring front sealing in NBR synthetic rubber, between the case and the boss.

Brass bushing with double O-ring sealing in NBR synthetic rubber inside the rear cavity of the base (DD52R-E-SST-IP67).

REAR GASKET


Foam polyethylene, supplied.

STANDARD EXECUTIONS

- **DD52R-E-RF-SST-IP65:** completely sealed indicator with IP 65 protection class, see EN 60529 table.
- **DD52R-E-RF-SST-IP67:** completely sealed indicator with IP 67 protection class, see EN 60529 table obtained by means of a brass bushing with double seal ring inside the rear cavity of the base.

ASSEMBLY INSTRUCTIONS


1. Drill a Ø 6 mm by 10 mm hole in the body of the machine with a 30 mm centre distance from the spindle to fit the rear referring pin.
2. Fit the indicator onto the spindle and make sure that the referring pin fit the hole.
3. Clamp the boss to the spindle by tightening the grub screw with hexagon socket and cup end, according to UNI 5929-85.



ELESA Original design


ACCESSORIES ON REQUEST (TO BE ORDERED SEPARATELY)

- **RB52-SST:** AISI 304 stainless steel reduction sleeves.

**RB52-SST**

Code	Description	dH7
CE.97941	RB52-12-SST-304	12
CE.97951	RB52-14-SST-304	14
CE.97956	RB52-15-SST-304	15
CE.97961	BSA52-16-SST-304	16

- **BSA52-E:** die-cast zinc alloy bases for spindle locking, epoxy resin coating, black colour, matte finish. GN 302 adjustable handle with die-cast zinc alloy lever body and AISI 304 stainless steel clamping element. A Ø 6.1 mm hole to fit the referring pin of the indicator. Handle positioned either on the right or on the left. Fitting to the machine by means of two M4 cylindrical-head screws (not included in the supply).



Code	Description	dH7
CE.99091	BSA52-E-12	12
CE.99093	BSA52-E-14	14
CE.99094	BSA52-E-15	15
CE.99095	BSA52-E-16	16
CE.99099	BSA52-E-20	20

FEATURES AND APPLICATIONS

DD52R-E-RF position indicators, with battery power supply, can be used on passing through shafts in any position to provide the reading of the absolute or incremental positioning of a machine component.

- The 6-digit display of 12,0 mm height ensures excellent readability even from a distance and from different viewing angles.
- The window in transparent technopolymer protects the LCD display against accidental shocks.
- The high protection degree, IP 65 or IP67, makes the indicator suitable for applications that require frequent washing, even with intense water jets.
- In the operating mode, by using the 4 function keys, it is possible to select the incremental or the absolute mode, the unit of measure (mm, inches or degrees), reset the absolute counter or load a preset source value and the preset offset value.
- In the programming mode, through the 4 function keys, it is possible to program the reading after one revolution of the shaft, the direction of rotation, the display orientation, the resolution (number of decimal digits displayed), the source value and the offset value, the max. speed of rotation and set the functions of the keys for the different options available.
- The internal battery ensures long battery life (over 3 years). A special symbol appears on the display when it is necessary to replace the battery. The replacement can be performed easily by removing the front cover (Fig.1), without disassembly of the indicator from the control shaft and without the loss of configuration parameters.

QUICK POSITIONING SYSTEM

DD52R-E-RF indicators (Elesa Patent) are networked to the control unit UC-RF via radio frequency (RF), constituting a wireless system for rapid positioning of the machine parts (fig.2).

This system is particularly suitable for applications that require frequent format changes, facilitating the correct adjustment of the target/current position of the machine parts, also representing a safety system. In fact, even if a single DD52R-E-RF indicator is not placed in the target position, PLC doesn't allow the beginning of the machine production cycle, thus avoiding production issues.

The installation of the system is quick and easy as it does not require the use of connecting cables between the control unit and the indicators. Further technical information available in "Operating instructions".

Mechanical and electrical characteristics	
Tension feed	Lithium battery CR2477 3.0 V
Battery life	3 years
Display	6-digit LCD of 12 mm height and special characters
Reading scale	-199999; 999999
Number of decimal digits	programmable ⁽¹⁾
Unit of measure	mm, inches, degrees programmable ⁽¹⁾
Rotation max. speed	300/600/1000 r.p.m ⁽²⁾ programmable ⁽¹⁾
Precision	10.000 impulses / revolution
Protection class	IP65 or IP67
Working temperature	0 to 50 °C
Storing temperature	-20 to +60 °C
Relative humidity	Max. 95% at 25°C without condensation
Interference protection	IEC 61326-1

- (1) See the operating instructions.
(2) Default: 600 r.p.m.
Higher rotation speed to 600 r.p.m. can be maintained for short periods of time.
The value of the max. speed affects the battery life.






Fig.2





INOX STAINLESS STEEL

Code	Description	
CE.99202	DD52R-E-RF-SST-IP65-C2	129
CE.99201	DD52R-E-RF-SST-IP65-C3	129
CE.99212	DD52R-E-RF-SST-IP67-C2	141
CE.99211	DD52R-E-RF-SST-IP67-C3	141

MATERIAL
ABS reinforced polycarbonate, self-extinguishing.

STANDARD EXECUTIONS

- **UC-RF RS232**: control unit with RS232 serial interface.
- **UC-RF RS485**: control unit with RS485 serial interface.
- **UC-RF ETHERNET/IP**: control unit with Ethernet/IP serial interface.
- **UC-RF MODBUS TCP**: control unit with Modbus TCP serial interface.

UC-RF control unit can manage up to 36 position indicators. DD52R-E-RF (see page 4).
Compatible for mounting on DIN RAIL. Two leds (green and red) for correct diagnostics.

FEATURES AND APPLICATIONS

UC-RF control unit, connected directly to PLC, receives the target positions and sends them to DD52R-E-RF electronic position indicators, receiving their current position (Fig.1).

This system is particularly suitable for applications that require frequent format changes, facilitating the correct adjustment of the target/current position of the machine parts, also representing a safety system.

In fact, even if a single DD52R-E-RF indicator is not placed in the target position, PLC doesn't allow the beginning of the machine production cycle, thus avoiding production issues.



SPECIAL EXECUTION ON REQUEST
Control unit with Profibus serial interface.




ELESA Original design



Fig.1



Code	Description
CE.99221	UC-RF RS232
CE.99223	UC-RF RS485
CE.99225	UC-RF ETHERNET/IP
CE.99229	UC-RF MODBUS TCP



ELESA. More and more...



elesa

ELESA SCANDINAVIA AB
Djupdalsvägen 27
SE - 192 51 Sollentuna
Phone +46 8 444 4430
Fax +46 8 35 75 40
info@elesa.se

elesa.com

Printed in Italy
ZDEPDD-RE-ENG18SVE



© Copyright ELESA 2018