


MRY-SST-HVD: The Ultimate Solution for Watertight Clamping

ELESA enhances its range of **adjustable handles** by introducing the brand-new **watertight MRY-SST-HVD handle**, designed for applications requiring **frequent cleaning** and **exposure to liquids**. This adjustable handle is conceived to meet the needs of industries where **cleanliness** and **safety** are paramount, offering robust performance and reliability in demanding environments, for example on machines and equipment in the food, pharmaceutical, and chemical industries.

Main Features:

- **Material and Design:** MRY-SST-HVD handle is made from glass-fibre reinforced polyamide (PA) technopolymer, "Signal blue" RAL 5005, material **suitable for contact with food** (FDA CFR.21 and EU 10/2011). Easily **detectable** and **recognisable** to the human eye, thanks to the specificity and uniqueness of the colour naturally absent in the environment in which these components are applied. These characteristics contribute to increasing the levels of safety in food production processes.
- **Watertight Construction:** the system of **gaskets** between the parts of the adjustment mechanism makes this handle practically **watertight**, preventing the deposit of residues, which can represent a risk of contamination. This feature makes the handle ideal for environments subject to cleaning cycles with water jets.
- **Stainless Steel Components:** the handle is available with AISI 316 stainless steel boss or threaded stud. Compared to other types of handles with metal retaining screws, this solution offers in addition: the **electrical insulation** for the operator during operations, the **removal** of visible steel parts that may rust, and a **more comfortable lever disengagement** – even with lack of space.
- **Ergonomics and Safe:** the **cavity-free design** and the **plain surface finish** (roughness Ra < 0.8 µm) ensure maximum serviceability, making it easier to clean and maintain.



1941 – 2025

Serving industry for over 80 years

Elesa designs and produces the widest range of standard components for industrial machines and equipment: handwheels, clamping handles and levers, adjustable levers, clamping elements, knobs, position indicators, indexing and spring plungers, levelling feet, hinges, tubes connectors, latches, accessories for hydraulic systems, modular roller tracks, castors and wheels, magnets, vibration mounts and vacuum components. Made with the most advanced technopolymers and metals, highly efficient and reliable, ergonomic and innovative design, Elesa brand products are used in the most diverse areas of application in the sector of industrial mechanics. The constant commitment to R&D is combined with a strongly customer-centric service. Founded in 1941 with headquarters in Monza and 15 subsidiaries abroad, Elesa exports its products to more than 60 countries worldwide.

Press Box

Contact: Alfred Jangbratt
E-mail: alfred.jangbratt@elesa.se

ELESA Scandinavia AB
Djupdalsvägen 27 – 192 51 Sollentuna
tel. +46 8 444 44 30 - info@elesa.se

elesa.com
STANDARD MACHINE ELEMENTS WORLDWIDE

